

INTRODUCING

ALCOSWITCH 12 MM ANTI-VANDAL FLUSH SWITCH

- Allows for an easy user interface with a large pushbutton and available LED indicators that illuminate the switch



TE Connectivity (TE)'s new ALCOSWITCH Anti-Vandal Flush switch series is designed for security and reliability in a variety of panel mount industrial and building applications. The large pushbutton and available LED indicators illuminate the switch and allow for an easy user interface. The Anti-Vandal series is available in panel sizes of 12 mm, 16 mm, 19 mm, 22 mm and 25 mm, and with various pushbutton symbols including spot, ring, and power logo. Switches are sealed to IP67 and available in single and double pole configurations.

BENEFITS

- Allows for an easy user interface with a large pushbutton and available LED indicators that illuminate the switch
- Achieves a vandal proof solution with a jam nut accessible for rear of the panel
- Ease of installation with available flying lead terminations
- IP67 Seal ensuring reliability in harsh environments

APPLICATIONS

- Industrial controls
- Outdoor lighting controls
- Hand-held control units
- Medical equipment
- Outdoor grills
- Communication equipment

MECHANICAL

- 100K cycles electrical life

ELECTRICAL

- 100 mA@24 VDC

MATERIAL

- Stainless steel

LEARN MORE

- [ALCOSWITCH 12 mm anti-vandal flush switch product page](#)
- [ALCOSWITCH 12 mm anti-vandal flush switch model detail page](#)
- [ALCOSWITCH 12 mm anti-vandal flush switch part list](#)
- [ALCOSWITCH 12 mm anti-vandal flush switch images](#)
- [ALCOSWITCH 12 mm anti-vandal flush switch datasheet](#)