




SYM	ECN	DESCRIPTION	DATE	APPROVED
0A	---	FIRST RELEASE	08/01'24	Dam



LABEL:




WIRE LIST:



NOTES:

- PRODUCT MUST COMPLY TO THE LATEST LEVEL OF SAE/USCAR30.
- ELECTRICAL PERFORMANCE:
CURRENT RATING: 5A
INSULATION RESISTANCE: 5M Ω MIN. (200V DC)
- MECHANICAL PERFORMANCE:
DURABILITY: 10 CYCLES MIN.
TEMPERATURE RANGE: -40°C TO +105°C
- MATERIAL SHOULD BE FULFILLED RoHS REQUIREMENT AND AMPHENOL SPEC# SSN002.
- ORDER P/N SYSTEM:



HF(无卤)
Non-HF(有卤) ☒

3	CONNECTOR	MINI HSBRIDGE+ USB INLINE CABLE CONNECTOR CODE-A	1
2	CONNECTOR	MINI HSBRIDGE+ USB PLUG CABLE CONNECTOR CODE-A	1
1	RAW CABLE	USB3.1 FEP,(30AWG-1P+EAM) $\times$ 4+(30AWG-1P+AM) $\times$ (32AWG-1C) $\times$ 4+21AWG $\times$ 1C,005.2	A/R
ITEM NAME		DESCRIPTION	
UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL DATE	
0 +/- 0.00 FRACTIONS ANGLES +/-		DRAWN Simon 08/01'24 CHECKED Johnny 08/01'24 CHECKED	
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS U.S. INCHES (METRIC) (MM)		TITLE Amphenol CUSTOMER DRAWING FOR MINI HSBRIDGE+ USB PLUG TO INLINE CABLE, CODE A-A, L=200MM	
SIZE A3		DRAWING NO. USBCC231AA019AS	
SCALE N/A		REV. 0A	
SHEET 1 OF 1		1	