



## Broadest Range of LED Panel Mount Indicators



**PCL22 Series**  
Ø.88" (22.3mm)



**CNX722 Series**  
Ø.866" (21.9mm)



**PML50 Series**  
Ø.69" (17.5mm)



**CNX718 Series**  
Ø.688" (17.5mm)



**1116 Series**  
Ø.688" (17.5mm)



**CL Series**  
Ø.551" (14mm)



**CNX714 Series**  
Ø.551" (14mm)



**1732 Series**  
Ø.53" (13.5mm)



**1092 Series**  
Ø.5" (12.7mm)



**P8 Series**  
Ø.5" (12.7mm)



**CNX482 Series**  
Ø.4" (10.2mm)



**6091 Series**  
Ø.38" (9.7mm)



**CCLB/BCLB Series**  
Ø.319" (8.1mm)



**CRLB/BRLB Series**  
Ø.319" (8.1mm)



**L65 Series**  
Ø.315" (8mm)



**CRM/BRM Series**  
Ø.315" (8mm)



**5400 Series**  
Ø.315" (8mm)



**74S Series**  
Ø.312" (7.9mm)



**PMRL200 Series**  
Ø.312" (7.9mm)



**100/600 Series**  
Ø.312" (7.9mm)



**CC Series**  
Ø.312" (7.9mm)



**CR/BR Series**  
Ø.312" (7.9mm)



**50 Series**  
Ø.312" (7.9mm)



**L79D Series**  
Ø.312" (7.9mm)



**L41EN Series**  
Ø.312" (7.9mm)



**90 Series**  
Ø.290" (7.4mm)



**CNX C Series**  
Ø.281" (7.1mm)



**L6-0/L6-1 Series**  
Ø.276" (7mm)



**5102H Series**  
Ø.250" (6.4mm)



**40 Series**  
Ø.250" (6.4mm)



**P44/PR44 Series**  
Ø.250" (6.4mm)



**P405/PR405 Series**  
Ø.250" (6.4mm)



**L5-0/L5-1 Series**  
Ø.250" (6.4mm)



**L63 Series**  
Ø.244" (6.2mm)



**CD/CDLB Series**  
Ø.236" (6mm)



**L60 Series**  
Ø.230" (5.8mm)



**CS/BS Series**  
Ø.230" (5.8mm)



**PMRL125 Series**  
Ø.230" (5.8mm)



**3990 Series**  
Ø.22" (5.6mm)



**6039 Series**  
Ø.193" (4.9mm)



**30 Series**  
Ø.190" (4.8mm)



**4000/3000 Series**  
Ø.187" (4.7mm)



**L4-0/L4-1 Series**  
Ø.187" (4.7mm)



**5110 Series**  
Ø.157" (4mm)



**P205 Series**  
Ø.156" (4mm)

### Legend

- Waterproof IP Rated
- Night Vision
- Ø Mounting Hole Size

Start a Conversation  
with One of Our  
Technical Engineers Today  
[vcclite.com](http://vcclite.com)