



VULCON ADAPTERS

Adapting to the Future of Circular Connectors



VULCON M8 & M12 Circular Connector Adapters are designed to easily accommodate cable routing in both free hanging and panel mount applications. Both the T and Y style adapters allow a single cable output to be split into multiple destinations, and the panel mount adapters offer a robust solution for the transition from internal wiring to external connections.

FEATURES & BENEFITS

- Available in pin counts ranging from 3 to 8 positions
- M8 A & B Code options; M12 A, B & D code options
- T & Y splitter formats for easy external cable routing
- M12 panel mounts in both male & female mating options
- RJ Adapters available in both straight and right angle options
- Up to 4 AMP contact rating / -40C to +85C
- IP67 performance in both mated & unmated conditions



NORCOMP

VULCON ADAPTERS

VULCON ADAPTERS

M8 T Adapters



T54 Series

M12 T Adapters



T58 Series

M12 Straight Panel Adapters



S58 Series

M8 Y Adapters



Y54 Series

M12 Y Adapters



Y58 Series

M12 - RJ45 Panel Adapters



RJM12 Series

T54 & Y54 Series

3 Pin A-Code
4 Pin A-Code
5 Pin B-Code

T58 & Y58 Series

4 Pin A & D Code
5 Pin A & B Code
8 Pin A Code

S58 Series

4 Pin A & D Code
5 Pin A & B Code
8 Pin A Code

RJM12 Series

4 Pin D-Code

M8 T & Y Splitters

T54-A03-MMMR001
T54-A04-MMMR001
T54B-05-MMMR001

T54-A03-FFFR001
T54-A04-FFFR001
T54-B05-FFFR001

T54-A03-MFFR001
T54-A04-MFFR001
T54-B05-MFFR001

T54-A03-FMFR001
T54-A04-FMFR001
T54-B05-FMFR001

T54-A03-FMMR001
T54-A04-FMMR001
T54-B05-FMMR001

Y54-A03-MFFR001
Y54-A04-MFFR001
Y54-B05-MFFR001

M12 T Splitters

T58-A04-MMMR001
T58-D04-MMMR001
T58-A05-MMMR001
T58-B05-MMMR001
T58-A08-MMMR001

T58-A04-FFFR001
T58-D04-FFFR001
T58-A05-FFFR001
T58-B05-FFFR001
T58-A08-FFFR001

T58-A04-FMFR001
T58-D04-FMFR001
T58-A05-FMFR001
T58-B05-FMFR001
T58-A08-FMFR001

M12 Y Splitters

Y58-A04-MMMR001
Y58-D04-MMMR001
Y58-A05-MMMR001
Y58-B05-MMMR001
Y58-A08-MMMR001

Y58-A04-FFFR001
Y58-D04-FFFR001
Y58-A05-FFFR001
Y58-B05-FFFR001
Y58-A08-FFFR001

Y58-A04-MFFR001
Y58-D04-MFFR001
Y58-A05-MFFR001
Y58-B05-MFFR001
Y58-A08-MFFR001

Y58-A04-FMFR001
Y58-D04-FMFR001
Y58-A05-FMFR001
Y58-B05-FMFR001
Y58-A08-FMFR001

M12 Adapters

S58-A04-MMR001
S58-D04-MMR001
S58-A05-MMR001
S58-B05-MMR001
S58-A08-MMR001

S58-A04-MFR001
S58-D04-MFR001
S58-A05-MFR001
S58-B05-MFR001
S58-A08-MFR001

RJM12MD04RA001
RJM12FD04RA001
RJM12MD04ST001
RJM12FD04ST001

