



Pushing Performance



People | Power | Partnership

HARTING Han-Eco[®] B

High-performance plastic connectors
in standard industrial sizes

Han-Eco® B

The Han-Eco® B series is a new series of hoods and housings in the Han-Eco® portfolio that comes in sizes 6 B – 24 B. This series is completely compatible with the Han® B industrial standard. Standard inserts and modules in conjunction with the hinged frames from the Han-Modular® portfolio may be used.



Outdoor version available for extreme environmental conditions



Compared to Han® B metal housings, the weight advantage is up to 50 % depending on the combination you choose.

The rear mounting option ensures a quick and easy assembly. Installation technicians do no longer have to conduct cables through the bulkhead mounted housing, before assembling the contact inserts. Instead, pre-assembled insulation bodies can be directly snapped into the housing from the rear.




Backward compatibility with Han® B metal hoods and housings



Rear mounting of inserts speeds up installation



Excellent mechanical robustness combined with minimal weight



“Click and mate” principle ensuring a secure assembly process

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60 529	IP65 and IP66
Material (hood / housing)	Polyamide, fibre-glass reinforced
Colour (hood / housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide, fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Flammability acc. to UL 94	V-0
Flammability acc. to UL 94 (locking levers)	V-0

Specifications and approvals

IEC 61948
EN 45545-2
R22: HL1, HL2, HL3
R23: HL1, HL2, HL3
R24: HL1, HL2, HL3



Pushing Performance

HARTING.com –
the gateway to your
local website.

www.HARTING.ae
www.HARTING.at
www.HARTING.com.au
www.HARTING.be
www.HARTING.com.br
www.HARTING.ca
www.HARTING.ch
www.HARTING.com.cn
www.HARTING.cz
www.HARTING.de
www.HARTING.dk
www.HARTING.ee
www.HARTING.es
www.HARTING.fi
www.HARTING.fr
www.HARTING.co.uk
www.HARTING.com.hk
www.HARTING.hu
www.HARTING.co.in
www.HARTING.it
www.HARTING.co.jp
www.HARTING.co.kr
www.HARTING.com.mx
www.HARTINGbv.nl
www.HARTING.no
www.HARTING.pl
www.HARTING.pt
www.HARTING.ro
www.HARTING.ru
www.HARTING.se
www.HARTING.sg
www.HARTING.sk
www.HARTING.com.tr
www.HARTING.com.tw
www.HARTING-USA.com
www.HARTING.co.za

HARTING Technology Group

info@HARTING.com
www.HARTING.com

at@HARTING.com
www.HARTING.at

ch@HARTING.com
www.HARTING.ch