


KSC-PF Series Potting Friendly Tact Switch

Features/Benefits

- Extended Cage
- Silicone actuator
- J or G terminations
- Tape & reel
- IP67

Typical Applications


- Automotive
- Medical equipment
- Industrial electronics



Type	Force (N)	Operating Life (operations)	Travel (mm)
KSC421G 70SH LFS PF	1.7+/-0.45	300,000	0.5+/-0.25
KSC421J 70SH LFS PF	1.7+/-0.45	300,000	0.5+/-0.25
KSC422G 70SH LFS PF	1.7+/-0.45	1,000,000	0.5+/-0.25
KSC422J 70SH LFS PF	1.7+/-0.45	1,000,000	0.5+/-0.25
KSC441G 70SH LFS PF	4 +/- 1	300,000	0.75+/-0.25
KSC441J 70SH LFS PF	4 +/- 1	300,000	0.75+/-0.25
KSC442G 70SH LFS PF	4 +/- 1	1,000,000	0.75+/-0.25
KSC442J 70SH LFS PF	4 +/- 1	1,000,000	0.75+/-0.25
KSC461G 70SH LFS PF	6.25+/- 1.75	300,000	1 +/- 0.3
KSC461J 70SH LFS PF	6.25+/- 1.75	300,000	1 +/- 0.3
KSC471G 70SH LFS PF	4 +/- 1	300,000	0.70+/-0.3
KSC471J 70SH LFS PF	4 +/- 1	300,000	0.70+/-0.3

Max. potting height: XX mm (see drawing)

Max. actuation altitude to PCB: xx.x mm (see drawing)



Packaging

In reels of 1,000 pieces.

Dimensions of reels according to EIA RS481 or IEC 2863.

External diameter 330 ± 2 mm

How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

For any part number different from those listed above, please consult your local representative.

