

MAXREFDES67#
uPLC Universal Input

P/N: EPCBREFDES67


maxim
integrated™

LAYER
TOPMIDLAYER


DATE:

ALL UNITS ARE IN 0.001"


REV
A




MAXREFDES67# uPLC Universal Input	
P/N: EPCBREFDES67	REV A
	
LAYER TOP SOLDERMASK	
DATE:	ALL UNITS ARE IN 0.001"





MAXREFDES67# uPLC Universal Input	
P/N: EPCBREFDES67	REV A
	
LAYER COMPONENT SIDE	
DATE:	ALL UNITS ARE IN 0.001"



MAXREFDES67# uPLC Universal Input	
P/N: EPCBREFDES67	REV A
	
LAYER LAYER 2 GND, PGND	
DATE:	ALL UNITS ARE IN 0.001"



MAXREFDES67# uPLC Universal Input	
P/N: EPCBREFDES67	REV A
 maxim integrated™	
LAYER LAYER 3 3.3V, 5VD, -1.25V, -18V	
DATE:	ALL UNITS ARE IN 0.001"




MAXREFDES67#
uPLC Universal Input

P/N: EPCBREFDES67REV
A


 **maxim**
integrated™

LAYER
LAYER 4 3.3V, 5VD, 5V, 18V


DATE:ALL UNITS ARE IN 0.001"



MAXREFDES67# uPLC Universal Input	
P/N: EPCBREFDES67	REV A
	
LAYER LAYER 5 GND, PGND	
DATE:	ALL UNITS ARE IN 0.001"



MAXREFDES67# uPLC Universal Input	
P/N: EPCBREFDES67	REV A
	
LAYER SOLDER SIDE SIGNALS, 22V, 7V	
DATE:	ALL UNITS ARE IN 0.001"



MAXREFDES67#
uPLC Universal Input

P/N: EPCBREFDES67



REV
A

maxim
integrated™

LAYER
BOTTOM SOLDERMASK

DATE:

ALL UNITS ARE IN 0.001"



MAXREFDES67#
uPLC Universal Input

P/N: EPCBREFDES67

REV
A

maxim
integrated™

LAYER
SOLDER MASK TYPE: ENK, 7V

DATE:

ALL UNITS ARE IN 0.001"

