



Copperhead Series Speakers

More than ever before, high quality audio is becoming the determining factor when distinguishing between products and driving sales. When the sound quality of your product is on the line, choose high fidelity speakers from PUI Audio.

Our new **Copperhead Series** was designed to create a family sound across three different speaker sizes: 36mm, 53mm and 78mm square. Specialized alloy cones are paired with optimized high-energy motors to achieve superior frequency response and output, with minimized harmonic distortion. Each speaker features an easy-to-mount square frame.



The eight ohm, 36mm square frame [**AS03608AS-R**](#) features a unique spider-less design for free-flowing cone travel that is controlled by the progressive treated foam surround. It is designed to handle up to 2W max power with frequency response of 150 Hz to 40 kHz.



The eight ohm, 53mm square frame [**AS05308AS-R**](#) features a rubber surround, for water and dust resistance, and a vented voice coil former for improved voice coil cooling. It is designed to handle up to 20W max power and can play from 80 Hz up to 40 kHz.



The eight ohm, 78mm square frame [**AS07808AS-R**](#) features a rubber surround, for water and dust resistance, and a shielded double-stacked motor to protect sensitive components and for high sensitivity. It is designed to handle up to 30W max power and can play from 60 Hz up to 40 kHz.