



QUINT POWER

Customizable power supplies

QUINT POWER

Customizable power supplies

Adaptable

- Integrated NFC interface
- Configurable reporting thresholds and characteristic curves

Powerful

- SFB technology:
 - 6 times the nominal current for 15 ms
- Power reserves:
 - Static boost: Up to 125 % for a sustained period
 - Dynamic boost: Up to 200 % for 5 s

Preventive

- Monitoring of outputs
- Evaluation of operating hours

Robust

- Mains buffering time > 20 ms
- High level of immunity thanks to integrated gas-filled surge arrester



QUINT POWER 1~			QUINT POWER 3~		
Input: 1-phase, 85 ... 264 V AC			Input: 3-phase, 3 x 320 ... 550 V AC, +/- 300 V DC		
					
24 V/5 A	24 V/10 A	24 V/20 A	24 V/5 A	24 V/10 A	24 V/20 A
QUINT4-PS/1AC/24DC/5 2904600	QUINT4-PS/1AC/24DC/10 2904601	QUINT4-PS/1AC/24DC/20 2904602	QUINT4-PS/3AC/24DC/5 2904620	QUINT4-PS/3AC/24DC/10 2904621	QUINT4-PS/3AC/24DC/20 2904622

PHOENIX CONTACT GmbH & Co. KG
 Flachmarktstraße 8
 32825 Blomberg, Germany
 Phone: + 49 5235 3-00
 Fax: + 49 5235 3-41200
 E-mail: info@phoenixcontact.com
phoenixcontact.com

Printed in Germany
 © PHOENIX CONTACT 2016

PS 02-16.000.L1
 MNR 52007990/2016-03-31/00