

				Designation	CRIMFOX CENTRUS 6S 1213144	CRIMFOX CENTRUS 10S 1213154	CRIMFOX CENTRUS 6H 1213146	CRIMFOX CENTRUS 10H 1213156	CRIMFOX 2,5-M 1212719	CRIMFOX 6-M 1212720	CRIMFOX 6 1212034	CRIMFOX 6T 1212037	CRIMFOX 6T-F 1212038	CRIMFOX 6S-F 1212043	CRIMFOX 10 1212721	CRIMFOX 25R 1212039	CRIMFOX 50R 1212041	CRIMFOX 16R TWIN 1212845	CRIMFOX 4 IN 1 1200101	CRIMFOX-M + ferrules dies 1212072	CRIMFOX-C120 + ferrules dies 1212318
				Crimping shape																	
				Order No.																	
Ferrules without insulating collar	Cross section	Stripping length (reference value)	Designation	Order No.																	
	0.25 mm²	5	A 0,25-5	3202465 ²⁾	●	●	●	●	●	●	●	●	●							●	
		7	A 0,25-7	3202478 ²⁾	●	●	●	●	●	●	●	●	●							●	
	0.34 mm²	7	A 0,34-7	3009202 ²⁾	●	●	●	●	●	●	●	●	●							●	
	0.5 mm²	6	A 0,5-6	3200218	●	●	●	●	●	●	●	●	●	●						●	
		8	A 0,5-8	3202481	●	●	●	●	●	●	●	●	●	●						●	
		10	A 0,5-10	3202494	●	●	●	●	●	●	●	●	●	●						●	
	0.75 mm²	7	A 0,75-6	3200221	●	●	●	●	●	●	●	●	●	●						●	
		8	A 0,75-8	3202504	●	●	●	●	●	●	●	●	●	●						●	
		10	A 0,75-10	3200234	●	●	●	●	●	●	●	●	●	●						●	
	1.00 mm²	6	A 1-6	3200247	●	●	●	●	●	●	●	●	●	●						●	
		8	A 1-8	3202517	●	●	●	●	●	●	●	●	●	●						●	
		10	A 1-10	3200250	●	●	●	●	●	●	●	●	●	●						●	
	1.50 mm²	7	A 1,5-7	3200263	●	●	●	●	●	●	●	●	●	●						●	
		10	A 1,5-10	3200276	●	●	●	●	●	●	●	●	●	●						●	
		12	A 1,5-12	3202588	●	●	●	●	●	●	●	●	●	●						●	
		15	A 1,5-15	3202591	●	●	●	●	●	●	●	●	●	●						●	
		18	A 1,5-18	3202601	●	●	●	●	●	●	●	●	●	●						●	
	2.5 mm²	7	A 2,5-7	3200289	●	●	●	●	●	●	●	●	●	●						●	
		12	A 2,5-12	3200292	●	●	●	●	●	●	●	●	●	●						●	
		18	A 2,5-18	3202821	●	●	●	●	●	●	●	●	●	●						●	
	4 mm²	9	A 4-9	3200302	●	●	●	●		●	●	●	●	●	●					●	
		12	A 4-12	3200315	●	●	●	●		●	●	●	●	●	●					●	
		18	A 4-18	3202834	●	●	●	●		●	●	●	●	●	●					●	
	6 mm²	10	A 6-10	3202520	●	●	●	●		●	●	●	●	●	●					●	
		12	A 6-12	3200328	●	●	●	●		●	●	●	●	●	●					●	
	10 mm²	12	A 10-12	3200331		●		●							●	●				●	
		18	A 10-18	3200344		●		●							●	●				●	
	16 mm²	12	A 16-12	3200425												●				●	
	25 mm²	12	A 25-12	3200357												●				●	
		15	A 25-15	3200360												●				●	
		18	A 25-18	3200373												●				●	
		20	A 25-20 ²⁾	3200386												●				●	
		40	A 25-40 ²⁾	3241238												●				●	
	35 mm²	18	A 35-18	3200399													●			●	
		20	A 35-20	3200409													●			●	
		40	A 35-40 ²⁾	3241239													●			●	
	50 mm²	40	A 50-40 ²⁾	3241240													●			●	●
	70 mm²	40	A 70-40 ²⁾	3241241																	●
	95 mm²	40	A 95-40 ²⁾	3241242																	●

²⁾These ferrules are not UL certified.

			Designation		CRIMFOX CENTRUS 6S	CRIMFOX CENTRUS 10S	CRIMFOX CENTRUS 6H	CRIMFOX CENTRUS 10H																															
					1213144	1213154	1213146	1213156	CRIMFOX 2,5-M	CRIMFOX 6-M	CRIMFOX 6	CRIMFOX 6T		CRIMFOX 6T-F	CRIMFOX 6S-F	CRIMFOX 10	CRIMFOX 25R	CRIMFOX 50R	CRIMFOX 16R TWIN	CRIMFOX 4 IN 1	CRIMFOX-M + ferrules dies	CRIMFOX-C120 + ferrules dies																	
Cross section	Stripping length (reference value)	Designation	Order No.	Color																																			
0.14 mm²	10	AI 0,14-8 GY-1000 ²⁾	3203011	Gray	●	●	●	●																															
	8	AI 0,25-6 BU ²⁾	3203040	Blue	●	●	●	●	●	●	●	●	●	●	●	●																			●				
0.25 mm²	8	AI 0,25-6 YE ²⁾	3203024	Yellow	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	10	AI 0,25-8 BU ²⁾	3201364	Blue	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	10	AI 0,25-8 YE ²⁾	3203037	Yellow	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	12	AI 0,25-10 YE ²⁾	3241128	Yellow	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	14	AI 0,25-12 BU ²⁾	3200632	Blue	●	●	●	●	●	●	●	●	●	●	●	●																			●				
0.34 mm²	8	AI 0,34-6 TQ ²⁾	3203053	Turquoise	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	10	AI 0,34-8 TQ ²⁾	3203066	Turquoise	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	12	AI 0,34-10 TQ ²⁾	3241129	Turquoise	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	14	AI 0,34-12 TQ ²⁾	3200645	Turquoise	●	●	●	●	●	●	●	●	●	●	●	●																			●				
0.5 mm²	9	AI 0,5-6 OG	3201301	Orange	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	9	AI 0,5-6 WH	3200687	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,5-8 OG	3201123	Orange	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,5-8 OG-1000	3202902	Orange	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,5-8 WH	3200014	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,5-8 WH-1000	3200881	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,5-10 OG	3241126	Orange	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,5-10 WH	3201275	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	15	AI 0,5-12 WH	3200506	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,5-8 WH-GB	1208966	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,5-10 WH-GB	3203150	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI-WM 0,5-8 WH ²⁾	3240542	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
0.75 mm²	9	AI 0,75-6 GY	3200690	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	9	AI 0,75-6 WH	3201314	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,75-8 BU	3200027	Blue	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,75-8 GY	3200519	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,75-8 GY-1000	3200894	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,75-8 WH	3201110	White	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,75-10 GY	3201288	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,75-10 GY-1000	3203118	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	15	AI 0,75-12 GY	3200849	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 0,75-8 GY-GB	1208979	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,75-10 GY-GB-1000	3203299	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	13	AI 0,75-10 GY-GB	3203163	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●				
11	AI-WM 0,75-8 GY ²⁾	3240543	Gray	●	●	●	●	●	●	●	●	●	●	●	●																			●					
1 mm²	9	AI 1-6 RD	3200742	Red	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	9	AI 1-6 YE	3201327	Yellow	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 1-8 RD	3200030	Red	●	●	●	●	●	●	●	●	●	●	●	●																			●				
	11	AI 1-8 RD-1000	3200904	Red	●																																		

²⁾ These ferrules are not UL certified.

					Designation	CRIMFOX CENTRUS 6S 1213144	CRIMFOX CENTRUS 10S 1213154	CRIMFOX CENTRUS 6H 1213146	CRIMFOX CENTRUS 10H 1213156	CRIMFOX 2,5-M 1212719	CRIMFOX 6-M 1212720	CRIMFOX 6 1212034	CRIMFOX 6T 1212037	CRIMFOX 6T-F 1212038	CRIMFOX 6S-F 1212043	CRIMFOX 10 1212721	CRIMFOX 25R 1212039	CRIMFOX 50R 1212041	CRIMFOX 16R TWIN 1212845	CRIMFOX 4 IN 1 1200101	CRIMFOX-M + ferrules dies 1212072	CRIMFOX-C120 + ferrules dies 1212318	
																							
Cross section	Stripping length (reference value)	Designation	Order No.	Color																			
1.5 mm²	9	AI 1,5-6 BK	3200755	Black	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 1,5-8 BK	3200043	Black	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 1,5-8 BK-1000	3200917	Black	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 1,5-8 RD	3201136	Red	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 1,5-8 RD-1000	3202928	Red	●	●	●	●	●	●	●	●	●	●						●			
	13	AI 1,5-10 BK	3200195	Black	●	●	●	●	●	●	●	●	●	●						●			
	13	AI 1,5-10 BK-1000	3203134	Black	●	●	●	●	●	●	●	●	●	●						●			
	15	AI 1,5-12 BK	3201482	Black	●	●	●	●	●	●	●	●	●	●						●			
	21	AI 1,5-18 BK	3200056	Black	●	●	●	●	●	●	●	●	●	●						●			
	21	AI 1,5-18 RD	3241125	Red	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 1,5-8 BK-GB-1000	3202892	Black	●	●	●	●	●	●	●	●	●	●						●			
	13	AI 1,5-10 BK-GB-1000	1208872	Black	●	●	●	●	●	●	●	●	●	●						●			
	11	AI-WM 1,5-8 WH ²⁾	3240545	White	●	●	●	●	●	●	●	●	●	●						●			
15	AI-XL 1,5-8 BK	3201916	Black	●	●	●	●	●	●	●	●	●	●						●				
13	AI-XL 1,5-10 BK	3201974	Black	●	●	●	●	●	●	●	●	●	●						●				
2.5 mm²	11	AI 2,5-8 BU	3200522	Blue	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 2,5-8 BU-1000	3200920	Blue	●	●	●	●	●	●	●	●	●	●						●			
	11	AI 2,5-8 GY	3200069	Gray	●	●	●	●	●	●	●	●	●	●						●			
	13	AI 2,5-10 BU	3202533	Blue	●	●	●	●	●	●	●	●	●	●						●			
	13	AI 2,5-10 BU-1000	3203147	Blue	●	●	●	●	●	●	●	●	●	●						●			
	15	AI 2,5-12 BU	3200962	Blue	●	●	●	●	●	●	●	●	●	●						●			
	15	AI 2,5-12 GY	3200205	Gray	●	●	●	●	●	●	●	●	●	●						●			
	21	AI 2,5-18 BU	3200580	Blue	●	●	●	●	●	●	●	●	●	●						●			
	21	AI 2,5-18 GY	3200072	Gray	●	●	●	●	●	●	●	●	●	●						●			
	11	AI-WM 2,5-8 BU ²⁾	3240572	Blue	●	●	●	●	●	●	●	●	●	●						●			
	13	AI-XL 2,5-8 BU	3201929	Blue	●	●	●	●	●	●	●	●	●	●						●			
17	AI-XL 2,5-12 BU	3201987	Blue	●	●	●	●	●	●	●	●	●	●						●				
4 mm²	13	AI 4-10 GY	3200535	Gray	●	●	●	●		●	●	●	●	●	●					●			
	13	AI 4-10 OG	3200085	Orange	●	●	●	●		●	●	●	●	●	●	●				●			
	15	AI 4-12 GY	3200959	Gray	●	●	●	●		●	●	●	●	●	●	●				●			
	15	AI 4-12 OG	3200438	Orange	●	●	●	●		●	●	●	●	●	●	●				●			
	21	AI 4-18 GY	3200593	Gray	●	●	●	●		●	●	●	●	●	●	●				●			
	21	AI 4-18 OG	3200098	Orange	●	●	●	●		●	●	●	●	●	●	●				●			
	16	AI-XL 4-10 GY	3201932	Gray	●	●	●	●		●	●	●	●	●	●	●				●			
6 mm²	15	AI 6-12 BK	3201107	Black	●	●	●	●		●	●	●	●	●	●					●			
	15	AI 6-12 GN	3200108	Green	●	●	●	●		●	●	●	●	●	●	●				●			
	15	AI 6-12 YE	3200548	Yellow	●	●	●	●		●	●	●	●	●	●	●				●			
	21	AI 6-18 GN	3200111	Green	●	●	●	●		●	●	●	●	●	●	●				●			
	21	AI 6-18 YE	3200603	Yellow	●	●	●	●		●	●	●	●	●	●	●				●			
	15	AI 6-12 TR ²⁾	1200129	Transparent	●	●	●	●		●	●	●	●	●	●	●				●			
	18	AI-XL 6-12 YE	3201945	Yellow	●	●	●	●		●	●	●	●	●	●	●				●			
10 mm²	15	AI 10-12 BN	3200124	Brown		●		●							●	●				●			
	15	AI 10-12 IV	3201068	Ivory		●		●							●	●				●			
	15	AI 10-12 RD	3200551	Red		●		●							●	●				●			

²⁾ These ferrules are not UL certified

						Designation																								
						CRIMFOX CENTRUS 6S 1213144	CRIMFOX CENTRUS 10S 1213154	CRIMFOX CENTRUS 6H 1213146	CRIMFOX CENTRUS 10H 1213156	CRIMFOX 2,5-M 1212719	CRIMFOX 6-M 1212720	CRIMFOX 6 1212034	CRIMFOX 6T 1212037	CRIMFOX 6T-F 1212038	CRIMFOX 6S-F 1212043	CRIMFOX 10 1212721	CRIMFOX 25R 1212039	CRIMFOX 50R 1212041	CRIMFOX 16R TWIN 1212845	CRIMFOX 4 IN 1 1200101	CRIMFOX-M + ferrules dies 1212072	CRIMFOX-C120 + ferrules dies 1212318								
	Crimping shape																													
Cross section	Stripping length	Designation	Order No.	Colors																										
Ferrules with insulating collar	10 mm²	15	AI 10-12 TR ²⁾	1200128	Transparent																									
		21	AI 10-18 BN	3200137	Brown																									
		21	AI 10-18 RD	3200616	Red																									
		18	AI-XL 10-12 RD	3201958	Red																									
	16 mm²	16	AI 16-12 BU	3200564	Blue																									
		16	AI 16-12 GN	3201152	Green																									
		16	AI 16-12 IV ²⁾	3201181	Ivory																									
		16	AI 16-12 WH	3200140	White																									
		22	AI 16-18 BU	3200629	Blue																									
		22	AI 16-18 GN	3201330	Green																									
		22	AI 16-18 WH	3200153	White																									
		18	AI-XL 16-12 BU ²⁾	3201961	Blue																									
	25 mm²	20	AI 25-16 BK	3200412	Black																									
		20	AI 25-16 BN	3201084	Brown																									
		20	AI 25-16 YE	3200577	Yellow																									
		22	AI 25-18 YE	3201505	Yellow																									
		26	AI 25-22 BK	3200739	Black																									
		26	AI 25-22 YE	3200700	Yellow																									
	35 mm²	20	AI 35-16 BE	3201071	Beige																									
20		AI 35-16 RD	3200441	Red																										
22		AI 35-18 RD	3201495	Red																										
29		AI 35-25 RD	3200713	Red																										
50 mm²	25	AI 50-20 BU	3200454	Blue																										
	25	AI 50-20 OL	3201178	Olive																										
	30	AI 50-25 BU	3200726	Blue																										
	30	AI 50-25 BK ²⁾	3240678	Black																										
70 mm²	25	AI 70-20 YE ²⁾	3201848	Yellow																										
95 mm²	30	AI 95-25 RD ²⁾	3201853	Red																										
120 mm²	32	AI120-27 BU ²⁾	3201822	Blue																										
TWIN ferrules	2 × 0.5 mm²	11	AI-TWIN 2 × 0,5-8 WH	3200933	White																									
		13	AI-TWIN 2 × 0,5-10 WH	3203309	White																									
	2 × 0.75 mm²	12	AI-TWIN 2 × 0,75-8 GY	3200807	Gray																									
		12	AI-TWIN 2 × 0,75-8 BU	3240668	Blue																									
		14	AI-TWIN 2 × 0,75-10 GY	3200975	Gray																									
	2 × 1 mm²	12	AI-TWIN 2 × 1-8 RD	3200810	Red																									
		14	AI-TWIN 2 × 1-10 RD	3200988	Red																									
		16	AI-TWIN 2 × 1-12 RD	3240679	Red																									
	2 × 1.5 mm²	12	AI-TWIN 2 × 1,5-8 BK	3200823	Black																									
		14	AI-TWIN 2 × 1,5-10 BK ²⁾	3201534	Black																									
		16	AI-TWIN 2 × 1,5-12 BK	3200991	Black																									
	2 × 2.5 mm²	14	AI-TWIN 2 × 2,5-10 GY	3240669	Gray																									
		14	AI-TWIN 2 × 2,5-10 BU	3200836	Blue																									
17		AI-TWIN 2 × 2,5-13 BU	3200878	Blue																										
2 × 4 mm²	17	AI-TWIN 2 × 4-12 GY	3201000	Gray																										
2 × 6 mm²	19	AI-TWIN 2 × 6-14 YE	3201013	Yellow																										
2 × 10 mm²	19	AI-TWIN 2 × 10-14 RD	3201026	Red																										
2 × 16 mm²	21	AI-TWIN 2 × 16-16 BU	3202847	Blue																										
Ferrule strips	0.5 mm²	11	AI 0,5-8 WH S1	1200104	White																									
	0.75 mm²	11	AI 0,75-8 GY S1	1200105	Gray																									
		11	AI 0,75-8 BU S1	1200163	Blue																									
	1.0 mm²	11	AI 1,0-8 RD S1	1200106	Red																									
	1.5 mm²	11	AI 1,5-8 BK S1	1200107	Black																									
	2.5 mm²	11	AI 2,5-8 BU S1	1200108	Blue																									
	11	AI 2,5-8 GY S1	1200164	Gray																										

²⁾ These ferrules are not UL certified