



FLASH PLUSCON

April 2011

M12 Outdoor

Sensor/actuator cables, sensor boxes and connectors for use in outdoor applications.



Phoenix Contact's M12 Outdoor product portfolio brings industrial connection technology into a new field of use. This new line of M12 cables, boxes, and connectors reliably fulfills all the requirements for outdoor use in both signal and Category 5e Ethernet applications.

Product Features:

- 4-position M12
- Stainless steel thread/coupling nut
- Resistant to UV, ozone, and corrosion
- Rated for extreme temperatures -40 to 105C
- IP65/IP67/IP69K



Order Details:

Order Number	Type	Description	
1454040	SAC-4P-M12MS/ 2,0-28X OD	Sensor/actuator cable, 4-position, male straight M12, on free end, PE-X, halogen-free black, cable 2 m	
1454053	SAC-4P-M12MS/ 5,0-28X OD	Sensor/actuator cable, 4-position, male straight M12, on free end, PE-X, halogen-free Black, cable 5 m	
1454066	SAC-4P-M12MS/10,0-28X OD	Sensor/actuator cable, 4-position, male straight M12, on free end, PE-X, halogen-free black, cable 10 m	
1454079	SAC-4P- 2,0-28X/M12FS OD	Sensor/actuator cable, M12, 4-position, female straight with open end, A-coded, PE-X halogen-free, black, cable 2 m	
1454082	SAC-4P- 5,0-28X/M12FS OD	Sensor/actuator cable, M12, 4-position, female straight with open end, A-coded, PE-X halogen-free, black, cable 5 m	
1454095	SAC-4P-10,0-28X/M12FS OD	Sensor/actuator cable, M12, 4-position, female straight with open end, A-coded, PE-X halogen-free, black, cable 10 m	



FLASH PLUSCON

1454105	SAC-4P-M12MS/2,0-28X/M12FS OD	Sensor/actuator cable, M12, 4-position, male straight on female straight, A-coded, PE-X halogen-free, black, cable 2 m	
1454118	SAC-4P-M12MS/5,0-28X/M12FS OD	Sensor/actuator cable, M12, 4-position, male straight on female straight, A-coded, PE-X halogen-free, black, cable 5 m	
1454121	SAC-4P-M12MS/ 2,0-28X SH OD	Sensor/actuator cable, M12, 4-position, male straight with open end, A-coded, PE-X halogen-free, black, shielded cable 2 m	
1454134	SAC-4P-M12MS/ 5,0-28X SH OD	Sensor/actuator cable, M12, 4-position, male straight with open end, A-coded, PE-X halogen-free, black, shielded cable 5 m	
1454147	SAC-4P-M12MS/10,0-28X SH OD	Sensor/actuator cable, M12, 4-position, male straight with open end, A-coded, PE-X halogen-free, black, shielded cable 10 m	
1454150	SAC-4P- 2,0-28X/M12FS SH OD	Sensor/actuator cable, M12, 4-position, female straight with open end, A-coded, PE-X halogen-free, Black, shielded cable 2 m	
1454163	SAC-4P- 5,0-28X/M12FS SH OD	Sensor/actuator cable, M12, 4-position, female straight with open end, A-coded, PE-X halogen-free, black, shielded cable 5 m	
1454176	SAC-4P-10,0-28X/M12FS SH OD	Sensor/actuator cable, M12, 4-position, female straight with open end, A-coded, PE-X halogen-free, black, shielded cable 10 m	
1454189	SAC-4P-M12MS/2,0-28X/M12FSSHOD	Sensor/actuator cable, M12, 4-position, male straight on female straight, A-coded, PE-X halogen-free, black, shielded cable 2 m	
1454192	SAC-4P-M12MS/5,0-28X/M12FSSHOD	Sensor/actuator cable, M12, 4-position, male straight on female straight, A-coded, PE-X halogen-free, black, shielded cable 5 m	
1454202	VS-M12MSD/ 2,0-93X OD	Data cable, M12, D-coded, 4-pos., male straight plug with open end, halogen-free, black, shielded cable 2 m	



FLASH PLUSCON

1454215	VS-M12MSD/ 5,0-93X OD	Data cable, M12, D-coded, 4-pos., male straight plug with open end, halogen-free, black, shielded cable 5 m	
1454228	VS-M12MSD/10,0-93X OD	Data cable, M12, D-coded, 4-pos., male straight plug with open end, halogen-free, black, shielded cable 10 m	
1454231	VS-M12MSD/2,0-93X/M12MSDOD	Data cable, M12, D-coded, 4-pos., male straight plug on male straight plug, halogen-free, black, shielded cable 2 m	
1454244	VS-M12MSD/5,0-93X/M12MSDOD	Data cable, M12, D-coded, 4-pos., male straight plug on male straight plug, halogen-free, black, shielded cable 5 m	
1440753	SACC-M12MS-4QO-0,34-VA	Sensor/actuator connector, male straight, 4-pos., M12, A-coded, Quickon-One, high-grade steel knurl, 4-6 mm cable od	
1440766	SACC-M12FS-4QO-0,34-VA	Sensor/actuator connector, Female straight, 4-pos., M12, A-coded, Quickon-One, high-grade steel knurl, 4-6 mm cable od	
1440779	SACC-M12MS-4QO-0,75-VA	Sensor/actuator connector, Male straight, 4-pos., M12, A-coded, Quickon-One, high-grade steel knurl, 6-8 mm cable od	
1440782	SACC-M12FS-4QO-0,75-VA	Sensor/actuator connector, Female straight, 4-pos., M12, A-coded, Quickon-One, high-grade steel knurl, 6-8 mm cable od	
1457364	SACB-8/16- 5,0PUR OD	Sensor/actuator box, M12 Speedcon, 8 female slots, 5 pos., double occupied, master cable 180-degree exit, 5 m	
1457377	SACB-8/16-10,0PUR OD	Sensor/actuator box, M12 Speedcon, 8 female slots, 5 pos., double occupied, master cable 180-degree exit, 10 m	
1457380	SACB-8/16-C OD	Sensor/actuator box, M12 Speedcon, 8 female slots, 5 pos., double occupied, master cable connection with pluggable screw terminals 180-degree cable exit	