

Product APPLICATION Guide

Stack Light- Light Only



KEY FEATURES

- 1 to 5 Stacks Available
- State-of-the-Art Brilliant LED's
- Low Current Draw
- 24 Vac/dc
- Pole or Direct Mount Options
- UL & cUL Approved; NEMA 12; IP-52

SPECIFICATIONS:

Stack Light Shape: Triangle

Lens Color: Opaque White

LED Colors: Red; Yellow; Green;
Blue; White

LED Current: < 60 mA max per Stack

Case Material: ABS FR15U (UL94-5VA)

Operating Temp: -25 to 60 °C

Storage Temp.: -25 to 60 °C

CUL File No.: NKCR8.E478987

UL File No.: NKCR2.E478987

Operating Voltage: 24 Vac/dc (20 to 28 Volts)

Termination: 22 AWG Wires- 48 in

Pole Mount Option: 12" Stainless Pole & Bracket

Direct Mount Option: ½" NPT Pipe & Nut

Stack Light- Light Only

Part Number	# of Stacks	Colors	Operating Voltage	Mount Type	Size (in)
1 Stack- Red or Green					
JT028-R-CS	1	R	20-28 Vac/dc	Pole	2.7 x 2.7 x 15.2
JT028-R-CD	1	R	20-28 Vac/dc	Direct	2.7 x 2.7 x 3
JT028-G-CS	1	G	20-28 Vac/dc	Pole	2.7 x 2.7 x 15.2
JT028-G-CD	1	G	20-28 Vac/dc	Direct	2.7 x 2.7 x 3
2 Stacks- Red/Green or Red/Yellow or Yellow/Green					
JT028-RG-CS	2	RG	20-28 Vac/dc	Pole	2.7 x 2.7 x 16.7
JT028-RG-CD	2	RG	20-28 Vac/dc	Direct	2.7 x 2.7 x 4.5
JT028-RY-CS	2	RY	20-28 Vac/dc	Pole	2.7 x 2.7 x 16.7
JT028-RY-CD	2	RY	20-28 Vac/dc	Direct	2.7 x 2.7 x 4.5
JT028-YG-CS	2	YG	20-28 Vac/dc	Pole	2.7 x 2.7 x 16.7
JT028-YG-CD	2	YG	20-28 Vac/dc	Direct	2.7 x 2.7 x 4.5
3 Stacks- Red/Yellow/Green					
JT028-RYG-CS	3	RYG	20-28 Vac/dc	Pole	2.7 x 2.7 x 18.2
JT028-RYG-CD	3	RYG	20-28 Vac/dc	Direct	2.7 x 2.7 x 6
4 Stacks- Red/Yellow/Green/Blue					
JT028-RYGB-CS	4	RYGB	20-28 Vac/dc	Pole	2.7 x 2.7 x 19.6
JT028-RYGB-CD	4	RYGB	20-28 Vac/dc	Direct	2.7 x 2.7 x 7.5
5 Stacks- Red/Yellow/Green/Blue/Clear					
JT028-RYGBC-CS	5	RYGBC	20-28 Vac/dc	Pole	2.7 x 2.7 x 21.1
JT028-RYGBC-CD	5	RYGBC	20-28 Vac/dc	Direct	2.7 x 2.7 x 9

Note: R = Red; Y = Yellow/Amber; G = Green; B = Blue; C = Clear/White

Part Number Structure

JT 028 - RYGB - C D

Series: **JT** = Triangle Shaped Stack Light

Maximum Voltage:

028 = 20 – 28 Vac/dc

Stack Colors:

R = Red; **Y** = Yellow/Amber; **G** = Green; **B** = Blue; **C** = Clear/White

Light Function: **C** = Continuous On

Mounting Type: **D** = Direct; **S** = Stainless Pole

Call 317-612-1000 or Visit www.mallory-sonalert.com for More Details