

INDUSTRIAL PRODUCT DATASHEET

Single Ended COB LED Strip - White(6500K) 110mm(5PCS)

Ultra-flexible 6500K COB LED strip with single-ended power and cut-to-fit design for precise decorative lighting.

SKU


100036812

UPDATED


2026-07-08 08:37:31

PRICE

\$5.50(Excl. VAT)



Overview




This ultra-flexible 1mm COB LED strip emits a 360° cool white light at 6500K with CRI >80, providing accurate color rendering and a continuous linear aesthetic. Its single-ended power design and cut-to-fit capability simplify installation in tight spaces, ideal for 3D print lighting, holiday decor, mini neon signs, and model detailing.

Key Features

- **1mm Ultra-Flexible & 360° Cool White:** Crafted from Flexible FPC and Silicone Phosphor, this 1mm filament delivers a 360° full-angle glow. It emits a crisp 6500K Cool White light with CRI >80, providing accurate color rendering and continuous linear aesthetic—far superior to traditional rigid LEDs.
- **Single-Ended Power & Cut-to-Fit Design:** Innovative single-ended wiring (Anode and Cathode on the same side) eliminates the need for wiring at the tail end, drastically simplifying installation in tight spaces. If 110mm is too long, simply trim it from the non-wired end to fit various scale models, wearables, or creative decoration projects perfectly.
- **3V 200mA Spec & PWM Compatibility:** Rated at 3V 200mA, this filament provides high brightness with efficient power usage. It matches perfectly with the **COB LED Driver Board for Seeed Studio XIAO** and supports PWM control, allowing for safe and smooth dynamic effects like breathing or fading.
- **DIY Connection Kit Included:** The pack includes pre-tinned red and black electronic wires (10cm). Designed for makers, users can solder the connections themselves, enjoying the flexibility to build custom light paths from scratch.

Product Gallery



Specification

Parameter	Description
Length	~110 mm
Width	~1.0 mm
Cuttability	Yes (Cut from the tail end)
Color Temperature	6500K (Cool White)
Luminous Flux (Brightness)	>23 lm (@ 200mA)
Operating Voltage	2.8V-3.2V (Current Limiting Required)
Operating Current	<200mA (Recommended)
Power Consumption	~0.3W
Beam Angle	360°
CRI	>80
Material	Flexible FPC + Silicone Phosphor
Connector Type	Single Ended
Operating Temp	-30°C ~ +55°C

Applications

- **3D Print Lighting:** Embed inside models for cool glowing effects.
- **Christmas & Holiday Decor:** Add festive glow to tree ornaments, wreaths, or gift boxes.
- **Mini Neon Signs:** Bend into shapes for unique desktop decor.
- **Model Detailing:** Upgrade robots and figures with precision lighting details

Part List

Single Ended COB LED Strip - White(6500K) 110mm	x5
100mm Red Connecting Wire	x5
100mm Black Connecting Wire	x5

Compliance & Logistics

HSCODE	9405429000
USHSCODE	8541410000
UPC	
EUHSCODE	9405413910
COO	CHINA

Resource Links

- <https://www.seeedstudio.com/Single-Ended-COB-LED-Strip-White-6500K-110mm-5PCS-p-6590.html>

Seeed Technology Co.,Ltd.

9F, Building G3, International E City,
Zhongshanyuan Road, Nanshan, Shenzhen, China

Tel: +86 0755-80695676

Web: www.seeed.cc

Shop: www.seeedstudio.com