

CKT. SIZE	DIM. A		DIM. B REF.	
	(MM)	INCH	(MM)	INCH
4	(5.08)	0.200	(2.54)	0.100
6	(7.62)	0.300	(5.08)	0.200
8	(10.16)	0.400	(7.62)	0.300
10	(12.70)	0.500	(10.16)	0.400
12	(15.24)	0.600	(12.70)	0.500
14	(17.78)	0.700	(15.24)	0.600
16	(20.32)	0.800	(17.78)	0.700
18	(22.86)	0.900	(20.32)	0.800
20	(25.40)	1.000	(22.86)	0.900
22	(27.94)	1.100	(25.40)	1.000
24	(30.48)	1.200	(27.94)	1.100
26	(33.02)	1.300	(30.48)	1.200
28	(35.56)	1.400	(33.02)	1.300
30	(38.10)	1.500	(35.56)	1.400
32	(40.64)	1.600	(38.10)	1.500
34	(43.18)	1.700	(40.64)	1.600
36	(45.72)	1.800	(43.18)	1.700
38	(48.26)	1.900	(45.72)	1.800
40	(50.80)	2.000	(48.26)	1.900
42	(53.34)	2.100	(50.80)	2.000
44	(55.88)	2.200	(53.34)	2.100
46	(58.42)	2.300	(55.88)	2.200
48	(60.96)	2.400	(58.42)	2.300
50	(63.50)	2.500	(60.96)	2.400
52	(66.04)	2.600	(63.50)	2.500
54	(68.58)	2.700	(66.04)	2.600
56	(71.12)	2.800	(68.58)	2.700
58	(73.66)	2.900	(71.12)	2.800
60	(76.20)	3.000	(73.66)	2.900
62	(78.74)	3.100	(76.20)	3.000
64	(81.28)	3.200	(78.74)	3.100
66	(83.82)	3.300	(81.28)	3.200
68	(86.36)	3.400	(83.82)	3.300
70	(88.90)	3.500	(86.36)	3.400
72	(91.44)	3.600	(88.90)	3.500
74	(93.98)	3.700	(91.44)	3.600
76	(96.52)	3.800	(93.98)	3.700
78	(99.06)	3.900	(96.52)	3.800
80	(101.60)	4.000	(99.06)	3.900
82	(104.14)	4.100	(101.60)	4.000
84	(106.68)	4.200	(104.14)	4.100
86	(109.22)	4.300	(106.68)	4.200
88	(111.76)	4.400	(109.22)	4.300
90	(114.30)	4.500	(111.76)	4.400
92	(116.84)	4.600	(114.30)	4.500
94	(119.38)	4.700	(116.84)	4.600
96	(121.92)	4.800	(119.38)	4.700
98	(124.46)	4.900	(121.92)	4.800
100	(127.00)	5.000	(124.46)	4.900

NOTES:

1. MATERIAL:

PIN: COPPER ALLOY

WAFER: GLASS FILLED LCP (LIQUID CRYSTAL POLYMER, UL 94V-0, COLOR: BLACK.
2. FINISH:



TIN = (0.00380)/.000150 MINIMUM TIN PLATE
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE.

15 GOLD = (0.00038)/.000015 MINIMUM GOLD PLATE IN SELECT AREA,
(0.00190)/.000075 MINIMUM TIN PLATE IN SELECT AREA,
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE OVERALL.

30 GOLD = (0.00076)/.000030 MINIMUM GOLD PLATE IN SELECT AREA,
(0.00190)/.000075 MINIMUM TIN PLATE IN SELECT AREA,
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE OVERALL.

GT15 = (0.00038)/.000015 MINIMUM GOLD PLATE IN SELECT AREA,
(0.00254)/.000100 MINIMUM TIN PLATE IN SELECT AREA,
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE OVERALL.

* THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD PLATING.



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
MM/IN		4:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 742602 DRWN: SUAIFR 2023/02/28 CHK'D: SUAIFR 2023/03/16 APPR: MRAMAKRISHNA 2023/03/20 SALES ASSY-HIGH TEMP. DUAL ROW WAFER W/BREAK- OFF OPT. .025 SQ PINS											
		MM	INCH												
4 PLACES	±		±												
3 PLACES	±		± 0.005												
2 PLACES	±	0.13	± 0.01												
1 PLACE	±	0.25	±	INITIAL REVISION: DRWN: SMR 04/19/1993 APPR: SMR 04/19/1993				PRODUCT CUSTOMER DRAWING							
0 PLACES	±		±					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION			
ANGULAR TOL ± 0.5 °								SDA-70280-0001-4000		PSD	001	H1			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE		70280		SEE TABLE		GENERAL MARKET		1 OF 9	

12		11		10		9		8		7		6		5		4		3		2		1				
ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010						MATING END PLATING		P.C BOARD END PLATING		FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)				
																		TYPE	D MEAS.		TYPE			F MEAS.		
-0001/-0040		R.F.M.						(2.72) .107				(11.10) .437		(6.10) .240						TIN	(2.54) .100		TIN	(1.27) .050		
-0001/-0080		R.F.M.						(2.72) .107				(11.10) .437		(6.10) .240						15 GOLD	(2.54) .100		TIN	(1.27) .050		
-0081/-0120		R.F.M.						(2.72) .107				(11.10) .437		(6.10) .240						30 GOLD	(2.54) .100		TIN	(1.27) .050		
-0121/-0160		R.F.M.						(2.79) .110				(13.21) .520		(8.13) .320						TIN	(4.57) .180		TIN	(1.27) .050		
-0161/-0200		R.F.M.						(2.79) .110				(13.21) .520		(8.13) .320						15 GOLD	(4.57) .180		TIN	(1.27) .050		
-0201/-0240		R.F.M.						(2.79) .110				(13.21) .520		(8.13) .320						30 GOLD	(4.57) .180		TIN	(1.27) .050		
-0241/-0280		R.F.M.						(3.94) .155				(12.32) .485		(6.10) .240						30 GOLD	(2.54) .100		TIN	(1.27) .050		
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS			
	N.A.	AX-70280-0001	N.A.	AX-70280-0041	N.A.	AX-70280-0081	N.A.	AX-70280-0121	N.A.	AX-70280-0161	N.A.	AX-70280-0201	N.A.	AX-70280-0241												
4	010-89-7041	A-70280-0002	010-89-7042	A-70280-0042	010-89-7040	A-70280-0082	010-97-7045	A-70280-0122	010-97-7046	A-70280-0162	010-89-7043	A-70280-0202	010-87-9045	A-70280-0242	4											
6	010-89-7061	A-70280-0003	010-89-7062	A-70280-0043	010-89-7060	A-70280-0083	010-97-7065	A-70280-0123	010-97-7066	A-70280-0163	010-89-7063	A-70280-0203	010-87-9065	A-70280-0243	6											
8	010-89-7081	A-70280-0004	010-89-7082	A-70280-0044	010-89-7080	A-70280-0084	010-97-7085	A-70280-0124	010-97-7086	A-70280-0164	010-89-7083	A-70280-0204	010-87-9085	A-70280-0244	8											
10	010-89-7101	A-70280-0005	010-89-7102	A-70280-0045	010-89-7100	A-70280-0085	010-97-7105	A-70280-0125	010-97-7106	A-70280-0165	010-89-7103	A-70280-0205	010-87-9105	A-70280-0245	10											
12	010-89-7121	A-70280-0006	010-89-7122	A-70280-0046	010-89-7120	A-70280-0086	010-97-7125	A-70280-0126	010-97-7126	A-70280-0166	010-89-7123	A-70280-0206	010-87-9125	A-70280-0246	12											
14	010-89-7141	A-70280-0007	010-89-7142	A-70280-0047	010-89-7140	A-70280-0087	010-97-7145	A-70280-0127	010-97-7146	A-70280-0167	010-89-7143	A-70280-0207	010-87-9145	A-70280-0247	14											
16	010-89-7161	A-70280-0008	010-89-7162	A-70280-0048	010-89-7160	A-70280-0088	010-97-7165	A-70280-0128	010-97-7166	A-70280-0168	010-89-7163	A-70280-0208	010-87-9165	A-70280-0248	16											
18	010-89-7181	A-70280-0009	010-89-7182	A-70280-0049	010-89-7180	A-70280-0089	010-97-7185	A-70280-0129	010-97-7186	A-70280-0169	010-89-7183	A-70280-0209	010-87-9185	A-70280-0249	18											
20	010-89-7201	A-70280-0010	010-89-7202	A-70280-0050	010-89-7200	A-70280-0090	010-97-7205	A-70280-0130	010-97-7206	A-70280-0170	010-89-7203	A-70280-0210	010-87-9205	A-70280-0250	20											
22	010-89-7221	A-70280-0011	010-89-7222	A-70280-0051	010-89-7220	A-70280-0091	010-97-7225	A-70280-0131	010-97-7226	A-70280-0171	010-89-7223	A-70280-0211	010-87-9225	A-70280-0251	22											
24	010-89-7241	A-70280-0012	010-89-7242	A-70280-0052	010-89-7240	A-70280-0092	010-97-7245	A-70280-0132	010-97-7246	A-70280-0172	010-89-7243	A-70280-0212	010-87-9245	A-70280-0252	24											
26	010-89-7261	A-70280-0013	010-89-7262	A-70280-0053	010-89-7260	A-70280-0093	010-97-7265	A-70280-0133	010-97-7266	A-70280-0173	010-89-7263	A-70280-0213	010-87-9265	A-70280-0253	26											
28	010-89-7281	A-70280-0014	010-89-7282	A-70280-0054	010-89-7280	A-70280-0094	010-97-7285	A-70280-0134	010-97-7286	A-70280-0174	010-89-7283	A-70280-0214	010-87-9285	A-70280-0254	28											
30	010-89-7301	A-70280-0015	010-89-7302	A-70280-0055	010-89-7300	A-70280-0095	010-97-7305	A-70280-0135	010-97-7306	A-70280-0175	010-89-7303	A-70280-0215	010-87-9305	A-70280-0255	30											
32	010-89-7321	A-70280-0016	010-89-7322	A-70280-0056	010-89-7320	A-70280-0096	010-97-7325	A-70280-0136	010-97-7326	A-70280-0176	010-89-7323	A-70280-0216	010-87-9325	A-70280-0256	32											
34	010-89-7341	A-70280-0017	010-89-7342	A-70280-0057	010-89-7340	A-70280-0097	010-97-7345	A-70280-0137	010-97-7346	A-70280-0177	010-89-7343	A-70280-0217	010-87-9345	A-70280-0257	34											
36	010-89-7361	A-70280-0018	010-89-7362	A-70280-0058	010-89-7360	A-70280-0098	010-97-7365	A-70280-0138	010-97-7366	A-70280-0178	010-89-7363	A-70280-0218	010-87-9365	A-70280-0258	36											
38	010-89-7381	A-70280-0019	010-89-7382	A-70280-0059	010-89-7380	A-70280-0099	010-97-7385	A-70280-0139	010-97-7386	A-70280-0179	010-89-7383	A-70280-0219	010-87-9385	A-70280-0259	38											
40	010-89-7401	A-70280-0020	010-89-7402	A-70280-0060	010-89-7400	A-70280-0100	010-97-7405	A-70280-0140	010-97-7406	A-70280-0180	010-89-7403	A-70280-0220	010-87-9405	A-70280-0260	40											
42	010-89-7421	A-70280-0021	010-89-7422	A-70280-0061	010-89-7420	A-70280-0101	010-97-7425	A-70280-0141	010-97-7426	A-70280-0181	010-89-7423	A-70280-0221	010-87-9425	A-70280-0261	42											
44	010-89-7441	A-70280-0022	01																							

H	12		11		10		9		8		7		6		5		4		3		2		1						
	ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010						MATING END PLATING			P.C BOARD END PLATING			FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)				
																			TYPE	D MEAS.		TYPE	F MEAS.						
-0281/-0320		R.F.M.						(2.92) .115				(12.83) .505		(7.62) .300						TIN	(4.57) .180		TIN	(1.27) .050		PK-70873-0090			
-0361/-0399		R.F.M.						(3.68) .145				(17.02) .670		(11.05) .435						TIN	(6.46) .254		TIN	(1.23) .048		PK-70873-0276			
-0549/-0588		R.F.M.						(2.72) .107				(11.10) .437		(6.10) .240						TIN	(2.54) .100		TIN	(1.27) .050		PK-70873-0090			
-0589/-0628		R.F.M.						(4.45) .175				(12.83) .505		(6.10) .240						TIN	(2.54) .100		TIN	(1.27) .050					
CKTS		EDP NUMBER		ENG NUMBER		EDP NUMBER		ENG NUMBER		EDP NUMBER		ENG NUMBER		EDP NUMBER		ENG NUMBER		EDP NUMBER		ENG NUMBER		EDP NUMBER		ENG NUMBER		CKTS			
		N.A		AX-70280-0281												N/A		A-70280-0549		N/A		A-70280-0589							
4		010-97-7047		A-70280-0282						70280-0361		A-70280-0361						70280-0550		A-70280-0550		70280-0590		A-70280-0590				4	
6		010-97-7067		A-70280-0283						70280-0362		A-70280-0362						70280-0551		A-70280-0551		70280-0591		A-70280-0591				6	
8		010-97-7087		A-70280-0284						70280-0363		A-70280-0363						70280-0552		A-70280-0552		70280-0592		A-70280-0592				8	
10		010-97-7107		A-70280-0285						70280-0364		A-70280-0364						70280-0553		A-70280-0553		70280-0593		A-70280-0593				10	
12		010-97-7127		A-70280-0286						70280-0365		A-70280-0365						70280-0554		A-70280-0554		70280-0594		A-70280-0594				12	
14		010-97-7147		A-70280-0287						70280-0366		A-70280-0366						70280-0555		A-70280-0555		70280-0595		A-70280-0595				14	
16		010-97-7167		A-70280-0288						70280-0367		A-70280-0367						70280-0556		A-70280-0556		70280-0596		A-70280-0596				16	
18		010-97-7187		A-70280-0289						70280-0368		A-70280-0368						70280-0557		A-70280-0557		70280-0597		A-70280-0597				18	
20		010-97-7207		A-70280-0290						70280-0369		A-70280-0369						70280-0558		A-70280-0558		70280-0598		A-70280-0598				20	
22		010-97-7227		A-70280-0291						70280-0370		A-70280-0370						70280-0559		A-70280-0559		70280-0599		A-70280-0599				22	
24		010-97-7247		A-70280-0292						70280-0371		A-70280-0371						70280-0560		A-70280-0560		70280-0600		A-70280-0600				24	
26		010-97-7267		A-70280-0293						70280-0372		A-70280-0372						70280-0561		A-70280-0561		70280-0601		A-70280-0601				26	
28		010-97-7287		A-70280-0294						70280-0373		A-70280-0373						70280-0562		A-70280-0562		70280-0602		A-70280-0602				28	
30		010-97-7307		A-70280-0295						70280-0374		A-70280-0374						70280-0563		A-70280-0563		70280-0603		A-70280-0603				30	
32		010-97-7327		A-70280-0296						70280-0375		A-70280-0375						70280-0564		A-70280-0564		70280-0604		A-70280-0604				32	
34		010-97-7347		A-70280-0297						70280-0376		A-70280-0376						70280-0565		A-70280-0565		70280-0605		A-70280-0605				34	
36		010-97-7367		A-70280-0298						70280-0377		A-70280-0377						70280-0566		A-70280-0566		70280-0606		A-70280-0606				36	
38		010-97-7387		A-70280-0299						70280-0378		A-70280-0378						70280-0567		A-70280-0567		70280-0607		A-70280-0607				38	
40		010-97-7407		A-70280-0300						70280-0379		A-70280-0379						70280-0568		A-70280-0568		70280-0608		A-70280-0608				40	
42		010-97-7427		A-70280-0301						70280-0380		A-70280-0380						70280-0569		A-70280-0569		70280-0609		A-70280-0609				42	
44		010-97-7447		A-70280-0302						70280-0381		A-70280-0381						70280-0570		A-70280-0570		70280-0610		A-70280-0610				44	
46		010-97-7467		A-70280-0303						70280-0382		A-70280-0382						70280-0571		A-70280-0571		70280-0611		A-70280-0611				46	
48		010-97-7487		A-70280-0304						70280-0383		A-70280-0383						70280-0572		A-70280-0572		70280-0612		A-70280-0612				48	
50		010-97-7507		A-70280-0305						70280-0384		A-70280-0384						70280-0573		A-70280-0573		70280-0613		A-70280-0613				50	
52		010-97-7527		A-70280-0306						70280-0385		A-70280-0385						70280-0574		A-70280-0574		70280-0614		A-70280-0614				52	
54		010-97-7547		A-70280-0307						70280-0386		A-70280-0386						70280-0575		A-70280-0575		70280-0615		A-70280-0615				54	
56		010-97-7567		A-70280-0308						70280-0387		A-70280-0387						70280-0576		A-70280-0576		70280-0616		A-70280-0616				56	
58		010-97-7587		A-70280-0309						70280-0388		A-70280-0388						70280-0577		A-70280-0577		70280-0617		A-70280-0617				58	
60		010-97-7607		A-70280-0310						70280-0389		A-70280-0389						70280-0578		A-70280-0578		70280-0618		A-70280-0618				60	
62		010-97-7627		A-70280-0311						70280-0390		A-70280-0390						70280-0579		A-70280-0579		70280-0619		A-70280-0619				62	
64		010-97-7647		A-70280-0312						70280-0391		A-70280-0391						70280-0580		A-70280-0580		70280-0620		A-70280-0620				64	
66		010-97-7667		A-70280-0313						70280-0392		A-70280-0392						70280-0581		A-70280-0581		70280-0621		A-70280-0621				66	
68		010-97-7687		A-70280-0314						70280-0393		A-70280-0393						70280-0582		A-70280-0582		70280-0622		A-70280-0622				68	
70		010-97-7707		A-70280-0315						70280-0394		A-70280-0394						70280-0583		A-70280-0583		70280-0623		A-70280-0623				70	
72		010-97-7727		A-70280-0316						70280-0395		A-70280-0395						70280-0584		A-70280-0584		70280-0624		A-70280-0624				72	
74		010-97-7747		A-70280-0317						70280-0396		A-70280-0396						70280-0585		A-70280-0585		70280-0625		A-70280-0625				74	
76		010-97-7767		A-70280-0318						70280-0397		A-70280-0397						70280-0586		A-70280-0586		70280-0626		A-70280-0626				76	
78		010-97-7787		A-70280-0319						70280-0398		A-70280-0398						70280-0587		A-70280-0587		70280-0627		A-70280-0627				78	
80		010-97-7807		A-70280-0320						70280-0399		A-70280-0399						70280-0588		A-70280-0588		70280-0628		A-70280-0628				80	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																													
DIMENSION UNITS: MM/IN SCALE: 1:1 CURRENT REV DESC:																													
GENERAL TOLERANCES (UNLESS SPECIFIED)																													
4 PLACES ± MM INCH																													
3 PLACES ± 0.005																													
2 PLACES ± 0.13 ± 0.01																													
1 PLACE ± 0.25 ±																													
0 PLACES ±																													
ANGULAR TOL ± 0.5 °																													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																													
THIRD ANGLE PROJECTION																													
DRAWING C-SIZE																													
SERIES 70280																													
MATERIAL NUMBER SEE TABLE																													
CUSTOMER GENERAL MARKET																													
SHEET NUMBER 3 OF 9																													
DOCUMENT STATUS P1 RELEASE DATE 2023/03/20 10:44:28																													
12 11 10 9 8 7 6 5 4 3 2 1																													

12		11		10		9		8		7		6		5		4		3		2		1		
ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010						MATING END PLATING		P.C BOARD END PLATING			FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)	
																		TYPE	D MEAS.		TYPE	F MEAS.		
-0629/-0668		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240						15 GOLD	(2.54) .100		TIN	(1.27) .050		
-0669/-0708		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240						30 GOLD	(2.54) .100		TIN	(1.27) .050		
-0709/-0748		R.F.M.						(4.70) .185		(15.11) .595		(8.13) .320						TIN	(4.57) .180		TIN	(1.27) .050		
-0749/-0788		R.F.M.						(4.70) .185		(15.11) .595		(8.13) .320						15 GOLD	(4.57) .180		TIN	(1.27) .050		
-0789/-0828		R.F.M.						(4.70) .185		(15.11) .595		(8.13) .320						30 GOLD	(4.57) .180		TIN	(1.27) .050		
-0829/-0868		R.F.M.						(5.08) .200		(13.21) .520		(5.84) .230						TIN	(2.54) .100		TIN	(1.27) .050		
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	CKTS
	N/A	A-70280-0629	N/A	A-70280-0669	N/A	A-70280-0709	N/A	A-70280-0749	N/A	A-70280-0789	N/A	A-70280-0829												
4	70280-0630	A-70280-0630	70280-0670	A-70280-0670	70280-0710	A-70280-0710	70280-0750	A-70280-0750	70280-0790	A-70280-0790	70280-0830	A-70280-0830											4	
6	70280-0631	A-70280-0631	70280-0671	A-70280-0671	70280-0711	A-70280-0711	70280-0751	A-70280-0751	70280-0791	A-70280-0791	70280-0831	A-70280-0831											6	
8	70280-0632	A-70280-0632	70280-0672	A-70280-0672	70280-0712	A-70280-0712	70280-0752	A-70280-0752	70280-0792	A-70280-0792	70280-0832	A-70280-0832											8	
10	70280-0633	A-70280-0633	70280-0673	A-70280-0673	70280-0713	A-70280-0713	70280-0753	A-70280-0753	70280-0793	A-70280-0793	70280-0833	A-70280-0833											10	
12	70280-0634	A-70280-0634	70280-0674	A-70280-0674	70280-0714	A-70280-0714	70280-0754	A-70280-0754	70280-0794	A-70280-0794	70280-0834	A-70280-0834											12	
14	70280-0635	A-70280-0635	70280-0675	A-70280-0675	70280-0715	A-70280-0715	70280-0755	A-70280-0755	70280-0795	A-70280-0795	70280-0835	A-70280-0835											14	
16	70280-0636	A-70280-0636	70280-0676	A-70280-0676	70280-0716	A-70280-0716	70280-0756	A-70280-0756	70280-0796	A-70280-0796	70280-0836	A-70280-0836											16	
18	70280-0637	A-70280-0637	70280-0677	A-70280-0677	70280-0717	A-70280-0717	70280-0757	A-70280-0757	70280-0797	A-70280-0797	70280-0837	A-70280-0837											18	
20	70280-0638	A-70280-0638	70280-0678	A-70280-0678	70280-0718	A-70280-0718	70280-0758	A-70280-0758	70280-0798	A-70280-0798	70280-0838	A-70280-0838											20	
22	70280-0639	A-70280-0639	70280-0679	A-70280-0679	70280-0719	A-70280-0719	70280-0759	A-70280-0759	70280-0799	A-70280-0799	70280-0839	A-70280-0839											22	
24	70280-0640	A-70280-0640	70280-0680	A-70280-0680	70280-0720	A-70280-0720	70280-0760	A-70280-0760	70280-0800	A-70280-0800	70280-0840	A-70280-0840											24	
26	70280-0641	A-70280-0641	70280-0681	A-70280-0681	70280-0721	A-70280-0721	70280-0761	A-70280-0761	70280-0801	A-70280-0801	70280-0841	A-70280-0841											26	
28	70280-0642	A-70280-0642	70280-0682	A-70280-0682	70280-0722	A-70280-0722	70280-0762	A-70280-0762	70280-0802	A-70280-0802	70280-0842	A-70280-0842											28	
30	70280-0643	A-70280-0643	70280-0683	A-70280-0683	70280-0723	A-70280-0723	70280-0763	A-70280-0763	70280-0803	A-70280-0803	70280-0843	A-70280-0843											30	
32	70280-0644	A-70280-0644	70280-0684	A-70280-0684	70280-0724	A-70280-0724	70280-0764	A-70280-0764	70280-0804	A-70280-0804	70280-0844	A-70280-0844											32	
34	70280-0645	A-70280-0645	70280-0685	A-70280-0685	70280-0725	A-70280-0725	70280-0765	A-70280-0765	70280-0805	A-70280-0805	70280-0845	A-70280-0845											34	
36	70280-0646	A-70280-0646	70280-0686	A-70280-0686	70280-0726	A-70280-0726	70280-0766	A-70280-0766	70280-0806	A-70280-0806	70280-0846	A-70280-0846											36	
38	70280-0647	A-70280-0647	70280-0687	A-70280-0687	70280-0727	A-70280-0727	70280-0767	A-70280-0767	70280-0807	A-70280-0807	70280-0847	A-70280-0847											38	
40	70280-0648	A-70280-0648	70280-0688	A-70280-0688	70280-0728	A-70280-0728	70280-0768	A-70280-0768	70280-0808	A-70280-0808	70280-0848	A-70280-0848											40	
42	70280-0649	A-70280-0649	70280-0689	A-70280-0689	70280-0729	A-70280-0729	70280-0769	A-70280-0769	70280-0809	A-70280-0809	70280-0849	A-70280-0849											42	
44	70280-0650	A-70280-0650	70280-0690	A-70280-0690	70280-0730	A-70280-0730	70280-0770	A-70280-0770	70280-0810	A-70280-0810	70280-0850	A-70280-0850											44	
46	70280-0651	A-70280-0651	70280-0691	A-70280-0691	70280-0731	A-70280-0731	70280-0771	A-70280-0771	70280-0811	A-70280-0811	70280-0851	A-70280-0851											46	
48	70280-0652	A-70280-0652	70280-0692	A-70280-0692	70280-0732	A-70280-0732	70280-0772	A-70280-0772	70280-0812	A-70280-0812	70280-0852	A-70280-0852											48	
50	70280-0653	A-70280-0653	70280-0693	A-70280-0693	70280-0733	A-70280-0733	70280-0773	A-70280-0773	70280-0813	A-70280-0813	70280-0853	A-70280-0853											50	
52	70280-0654	A-70280-0654	70280-0694	A-70280-0694	70280-0734	A-70280-0734	70280-0774	A-70280-0774	70280-0814	A-70280-0814	70280-0854	A-70280-0854											52	
54	70280-0655	A-70280-0655	70280-06																					

12		11		10		9		8		7		6		5		4		3		2		1	
ENGINEERING NUMBER A-70280-	RELEASE FOR MANUFACTURE			E REF.		J REF.	C (0.25) ±.010			MATING END PLATING			P.C BOARD END PLATING			FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)							
										TYPE	D MEAS.		TYPE	F MEAS.									
-0439/-0448	R.F.M.			(2.72) .107		(11.10) .437	(6.10) .240			TIN	(2.54) .100		TIN	(1.27) .050									
-0449/-0458	R.F.M.			(2.72) .107		(11.10) .437	(6.10) .240			15 GOLD	(2.54) .100		TIN	(1.27) .050									
-0459/-0468	R.F.M.			(2.72) .107		(11.10) .437	(6.10) .240			30 GOLD	(2.54) .100		TIN	(1.23) .048									
-0469/-0478	R.F.M.			(2.79) .110		(13.21) .520	(8.13) .320			TIN	(4.57) .180		TIN	(1.27) .050									
-0479/-0488	R.F.M.			(2.79) .110		(13.21) .520	(8.13) .320			15 GOLD	(4.57) .180		TIN	(1.27) .050									
-0489/-0498	R.F.M.			(2.79) .110		(13.21) .520	(8.13) .320			30 GOLD	(4.57) .180		TIN	(1.27) .050									
-0499/-0508	R.F.M.			(3.94) .155		(12.32) .485	(6.10) .240			30 GOLD	(2.54) .100		TIN	(1.27) .050									

CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS
82	70280-0439	A-70280-0439	70280-0449	A-70280-0449	70280-0459	A-70280-0459	70280-0469	A-70280-0469	70280-0479	A-70280-0479	70280-0489	A-70280-0489	70280-0499	A-70280-0499	82
84	70280-0440	A-70280-0440	70280-0450	A-70280-0450	70280-0460	A-70280-0460	70280-0470	A-70280-0470	70280-0480	A-70280-0480	70280-0490	A-70280-0490	70280-0500	A-70280-0500	84
86	70280-0441	A-70280-0441	70280-0451	A-70280-0451	70280-0461	A-70280-0461	70280-0471	A-70280-0471	70280-0481	A-70280-0481	70280-0491	A-70280-0491	70280-0501	A-70280-0501	86
88	70280-0442	A-70280-0442	70280-0452	A-70280-0452	70280-0462	A-70280-0462	70280-0472	A-70280-0472	70280-0482	A-70280-0482	70280-0492	A-70280-0492	70280-0502	A-70280-0502	88
90	70280-0443	A-70280-0443	70280-0453	A-70280-0453	70280-0463	A-70280-0463	70280-0473	A-70280-0473	70280-0483	A-70280-0483	70280-0493	A-70280-0493	70280-0503	A-70280-0503	90
92	70280-0444	A-70280-0444	70280-0454	A-70280-0454	70280-0464	A-70280-0464	70280-0474	A-70280-0474	70280-0484	A-70280-0484	70280-0494	A-70280-0494	70280-0504	A-70280-0504	92
94	70280-0445	A-70280-0445	70280-0455	A-70280-0455	70280-0465	A-70280-0465	70280-0475	A-70280-0475	70280-0485	A-70280-0485	70280-0495	A-70280-0495	70280-0505	A-70280-0505	94
96	70280-0446	A-70280-0446	70280-0456	A-70280-0456	70280-0466	A-70280-0466	70280-0476	A-70280-0476	70280-0486	A-70280-0486	70280-0496	A-70280-0496	70280-0506	A-70280-0506	96
98	70280-0447	A-70280-0447	70280-0457	A-70280-0457	70280-0467	A-70280-0467	70280-0477	A-70280-0477	70280-0487	A-70280-0487	70280-0497	A-70280-0497	70280-0507	A-70280-0507	98
100	70280-0448	A-70280-0448	70280-0458	A-70280-0458	70280-0468	A-70280-0468	70280-0478	A-70280-0478	70280-0488	A-70280-0488	70280-0498	A-70280-0498	70280-0508	A-70280-0508	100

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

MM/IN

SCALE

1:1

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

CURRENT REV DESC:

EC NO: 742602

DRWN: SUAIFR

CHK'D: SUAIFR

APPR: MRAMAKRISHNA

2023/02/28

2023/03/16

2023/03/20

SALES ASSY-HIGH TEMP.
DUAL ROW WAFER W/BREAK- OFF OPT. .025 SQ
PINS

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SDA-70280-0001-4000

DOC TYPE

PSD

DOC PART

001

REVISION

H1

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

5 OF 9

DOCUMENT STATUS

P1

RELEASE DATE

2023/03/20

10:44:28

12

11

10

9

8

7

6

5

4

3

2

1

FORMATT: Eng-High-master-16-print-C
REVISION: D
DATE: 2018/01/18

[illegible]

12		11		10		9		8		7		6		5		4		3		2		1	
ENGINEERING NUMBER A-70280-	RELEASE FOR MANUFACTURE			E REF.		J REF.	C (0.25) ±.010			MATING END PLATING			P.C BOARD END PLATING			FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)							
										TYPE	D MEAS.		TYPE	F MEAS.									
-0899/-0908	R.F.M.			(4.45) .175		(12.83) .505	(6.10) .240			30 GOLD	(2.54) .100		TIN	(1.27) .050									
-0909/-0918	R.F.M.			(4.70) .185		(15.11) .595	(8.13) .320			TIN	(4.57) .180		TIN	(1.27) .050									
-0919/-0928	R.F.M.			(4.70) .185		(15.11) .595	(8.13) .320			15 GOLD	(4.57) .180		TIN	(1.27) .050									
-0929/-0938	R.F.M.			(4.70) .185		(15.11) .595	(8.13) .320			30 GOLD	(4.57) .180		TIN	(1.27) .050									
-0939/-0948	R.F.M.			(5.08) .200		(13.21) .520	(5.84) .230			TIN	(2.54) .100		TIN	(1.27) .050									

CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS
82	70280-0899	A-70280-0899	70280-0909	A-70280-0909	70280-0919	A-70280-0919	70280-0929	A-70280-0929	70280-0939	A-70280-0939					82
84	70280-0900	A-70280-0900	70280-0910	A-70280-0910	70280-0920	A-70280-0920	70280-0930	A-70280-0930	70280-0940	A-70280-0940					84
86	70280-0901	A-70280-0901	70280-0911	A-70280-0911	70280-0921	A-70280-0921	70280-0931	A-70280-0931	70280-0941	A-70280-0941					86
88	70280-0902	A-70280-0902	70280-0912	A-70280-0912	70280-0922	A-70280-0922	70280-0932	A-70280-0932	70280-0942	A-70280-0942					88
90	70280-0903	A-70280-0903	70280-0913	A-70280-0913	70280-0923	A-70280-0923	70280-0933	A-70280-0933	70280-0943	A-70280-0943					90
92	70280-0904	A-70280-0904	70280-0914	A-70280-0914	70280-0924	A-70280-0924	70280-0934	A-70280-0934	70280-0944	A-70280-0944					92
94	70280-0905	A-70280-0905	70280-0915	A-70280-0915	70280-0925	A-70280-0925	70280-0935	A-70280-0935	70280-0945	A-70280-0945					94
96	70280-0906	A-70280-0906	70280-0916	A-70280-0916	70280-0926	A-70280-0926	70280-0936	A-70280-0936	70280-0946	A-70280-0946					96
98	70280-0907	A-70280-0907	70280-0917	A-70280-0917	70280-0927	A-70280-0927	70280-0937	A-70280-0937	70280-0947	A-70280-0947					98
100	70280-0908	A-70280-0908	70280-0918	A-70280-0918	70280-0928	A-70280-0928	70280-0938	A-70280-0938	70280-0948	A-70280-0948					100

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

MM/IN

SCALE

1:1

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

CURRENT REV DESC:

EC NO: 742602

DRWN: SUAIFR

CHK'D: SUAIFR

APPR: MRAMAKRISHNA

2023/02/28

2023/03/16

2023/03/20

SALES ASSY-HIGH TEMP.
DUAL ROW WAFER W/BREAK- OFF OPT. .025 SQ
PINS

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SDA-70280-0001-4000

DOC TYPE

PSD

DOC PART

001

REVISION

H1

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

7 OF 9

DOCUMENT STATUS

P1

RELEASE DATE

2023/03/20

10:44:28

12

11

10

9

8

7

6

5

4

3

2

1

FORMATT: Eng-High-master-to-print-C

REVISION: D

DATE: 2018/01/18

12

11

10

9

8

7

6

5

4

3

2

1

12	11	10	9	8	7	6	5	4	3	2	1				
ENGINEERING NUMBER A-70280-	RELEASE FOR MANUFACTURE			E REF.		J REF.	C (0.25) ±.010			MATING END PLATING		P.C BOARD END PLATING		FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)	
									TYPE	D MEAS.		TYPE	F MEAS.		
		-1247 / -1285	R.F.M		(3.68) .145		(17.02) .670	(11.05) .435			TIN	(6.46) 2.54			TIN
1286	R.F.M.			(3.56) .140		(15.24) .600	(9.40) .370			TIN	(5.33) .210		TIN	(2.54) .100	

G																
---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	ITEM NUMBER	ITEM NUMBER	ITEM NUMBER	CKTS
4								4
6								6
8								8
10								10
12								12
14								14
16								16
18	70280-1254	A-70280-1254						18
20								20
22								22
24								24
26			70280-1286	A-70280-1286				26
28								28
30								30
32								32
34								34
36								36
38								38
40								40
42								42
44								44
46								46
48								48
50								50
52								52
54								54
56								56
58								58
60								60
62								62
64								64
66								66
68								68
70								70
72								72
74								74
76								76
78								78
80								80

H1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex					
MM/IN		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)															
	MM	INCH		EC NO: 742602 DRWN: SUAIFR 2023/02/28 CHK'D: SUAIFR 2023/03/16 APPR: MRAMAKRISHNA 2023/03/20						SALES ASSY-HIGH TEMP. DUAL ROW WAFER W/BREAK- OFF OPT. .025 SQ PINS					
4 PLACES	±	±													
3 PLACES	±	± 0.005													
2 PLACES	± 0.13	± 0.01													
1 PLACE	± 0.25	±													
0 PLACES	±	±		INITIAL REVISION: DRWN: SMR 04/19/1993 APPR: SMR 04/19/1993						DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION
ANGULAR TOL ± 0.5 °										SDA-70280-0001-4000			PSD	001	H1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
						C-SIZE	70280	SEE TABLE		GENERAL MARKET		9 OF 9			
DOCUMENT STATUS	P1	RELEASE DATE	2023/03/20 10:44:28												