


1. SPECIFICATION

APD-903-PP

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	3	 Square wave 1/2 duty.
02	Operating Voltage	V	1 ~ 25	
03	Consumption Current	mA (Max)	1	
04	Sound pressure level (Distance at 10cm)	dB(A) (Min)	65	Rated voltage, rated frequency.
05	Capacitance	pF	12000±30%	At 120Hz
06	Rated Frequency	Hz	4000	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RECOMMENDED PCB LAYOUT

RoHS

TITLE: SMD PIEZO BUZZER		DRAWN: Zack	2018/03/05	SCALE: 2:1	SHEET: 1 of 1
PART NO. APD-903-PP		DESIGNED: R&D OF AAT		UNITS: mm	
DWG NO. UGPT09A4003P		CHECKED:		TOLERANCE ± 0.5	
		APPROVAL:		UNLESS OTHERWISE SPECIFIED:	
		MATERIAL: LCP		ONE PLACE DECIMAL $\pm$ ***	
				TWO PLACE DECIMAL $\pm$ ***	
				THREE PLACE DECIMAL $\pm$ ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC