

Han TC400_CT_SMC_F_CRT_150mm²_Ag



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6677
Specification	Han TC400_CT_SMC_F_CRT_150mm²_Ag
HARTING eCatalogue	https://harting.com/09110006677

Identification

Category	Contacts
Series	TC 400
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts
Details	The vibration and shock resistance can only be met if the cables are fixed at an appropriate distance. Instructions for the spacing of strain relief can be found in the document in eCatalogue under the section Instructions.

Technical characteristics

Conductor cross-section (mm²)	150 mm²
Rated current	≤400 A
Contact resistance	≤0.3 mΩ
Stripping length	22.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Vibration resistance	Category 2 acc. to IEC 61373
Shock resistance	Category 2 acc. to IEC 61373

Material properties

Material (contacts)	Copper alloy
---------------------	--------------



Pushing Performance
Since 1945

Material properties

Surface (contacts)	Silver plated
--------------------	---------------

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85359000
GTIN	5713141118286
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522