



Pushing Performance  
Since 1945

# Han-Mod\_M\_Carrier\_C.2\_Short




Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 97 00 000 0428                                                                |
| Specification      | Han-Mod_M_Carrier_C.2_Short                                                   |
| HARTING eCatalogue | <a href="https://harting.com/97000000428">https://harting.com/97000000428</a> |

## Identification

|                           |                            |
|---------------------------|----------------------------|
| Category                  | Modules                    |
| Series                    | Han-Modular®               |
| Type of module            | Han® Carrier Cube          |
| Size of the module        | Domino module              |
| Description of the module | Short version<br>Large Tab |

## Version

|         |                                |
|---------|--------------------------------|
| Details | Insulated to the hinged frame. |
|---------|--------------------------------|

## Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -40 ... +85 °C |
|----------------------|----------------|

## Material properties

|                                           |                        |
|-------------------------------------------|------------------------|
| Material (insert)                         | Polycarbonate (PC)     |
| Colour (insert)                           | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | V-0                    |
| RoHS                                      | compliant              |
| ELV status                                | compliant              |
| China RoHS                                | e                      |
| REACH Annex XVII substances               | Not contained          |
| REACH ANNEX XIV substances                | Not contained          |
| REACH SVHC substances                     | Not contained          |



**Pushing Performance**  
Since 1945

**Material properties**

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| California Proposition 65 substances | Not contained                       |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels   | R22 (HL 1-3)<br>R23 (HL 1-3)        |

**Specifications and approvals**

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
|----------------|--------------------------|

**Commercial data**

|                                |                                                           |
|--------------------------------|-----------------------------------------------------------|
| Packaging size                 | 2                                                         |
| Country of origin              | Romania                                                   |
| European customs tariff number | 85389099                                                  |
| eCl@ss                         | 27440217 Module for industrial connectors (power/signals) |