


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A2	NEW RELEASE	23/AUG./2022	
A3	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A4	Add length 2.82FT	17/APR/2025	
A5	INCREASE 2.5FT/50FT LENGTH	13/JAN/2026	

LENGTH±T



CABLE PRINTING: Amphenol Cables on Demand E119932 AWM 21118 80°C 30V COPARTNER



P/N CHART

ACD P/N	LENGTH±T	
CS-DSLSZH9MM0-002.5	2.5FT±1inch	762±25mm
CS-DSLSZH9MM0-002.82	2.82FT±1inch	860±25mm
CS-DSLSZH9MM0-005	5FT±2inch	1524±51mm
CS-DSLSZH9MM0-006.5	6.5FT±2inch	1981±51mm
CS-DSLSZH9MM0-010	10FT±3inch	3048±76mm
CS-DSLSZH9MM0-015	15FT±3inch	4572±76mm
CS-DSLSZH9MM0-025	25FT±4inch	7620±102mm
CS-DSLSZH9MM0-050	50FT±8inch	15240±203mm

- NOTE:
- TESTING CONDITIONS:
A: INSULATION RESISTANCE: 10MΩ
B: VOLTAGE: DC300V/0.01S
C: CONDUCTOR RESISTANCE 2Ω(<3M), 5Ω(>3M,<10M), 8M≥10Ω
 - SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT	
P1	P2
1	1 BLACK
2	2 BROWN
3	3 RED
4	4 ORANGE
5	5 YELLOW
6	6 GREEN
7	7 BLUE
8	8 PURPLE
9	9 GREY
SHELL	SHELL DRAIN



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	ANGLES	APPROVALS	DATE		
X ±X ±X°		DRAWN XF		CABLE, 9PIN D-SUB M/M LS0H XFT	
.XX ±XX		CHECKED HYJ			
.XXX ±XXX		RESP ENG			
THIRD ANGLE PROJECTION		MFG ENG		SIZE A	REV. A5
CAD FILE		DWG. NO. CS-DSLSZH9MM0-XXX		SHEET 1 OF 1	

NOTES: UNLESS OTHERWISE SPECIFIED