


Cable Length(L):01~99Meters



Conn.
Pin Assignments
Front View

8	Brown	16AWG	棕
7	Green/Yellow	16AWG	綠 / 黃
6	Blue	16AWG	藍
5	Red	24AWG	紅
4	Green	24AWG	綠
3	White	24AWG	白
2	Blue	24AWG	藍
1	Drain		地線
Conn.	Wire Color		
	Pin Out		

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, UL94V-0, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2586 (24#*1P+A)*2C+16#*3C+Drain+Al/Mylar,
PVC Jacket, UV Resistant, OD=Ø10.0mm, Black
- * Cable Length Tolerance: 01M±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm

TOLERANCE

± 0.5 mm



TITLE			
O CERES, D-20A+2A, 08P, CABLE W/SR M, M PWR+F SIG, MOLDING, 2LOCK 			
SCALE	1:1	SIZE	A4
		SHEET	1 OF 1
REV.	C	MC-REV.	B.2
QC: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
DCU-08AMEM-LL7BXX	Rita	2024-05-28
CUSTOMER	APPROVED BY	DATE
ALTW	Fred	2024-05-28