


Data Sheet

15.04.2026

Fiber Optic Trunk Cable DB02-0089



CONNECTOR SIDE A		CONNECTOR SIDE B
LC/UPC Multimode UNIBOOT WITH TAB	CONNECTOR DESCRIPTION	LC/UPC Multimode UNIBOOT WITH TAB
IEC 61754-20, JIS C 5964-20, Telecordia GR 326 CORE	DESIGN SPECIFICATION	IEC 61754-20, JIS C 5964-20, Telecordia GR 326 CORE
Seikoh Giken	MANUFACTURER	Seikoh Giken
Ø1.25mm, ceramics, axial suspended	FERRULE	Ø1.25mm, ceramics, axial suspended
-40°C to +75°C	OPERATION TEMPERATURE	-40°C to +75°C
Plastic / Heather Violet	MATERIAL OF FERRULE	Plastic / Heather Violet
500	PLUG CYCLES	500
≤ 0.20dB	TYPICAL INSERTION LOSS (IL)	≤ 0.20dB
White	BEND PROTECTION	White
12-times Dividing elements M25	DIVIDING ELEMENT	12-times Dividing elements M25
0.60m	WHIP	0.60m

CABLE			
CABLE TYPE	U-DQ(ZN)BH	MANUFACTURER	WEINERT
NUMBER OF FIBERS	24	FIBER CLASS	OM4 BI
OUTER DIAMETER	7.5mm	CABLE COLOR	Heather Violet
CLOAK MATERIAL	FRNC	PULL STRENGTH	1750N
CABLE WEIGHT	60kg/km	OPERATION TEMPERATURE	-20°C to +60°C
CPR CLASSIFICATION	CPR Dca		