



SIMATIC DP, ET 200ECO PN, voltage distributor PD 24 V DC; 1x 7/8", 4xM12, Degree of protection IP67

Power loss			
Power loss, typ.		3.5 W	
Potential separation			
between the load voltages		Yes	
Isolation			
tested with			
• 24 V DC circuits		500 V	
• Test voltage for interface, rms value [Vrms]		1 500 V; According to IEEE 802.3	
Dimensions			
Width		45 mm	
Height		175 mm	
Depth		49 mm	
Weights			
Weight, approx.		590 g	
Classifications			
		Version	Classification
	eClass	16	27-24-26-92
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
Approvals / Certificates			
General Product Approval			

[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval	EMV	For use in hazardous locations	Maritime application
--------------------------	-----	--------------------------------	----------------------



[China RoHS](#)



[CCS \(China Classification Society\)](#)

Maritime application

[KR \(Korean Register of Shipping\)](#)

last modified: 4/7/2025