

MODLIGHT50/70 MAGNET BASE WITH M12 8-POLE

Side cable entry

Art.No.: 4000-75070-0000921

Weight: 0.381 kg

Country of origin: DE

Model designation: Modlight50/70-Magnetfuß M12

Magnet base

with M12 flange plug connector (8-pole)

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-75070-0000921
GTIN	4048879031080
EU-Customs tariff number	85319000
US-Customs tariff number	8531909001
ECLASS-6.0	27371235
ECLASS-6.1	27371235
ECLASS-7.0	27371235
ECLASS-7.1	27371235
ECLASS-8.0	27371235
ECLASS-8.1	27371235
ECLASS-9.0	27371235
ECLASS-9.1	27371235
ECLASS-10.0.1	27371235
ECLASS-10.1	27371235
ECLASS-11.0	27371235
ECLASS-11.1	27371235
ECLASS-12.0	27371235
ECLASS-13.0	27371235
ECLASS-14.0	27371235
ETIM-5.0	EC001154
ETIM-6.0	EC001154
ETIM-7.0	EC001154
ETIM-8.0	EC001154
ETIM-9.0	EC001154

ETIM-10.0	EC001154
customs tariff number	85319000
EAN	4048879031080
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
housing	Aluminum
Color housing	black
Mechanical data Mounting data	
Height	35 mm
Width	70 mm
Depth	70 mm
Connection type 2-2	
Family construction form	M12
No. of poles	5
Coding	A
Gender	male
PIN 1	n.c.
PIN 2	n.c.
PIN 3	0 V DC
PIN 4	24 V DC
PIN 5	FE
Family construction form	M12
No. of poles	8
Coding	A
Gender	male