





APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 3 FOR REVISION				



With CAP



Mating Application— Mezzanine



Mating Application— Daughter Card to Motherboard

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

MM	.X	± 0.35	ANGLE	± 2°
	.XX	± 0.20		
	.XXX	± 0.10		

DRAWN

WY

9/3/26

CHECKED

RC

9/3/26

APPROVED

CONFIDENTIAL AND PROPRIETARY

© Adam Tech. All rights reserved. This document contains confidential and proprietary information belonging to Adam Tech. It is provided solely for design and reference purposes by authorized parties. Any reproduction, distribution, display, or disclosure to third parties, in whole or in part, without the prior written consent of Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright, trademark, trade secret, and all other intellectual property rights worldwide.

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE

POWER 2.54mm SIGNAL 1.27mm BOARD TO BOARD
HYBRID CONNECTOR, MALE, STRAIGHT, SMT TYPE

SIZE
X

PART NO.

ESMC24-XX-20A2

REV.
-

REF:

S00242T

SCALE: NTS

SHEET 2 OF 3

APPROVED: _____

DATE: _____ TITLE: _____




Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 3 FOR REVISION				

@ PACKING LIST

ADAM TECH P/N	PCS (REEL)	REEL (OUTSIDE CTN)	PCS (OUTSIDE CTN)	DIM H +0.2/-0	CTN SIZE
ESMC24-10-20A2	450	5	2250	32.40	350*350*260
ESMC24-20-20A2		4	1800	44.40	
ESMC24-32-20A2		3	1350	56.40	
ESMC24-44-20A2		5	2250	72.40	350*350*460

@ DIM. TABLE

ADAM TECH P/N	DIM B ±0.15	DIM E ±0.10	DIM F ±0.10	DIM W +0.30/-0.10
ESMC24-10-20A2	16.9	28.40	14.20	32.00
ESMC24-20-20A2	27.1	40.40	20.20	44.00
ESMC24-32-20A2	38.5	52.40	26.20	56.00
ESMC24-44-20A2	49.9	68.40	34.20	72.00



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

MM	.X ± 0.35	ANGLE ± 2°
	.XX ± 0.20	
	.XXX ± 0.10	

DRAWN WY 9/3/26

CHECKED RC 9/3/26

APPROVED

CONFIDENTIAL AND PROPRIETARY
© Adam Tech. All rights reserved. This document contains confidential and proprietary information belonging to Adam Tech. It is provided solely for design and reference purposes by authorized parties. Any reproduction, distribution, display, or disclosure to third parties, in whole or in part, without the prior written consent of Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright, trademark, trade secret, and all other intellectual property rights worldwide.

ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE
POWER 2.54mm SIGNAL 1.27mm BOARD TO BOARD
HYBRID CONNECTOR, MALE, STRAIGHT, SMT TYPE

SIZE X PART NO. ESMC24-XX-20A2 REV. -

REF: S00242T SCALE: NTS SHEET 3 OF 3