





APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 3 FOR REVISION				



With CAP



Mating Application- Mezzanine



Mating Application- Daughter Card to Motherboard

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

MM	.X	± 0.35	ANGLE	± 2°
	.XX	± 0.20		
	.XXX	± 0.10		

DRAWN WY 9/3/26

CHECKED RC 9/3/26

APPROVED

CONFIDENTIAL AND PROPRIETARY
© Adam Tech. All rights reserved. This document contains confidential and proprietary information belonging to Adam Tech. It is provided solely for design and reference purposes by authorized parties. Any reproduction, distribution, display, or disclosure to third parties, in whole or in part, without the prior written consent of Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright, trademark, trade secret, and all other intellectual property rights worldwide.

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE
**POWER 2.54mm SIGNAL 1.27mm BOARD TO BOARD
HYBRID CONN, MALE, STRAIGHT, DIP/SMT TYPE**

SIZE	PART NO.	REV.
X	ESMC24D-XX-20C2	-

REF: S00242T SCALE: NTS SHEET 2 OF 3

APPROVED: _____

DATE: _____ TITLE: _____




Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 3 FOR REVISION				

@ PACKING LIST

ADAM TECH P/N	PCS (REEL)	REEL (OUTSIDE CTN)	PCS (OUTSIDE CTN)	DIM H +0.2/-0	CTN SIZE
ESMC24D-10-20C2	350	5	1750	32.40	350*350*260
ESMC24D-20-20C2		4	1400	44.40	
ESMC24D-32-20C2		3	1050	56.40	
ESMC24D-44-20C2		5	1750	72.40	

@ DIM. TABLE

ADAM TECH P/N	DIM B ±0.15	DIM E ±0.10	DIM F ±0.10	DIM W +0.30/-0.10
ESMC24D-10-20C2	16.9	28.40	14.20	32.00
ESMC24D-20-20C2	27.1	40.40	20.20	44.00
ESMC24D-32-20C2	38.5	52.40	26.20	56.00
ESMC24D-44-20C2	49.9	68.40	34.20	72.00



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED			ADAM TECH	909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 adam-tech.com	
MM	.X ± 0.35 .XX ± 0.20 .XXX ± 0.10	ANGLE ± 2°			
DRAWN	WY	9/3/26			
CHECKED	RC	9/3/26	TITLE		
APPROVED			POWER 2.54mm SIGNAL 1.27mm BOARD TO BOARD HYBRID CONN, MALE, STRAIGHT, DIP/SMT TYPE		
CONFIDENTIAL AND PROPRIETARY © Adam Tech. All rights reserved. This document contains confidential and proprietary information belonging to Adam Tech. It is provided solely for design and reference purposes by authorized parties. Any reproduction, distribution, display, or disclosure to third parties, in whole or in part, without the prior written consent of Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright, trademark, trade secret, and all other intellectual property rights worldwide.			SIZE X	PART NO. ESMC24D-XX-20C2	REV. -
			REF: S00242T	SCALE: NTS	SHEET 3 OF 3