


Ferrule; black



Similar to illustration

Strip length	13.5 ... 14.5 mm / 0.53 ... 0.57 inches
Metric cross-section of the twin ferrule	2 x 1,5 mm ²
Cross-section (AWG) of twin ferrule	2 x 16 AWG

Total length (L)	20 mm
Wall thickness of crimp sleeve (W2)	0.15 mm
Wall thickness (plastic collar W1)	0.3 mm
Inner dimension of small plastic collar (D1)	3.6 mm
Inner dimension plastic collar large (D)	6.5 mm
Crimp length (length of sleeve L1)	12 mm
Diameter crimp sleeve inside (D2)	2.35 mm

Plastic collar	Standard collar
----------------	-----------------

Color	black
Weight	0.2 g




Commercial data	
PU (SPU)	500 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143323826
Customs tariff number	85369010000

Product Classification	
UNSPSC	39121405
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable