




Color: ■ blue

Connection Data		
Strip length		13.5 ... 14.5 mm / 0.53 ... 0.57 inches
Metric cross-section of the twin ferrule		2 x 2,5 mm ²
Cross-section (AWG) of twin ferrule		2 x 14 AWG

Physical data		
Total length (L)		21 mm
Wall thickness of crimp sleeve (W2)		0.2 mm
Wall thickness (plastic collar W1)		0.4 mm
Inner dimension of small plastic collar (D1)		4.5 mm
Inner dimension plastic collar large (D)		8 mm
Crimp length (length of sleeve L1)		12 mm
Diameter crimp sleeve inside (D2)		2.9 mm

Mechanical data		
Plastic collar		Standard collar

Material data		
Color		blue
Weight		0 g



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454432942
Customs tariff number	85369010000

Product Classification	
UNSPSC	39121405
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 216-545

↓

Documentation			
Bid Text			
216-545	19.02.2019	xml 2.62 KB	↓
216-545	28.04.2017	doc 22.50 KB	↓


CAD/CAE-Data

CAD data

2D/3D Models 216-545

↓

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable