

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

00and01Coaxial en

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Series	00 - NIM-CAMAC

Technical details

Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	00.25 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
Contact Dia.	0.7 mm (0.028 in)

Form & Material

Shell style / Model id	APF - Adapter from LEMO plug to CINCH receptacle
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Weight	7.93 g

Environment

Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles

Drawings



Dimensions

	A	L	M
mm.	6.4	43	34.5
in.	0.25	1.69	1.36