


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	PART STATUS CHANGE TO DISCONTINUNACE	24JUN2026	NS	PS

MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M2, BRASS, NICKEL PLATED.

ELECTRICAL:
VOLTAGE RATING: 300V
CURRENT RATING: 11A
WIRE SIZE RANGE: 14-30 AWG

ENVIRONMENTAL:
OPERATING TEMP RANGE: -40°C TO +110°C



OBSOLETE	60.96	16	1-1986375-6
	57.15	15	1-1986375-5
	53.34	14	1-1986375-4
	49.53	13	1-1986375-3
	45.72	12	1-1986375-2
	41.91	11	1-1986375-1
	38.10	10	1-1986375-0
	34.29	9	1986375-9
	30.48	8	1986375-8
	26.67	7	1986375-7
	22.86	6	1986375-6
	19.05	5	1986375-5
	15.24	4	1986375-4
	11.43	3	1986375-3
	7.62	2	1986375-2
	DIM L	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 17MAR2008	TE Connectivity		
		CHK C RICHARD 3/17/08			
		APVD C RICHARD 3/17/08	NAME TERMINAL BLOCK, PLUG, VERTICAL STACKING, LEFT HAND, 3.81mm PITCH		
		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT 0.000000	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986375
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
				REV A1	