




© COPYRIGHT 1969 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓		A	REDRAWN & REVISED A-3943	4/26/78
✓	✓		B	REVISED PER A-6127	9/19/83
✓	✓		C	REV PER AF-4968	7/12/87



- 1. CONTINUOUS STRIP ON REELS
- 2. DIMENSIONS IN BRACKETS ARE IN INCHES.

METRIC

M4 #8	0.5-1.4 mm ² [20-16]	TIN	0.51 [020] BRASS	40812
STUD SIZE	WIRE RANGE	FINISH	MATERIAL	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm TOLERANCES ON: DECIMALS ±0.38 [015] ANGLES ±1°0'		CONTRACT NO		
		DR <i>S. Mogaro</i> 4/26/78		
		CHK <i>Wagner & Vetter</i> 7-25-78		
		APPD <i>R.P.F. Smith</i> 8-10-78		
MATERIAL		NAME		
SEE TABLE		RING		
FINISH		SIZE	CODE IDENT NO	DRAWING NO
SEE TABLE		B	00779	40812
		DSGN APPD	SCALE	SHEET
		OTHER APPD		