

D

C

B

A








D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED AS PER ECN-22-176158	26JUL'22	HS	SZ



- NOTE:
- MATERIAL:
HOUSING: THERMOPLASTIC, UL 94V-0 COLOR: BLACK.
CAP: LCP E130i , COLOR:BLACK.
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.25mm.
SHIELD: PHOSPHOR BRONZE, THICKNESS: 0.40mm.
 - FINISH:
CONTACT: GOLD FLASH OVER 30u" MIN. PALLADIUM-NICKEL OR ALTERNATIVE 30u" MIN. GOLD PLATING ON CONTACT AREA, 100u" MIN. MATTE-TIN PLATED ON SOLDER TAILS 50u" MIN. NICKEL UNDERPLATED ALL OVER.
SHIELD: 100u" MIN. BRIGHT TIN PLATED OVER 50u" MIN. NICKEL UNDERPLATED ALL OVER.
 - WAVE SOLDER CAPABLE TO 240°C PER TE SPEC 109-202, CONDITION A (FOR 1734753-1).

RECOMMENDED PCB LAYOUT (THICKNESS: 1.6MM)
(DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05)

SEE SHEET 3	YES	1734753-2
SEE SHEET 3	NO	1734753-1
PACKING	REFLOW CAPABLE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU CHK S. HOU APVD W.J. KE		02SEP2022 10MAR2005 10MAR2005		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MINI USB CONN., RCPT V/T, DIP, B TYPE			
		0 PLC ± - 1 PLC ± 0.25 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± 3'		PRODUCT SPEC 108-57509 APPLICATION SPEC —					
MATERIAL SEE NOTE		FINISH SEE NOTE		WEIGHT 0.789 GRAMS		SIZE A2	CAGE CODE 00779	DRAWING NO C-1734753	RESTRICTED TO —
CUSTOMER DRAWING						SCALE —	SHEET 1 of 4	REV B	

D

C

B

A



D

C

B

A


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



(A3) ADD THIS PAGE
1734753-3 AS SHOWN
THE OTHER DIMENSIONS ARE THE SAME AS SHEET1.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU	02SEP2022	 TE Connectivity						
		CHK S. HOU	10MAR2005							
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W.J. KE	10MAR2005	NAME						
	0 PLC ± - 1 PLC ± 0.25 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± 3°	PRODUCT SPEC	MINI USB CONN., RCPT V/T, DIP, B TYPE							
		108-57509								
		APPLICATION SPEC								
		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL	FINISH	WEIGHT	0.789 GRAMS	A2	00779	C-1734753	—			
SEE NOTE	SEE NOTE	CUSTOMER DRAWING			SCALE	—	SHEET	2 of 4	REV	B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 02SEP2022	TE Connectivity		
DIMENSIONS: mm		CHK S. HOU 10MAR2005			
		APVD W.J. KE 10MAR2005	NAME		
		PRODUCT SPEC 108-57509	MINI USB CONN., RCPT V/T, DIP, B TYPE		
MATERIAL SEE NOTE		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=-1734753
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT 0.789 GRAMS	RESTRICTED TO -		
FINISH SEE NOTE		CUSTOMER DRAWING		SCALE -	SHEET 3 of 4
				REV B	

