




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M3	ECR-25-239014	26APR2025	ABS	PS

13	OBSOLETE	12	2	2.40	1.198	1-104257-1	12	6-103959-1
13	OBSOLETE	12	2	2.20	1.098	1-104257-0	1 1	6-103959-0
	OBSOLETE	12	2	2.00	.998	104257-9	10	5-103959-9
	OBSOLETE	12	2	1.80	.898	104257-8	9	5-103959-8
		12	2	1.60	.798	104257-7	8	5-103959-7
13	OBSOLETE	12	2	1.40	.698	104257-6	7	5-103959-6
	OBSOLETE	12	4	2.39	.598	104257-5	6	5-103959-5
		12	4	1.99	.498	104257-4	5	5-103959-4
		12	5	1.99	.398	104257-3	4	5-103959-3
		12	8	2.40	.298	104257-2	3	5-103959-2
		12	10	2.00	.198	104257-1	2	5-103959-1
	OBSOLETE	10	5	1.99	.398	104257-3	4	1-103959-3
11	OBSOLETE	10	4	1.99	.498	104257-4	5	1-103959-2
13	OBSOLETE	9	2	2.40	1.198	1-104257-1	12	1-103959-1
13	OBSOLETE	9	2	2.20	1.098	1-104257-0	1 1	1-103959-0
	OBSOLETE	9	2	2.00	.998	104257-9	10	103959-9
13	OBSOLETE	9	2	1.80	.898	104257-8	9	103959-8
	OBSOLETE	9	2	1.60	.798	104257-7	8	103959-7
13	SUPERSEDED BY 5-103959-7	9	2	1.40	.698	104257-6	7	103959-6
	OBSOLETE	9	4	2.39	.598	104257-5	6	103959-5
	SUPERSEDED BY 5-103959-4	9	4	1.99	.498	104257-4	5	103959-4
	OBSOLETE	9	5	1.99	.398	104257-3	4	103959-3
	SUPERSEDED BY 5-103959-2	9	8	2.40	.298	104257-2	3	103959-2
	SUPERSEDED BY 5-103959-1	9	10	2.00	.198	104257-1	2	103959-1

- 1
- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS

2

3

4

5

6

7

8

9

10

11

12

13

PLATING	6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L A MAYER 11-4-86 CHK P de Jong 11-12-86 APVD P de Jong 11-12-86 PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026 WEIGHT - CUSTOMER DRAWING		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH			NAME RCPT ASSY, AMPMODU MTE, SINGLE ROW .100 C/L, LATCHED AND POLARIZED FOR #26-#30 AWG WIRE SIZE, STRIP FORM		
MATERIAL	HOUSING:	SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=103959
				SCALE 4:1	SHEET 1 OF 1	REV M3