

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

— , — , *

©

COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

1

REVISIONS

	F
--	---

LTR

DESCRIPTION

DATE _____

DWN

	APVD
--	------

	C1
--	----

Dimension	255±2 corrected to 250±5 mm.
-----------	------------------------------


23APR2015

SP

	JK
--	----

NOTES:

- 1 RANGE: Ø68 MAX.
2 MIN. TENSILE STRENGTH 220N.



OBSOLETE	500	BLACK	POLYAMIDE 6.6	3-160976-2
OBSOLETE	500	NATURAL	POLYAMIDE 6.6	3-160976-1
	100	BLACK	POLYAMIDE 6.6	2-160976-2
OBSOLETE	100	NATURAL	POLYAMIDE 6.6	2-160976-1
	QTY	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.V.D.HEIJDEN		27FEB92		 TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R.VOS		NAME									
		0 PLC ± —		APVD L.V.SOEST		CABLE TY.									
		1 PLC ± 0.4		PRODUCT SPEC											
		2 PLC ± —		—											
		3 PLC ± —		APPLICATION SPEC											
4 PLC ± —		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —		A3		00779		C-160976		—			
CUSTOMER DRAWING										SCALE NTS		SHEET 1 OF 1		REV C1	