






TYPE	L	W	C	D	t
1H (0201)	0.58±0.05	0.29±0.05	0.15±0.05	0.12±0.05	0.23±0.05
1E (0402)	1.00±0.05	0.50±0.05	0.20±0.10	0.25±0.10	0.32±0.10
1J (0603)	1.60±0.10	0.80±0.10	0.30±0.20	0.30±0.20	0.45±0.10
2A (0805)	2.00±0.15	1.25±0.15	0.40±0.25	0.30±0.20	0.55±0.10
2B (1206)	3.10±0.10	1.55±0.15	0.40±0.25	0.50±0.30	0.55±0.10
2E (1210)	3.10±0.10	2.50±0.15	0.50±0.25	0.50±0.30	0.55±0.10
2H (2010)	5.00±0.20	2.50±0.15	0.50±0.25	0.60±0.30	0.60±0.15
3A (2512)	6.35±0.20	3.10±0.15	0.55±0.25	0.60±0.30	0.60±0.10

FOR FURTHER INFORMATION SEE DATA SHEET FOR
CURRENT SENSING CHIP RESISTOR - RL73 SERIES

RoHS Compliant



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08MAR2012 DARSHAN MS	TE Connectivity		
DIMENSIONS: mm		CHK 08MAR2012 ALLAN P			
		APVD 08MAR2012 STEPHEN.P	NAME SMD LOW OHMIC CURRENT SENSE RESISTOR RL73 SERIES		
		PRODUCT SPEC -	-		
MATERIAL -		APPLICATION SPEC -	SIZE A3		
		WEIGHT -	CAGE CODE 00779		
FINISH -		DRAWING NO C-1622824			RESTRICTED TO -
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV BA