


4

3

2




1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	5	combine *-1 in this drawing	04MAY2015	I.T	W.H
	6	ECR-18-015944	08JAN2018	E.Z	W.H




1734303-2 AS SHOWING

- NOTE:
- 1.MATERIAL:PH/BR, T=0.1±0.01MM
 - 2.FINISH
GOLD FLASH PLATING ON SOLDER AREA AND CONTACT AREA
40U'' Min NICKEL UNDER PLATING OVERALL
 - ② 3.NORMAL FORCE 0.6N MINIMUM AT 2.8MM WORKING HEIGHT,
(COMPRESS 0.5MM WHEN MEASURE NORMAL FORCE)
 - 4. INSPECTION ITEMS MARKED WITH INSPECTION BUBBLE.




NORMAL FORCE CURVE



SOLDER AREA

RECOMMENDED FOOTPRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Ivan Tian 21NOV2014	TE Connectivity										
		CHK Wenke He 21NOV2014											
DIMENSIONS: mm		APVD Wenke He 21NOV2014	NAME SHIELD FINGER WITH PROTECT WALL GIANTS J95										
		PRODUCT SPEC -	SIZE A3										
		APPLICATION SPEC -							CAGE CODE 00779	DRAWING NO C-1734303			RESTRICTED TO -
		WEIGHT -											
MATERIAL -		FINISH -		CUSTOMER DRAWING				SCALE 14:1	SHEET 1	OF 4	REV 6		

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD



A-A



165°~180°
PEELING ANGLE
0.1~0.7N(300mm/min)
PEELING STRENGTH


300REF WITHOUT CHARGE
WITH PRODUCT CHARGE 2250PCS/REEL
WITHOUT CHARGE 20HOLES MIN.

2250	1734303-2
QTY/REEL	SALES P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

-

DWN 21NOV2014

Ivan Tian

CHK 21NOV2014

Wenke He

APVD 21NOV2014

Wenke He

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

SHIELD FINGER WITH PROTECT WALL
GIANTS J95

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-1734303

-

SCALE

14:1

SHEET

2

OF

4

REV

6

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD



NOTE:

1. QUANTITY
2000 PCS/REEL
12 REEL/SHIPPING BOX MAX.
2. DIMENSION:
BOX: 340 X340X224
3. GENERAL TOLERANCE: ±0.12
4. MATERIAL:
CARRIER TAPE: ACRYLIC FLIM
TOP TAPE: PET FILM
REEL: PLASTIC
5. WEIGHT:
NET WEIGHT 3.3KG
GROSS WEIGHT 4.8KG


300 REF
WEEDING THE COVER TAPE.165°~180°
PEELING ANGLE
0.1~0.7N(300mm/min)
PEELING STRENGTH

USER DIRECTION OF UNREELING

300REF
WITHOUT CHARGEWITH PRODUCT CHARGE
2000PCS/REELWITHOUT CHARGE
20HOLES MIN.

2000	1734303-1
QTY/REEL	SALES P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.12
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	SEE NOTE

DWN 21NOV2014

Ivan Tian

CHK 21NOV2014

Wenke He

APVD 21NOV2014

Wenke He

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE

TE Connectivity

NAME
SHIELD FINGER WITH PROTECT WALL
4025B-T

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-1734303

SCALE 14:1 SHEET 4 OF 4 REV 6