


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R2	PART STATUS CHANGE TO DISCONTINUNACE	26JUN2026	NS	PS

1. MATERIAL:
HOUSING: POLYAMIDE 6, UL94V-2,
COLOR OFF WHITE.
CONTACT: BRASS, TIN PLATED.
WIRE PROTECTOR: STAINLESS STEEL.
SCREW: M5, STEEL, ZINC PLATED W/ NON-
HEXAVALENT CHROMATE (CHROME III).
WIRE PROTECTOR: STAINLESS STEEL.
2. ELECTRICAL:
MAX CURRENT: 65A (UR) 70A (CSA)
OPERATING VOLTAGE: 600V PER UL FILE E60677
WIRE RANGE: 6-14 AWG (UR) 6-22 AWG (CSA)
DIELECTRIC WITHSTAND: 6000V.
3. ENVIRONMENT:
CONTINUOUS WORKING TEMP.: -35°C TO 100°C.
4. CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION
5. CUTTING BURR MAX. 1mm ALLOWED.



	145.0	170.7	12	TSB200012DS	1-1776313-2
OBSOLETE	130.5	156.2	11	TSB200011DS	1-1776313-1
	116.0	141.7	10	TSB200010DS	1-1776313-0
OBSOLETE	101.5	127.2	9	TSB200009DS	1776313-9
	87.0	112.7	8	TSB200008DS	1776313-8
OBSOLETE	72.5	98.2	7	TSB200007DS	1776313-7
	58.0	83.7	6	TSB200006DS	1776313-6
	43.5	69.2	5	TSB200005DS	1776313-5
	29.0	54.7	4	TSB200004DS	1776313-4
	14.5	40.2	3	TSB200003DS	1776313-3
	-	25.7	2	TSB200002DS	1776313-2
	-	11.2	1	TSB200001DS	1776313-1
DIM B	DIM A	NO OF POS	CATALOG NUMBER	TE PART NUMBER	

1776313-4 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 3/21/05	TE Connectivity		
		CHK C RICHARD 3/21/05			
		APVD C RICHARD 3/21/05	NAME		
		PRODUCT SPEC	14.5MM PITCH WITH WIRE PROTECTOR		
		APPLICATION SPEC			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-1776313
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 OF 1	REV R2