

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

AS SHOWN

2293269-2

A-A

60.7

18

25.1

Ø5.6

Ø2.7

Ø6.7

Ø6-0.075

3

1

2

A3

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW NOTE 5 AND NEW PN 2-2293269-3	23MAR2020	FRAN	SCH.
	A2	NEW SHEET 2 AND NEW PN 2293269-6	07MAR2023	JCP	HMF
	A3	ADD DIAMETER TO PN 2293269-6	15MAR2023	JCP	HMF
	A4	CORRECTED PN 2293269-3	14SEP2023	GL	HMF

NOTES

Bemerkungen

1

IN CASE OF DISCREPANCIES BETWEEN GERMAN AND ENGLISH TEXT THE GERMAN TEXT IS BINDING
Im Falle von Unterschieden zwischen dem deutschen und dem englischen Text ist der deutsche Text verbindlich

2

HANDLING OF PARTS ONLY WITH GLOVES
Teile dürfen nur mit Handschuhen angefasst werden

3

CROSS SECTION MARKING:
NUMBER OF GROOVES ACC. NUMBER AFTER BASIS-PN
Kennzeichnung Leitungsquerschnitt:
Anzahl Einstiche gemäß Nachstrichzahl

4

BULK PACKAGING IN PLASTIC BAG IN FOLDING CARTON AND CORRUGATED SHIPPING BOX
Schüttgut in Beutel in Faltschachtel und Versandkarton

5

PLATING MARKING: 6µm Ag
Kennzeichnung Beschichtung: 6µm Ag

1	1	1	1	FINGER PROTECTION CAP	-	2	0.06	PA66/6 FR	BLACK			
1	-	-	-	PIN CONTACT DIA 6.0, 6mm², 6µm Ag over Cu	-	1	12.23	COPPER	SILVER			
-	1	-	-	PIN CONTACT DIA 6.0, 6mm², 6µm Ag	1+3		12.38	BRASS				
-	-	1	-	PIN CONTACT DIA 6.0, 6mm²	0+3		12.75					
-	-	-	1	PIN CONTACT DIA 6.0, 4mm²	0+2							
2293269-6	2-2293269-3	2293269-3	2293269-2	DESCRIPTION	GROOVES	ITEM NO	WEIGHT (g)	MATERIAL	SURFACE/COLOR			
A	A	A	A	REVISION OF EACH ASSEMBLY								
QUANTITY PER ASSEMBLY				COMPONENT								

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:

mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:
DIN ISO 2768-mK

0 PLC

±

1 PLC

±

2 PLC

±

3 PLC

±

4 PLC

±

ANGLES

±

FINISH

-

-

DWN

30JUN2016

Vishwa A

CHK

30JUN2016

F. Wittrock

APVD

30JUN2016

F. Wittrock

PRODUCT SPEC

-

APPLICATION SPEC

114-94403

WEIGHT

-

CUSTOMER DRAWING

TE

TE Connectivity

NAME

PIN, DIA 6.0, L/N, ASSY
Rundkontakt 6mm, L/N, ZSB

-

SIZE

A3

CAGE CODE

-

DRAWING NO

©-2293269

RESTRICTED TO

-

SCALE

2:1

SHEET

1 OF 2

REV

A4

1470-19 (3/13)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


AS SHOWN
2293269-3



AS SHOWN
2-2293269-3



AS SHOWN
2293269-6



THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	DIN ISO 2768-mK
	~~0 PLC ±-~~
	~~1 PLC ±-~~
	~~2 PLC ±-~~
	~~3 PLC ±-~~
	~~4 PLC ±-~~
	~~ANGLES ±~~
MATERIAL	FINISH
-	-
-	-

DWN	Vishwa A	30JUN2016
CHK	F. Wittrock	30JUN2016
APVD	F. Wittrock	30JUN2016
PRODUCT SPEC	-	
APPLICATION SPEC	114-94403	
WEIGHT	-	
CUSTOMER DRAWING		



TE Connectivity

NAME
PIN, DIA 6.0, L/N, ASSY
Rundkontakt 6mm, L/N, ZSB
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C-2293269	-
SCALE		SHEET	REV
2:1		2 OF 2	A4