




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 28APR97	TE Connectivity	
		CHK R. SWING 28APR97		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD E. REILES 28APR97	NAME	MTA-100 POSTED CONNECTOR ASSEMBLY,CLOSED END,22 AWG,TIN
	0 PLC ± -	PRODUCT SPEC	SIZE	CAGE CODE
	1 PLC ± -	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A1 00779	647000
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 2	REV H

LOC	DIST	REVISIONS					
		#	LT#	DESCRIPTION	DATE	DWN	APVD
CM	00	-	-	SEE SHEET 1	-	-	-

1-640642-9	1-643077-9	4	2	45.72	1.800	48.95	1.927	50.80	2.000	19	4-647000-9
1-640642-8	1-643077-8	4	2	43.18	1.700	46.41	1.827	48.26	1.900	18	4-647000-8
1-640642-7	1-643077-7	4	2	40.64	1.600	43.87	1.727	45.72	1.800	17	4-647000-7
1-640642-6	1-643077-6	4	2	38.10	1.500	41.33	1.627	43.18	1.700	16	4-647000-6
1-640642-5	1-643077-5	4	2	35.56	1.400	38.79	1.527	40.64	1.600	15	4-647000-5
1-640642-4	1-643077-4	4	2	33.02	1.300	36.25	1.427	38.10	1.500	14	4-647000-4
1-640642-3	1-643077-3	4	2	30.48	1.200	33.71	1.327	35.56	1.400	13	4-647000-3
1-640642-2	1-643077-2	2	1	27.94	1.100	31.17	1.227	33.02	1.300	12	4-647000-2
1-640642-1	1-643077-1	2	1	25.40	1.000	28.63	1.127	30.48	1.200	11	4-647000-1
1-640642-0	1-643077-0	2	1	22.86	.900	26.09	1.027	27.94	1.100	10	4-647000-0
640642-9	643077-9	2	1	20.32	.800	23.55	.927	25.40	1.000	9	3-647000-9
640642-8	643077-8	2	0	17.78	.700	21.01	.827	22.86	.900	8	3-647000-8
640642-7	643077-7	0	0	15.24	.600	18.47	.727	20.32	.800	7	3-647000-7
640642-6	643077-6	0	0	12.70	.500	15.93	.627	17.78	.700	6	3-647000-6
640642-5	643077-5	0	0	10.16	.400	13.39	.527	15.24	.600	5	3-647000-5
640642-4	643077-4	0	0	7.62	.300	10.85	.427	12.70	.500	4	3-647000-4
640642-3	643077-3	0	0	5.08	.200	8.31	.327	10.16	.400	3	3-647000-3
-	643077-2	0	0	2.54	.100	5.77	.227	7.62	.300	2	3-647000-2
1-640642-9	1-643077-9	4	2	45.72	1.800	48.95	1.927	50.80	2.000	19	~~1-647000-9~~
1-640642-8	1-643077-8	4	2	43.18	1.700	46.41	1.827	48.26	1.900	18	~~1-647000-8~~
1-640642-7	1-643077-7	4	2	40.64	1.600	43.87	1.727	45.72	1.800	17	~~1-647000-7~~
1-640642-6	1-643077-6	4	2	38.10	1.500	41.33	1.627	43.18	1.700	16	1-647000-6
1-640642-5	1-643077-5	4	2	35.56	1.400	38.79	1.527	40.64	1.600	15	~~1-647000-5~~
1-640642-4	1-643077-4	4	2	33.02	1.300	36.25	1.427	38.10	1.500	14	~~1-647000-4~~
1-640642-3	1-643077-3	4	2	30.48	1.200	33.71	1.327	35.56	1.400	13	~~1-647000-3~~
1-640642-2	1-643077-2	2	1	27.94	1.100	31.17	1.227	33.02	1.300	12	1-647000-2
1-640642-1	1-643077-1	2	1	25.40	1.000	28.63	1.127	30.48	1.200	11	~~1-647000-1~~
1-640642-0	1-643077-0	2	1	22.86	.900	26.09	1.027	27.94	1.100	10	~~1-647000-0~~
640642-9	643077-9	2	1	20.32	.800	23.55	.927	25.40	1.000	9	647000-9
640642-8	643077-8	2	0	17.78	.700	21.01	.827	22.86	.900	8	647000-8
640642-7	643077-7	0	0	15.24	.600	18.47	.727	20.32	.800	7	~~647000-7~~
640642-6	643077-6	0	0	12.70	.500	15.93	.627	17.78	.700	6	647000-6
640642-5	643077-5	0	0	10.16	.400	13.39	.527	15.24	.600	5	647000-5
640642-4	643077-4	0	0	7.62	.300	10.85	.427	12.70	.500	4	647000-4
640642-3	643077-3	0	0	5.08	.200	8.31	.327	10.16	.400	3	647000-3
-	643077-2	0	0	2.54	.100	5.77	.227	7.62	.300	2	647000-2
DUST COVER	STRAIN RELIEF COVERS	QTY OF GUSSET RIBS 	QTY OF CENTRAL RAILS 	MM	IN	MM	IN	MM	IN	NO. OF CIRCUITS	PART NO
	ACCESSORIES			C		B		A			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± -
± -
± -
± -
± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

ANGLES
FINISH

± -
± -

MATERIAL

1

DWN
E. LEWIS
CHK
R. SWING
APVD
E. BEILES

28APR97
28APR97
28APR97

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

-
-
-

NAME
MTA-100 POSTED CONNECTOR ASSEMBLY,CLOSED END,22 AWG,TIN

SIZE
A1

CAGE CODE
00779

DRAWING NO
647000

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
1:1

SHEET
2

OF
2

REV
H

TE Connectivity