




P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECO-19-005751	26SEP2019	RS	SG



SECTION C-C
SCALE 12:1



SECTION D-D
SCALE 12:1

1. THIS CONTACT IS USED ON EITHER PLUG AND CAP HOUSING
- 2 0.00076mm MIN THICK GOLD-PLATED IN THE CONTACT SECTION TO 3.2mm FROM TIP END, OVER NICKEL UNDERPLATE ALL OVER
3. WIRE RANGE: 26-22 AWG,
INSULATION DIA: 1.2-1.75 mm

170361, 170362, 170365, 170366	TIN/PHOS BRONZ	170363-4	170359-4
	GOLD/BRASS 3	170363-3	170359-3
	TIN/BRASS	170363-1	170359-1
MATING P/N		FINISH/MATERIAL	LOOSE PIECE P/N
		PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.4 1 PLC ±0.4 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL SEE TABLE	FINISH SEE TABLE

DWN R. SMITH 26SEP2019	CHK S. WRIGHT 26SEP2019	APVD S. WRIGHT 26SEP2019
PRODUCT SPEC 108-5138		
APPLICATION SPEC 114-5050		
WEIGHT -		
CUSTOMER DRAWING		

NAME
MINI UNIVERSAL MATE-N-LOK
PIN CONTACT
-

SIZE A3	CAGE CODE 00779	DRAWING NO C-170359	RESTRICTED TO -
------------	--------------------	------------------------	--------------------

SCALE 4:1	SHEET 1 OF 1	REV F
--------------	-----------------	----------