




| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | D   | REVISED PER ECR-20-100603 | 02NOV2020 | PC  | SW   |

|                                                                        |             |                                                                                                                                                           |                                               |                      |                    |
|------------------------------------------------------------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|----------------------|--------------------|
| WIRE RANGE: 0.5-1.3 mm², 20-16 AWG<br>INSULATION DIA : 2.0-3.2 2.4X2mm | -           |                                                                                                                                                           | GOLD-PLATED BRASS<br>(0.252)                  |                      | 171637-3-4         |
|                                                                        | 171639-1    |                                                                                                                                                           | PRE TINNED BRASS<br>(0.252)                   |                      | 171637-1           |
|                                                                        | LOOSE PIECE |                                                                                                                                                           | FINISH-MATERIAL                               |                      | PART NUMBER        |
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                 |             | DWN<br>BASAVARAJA D A<br>05JUL2019<br>CHK<br>WRIGHT SCOTT<br>05JUL2019<br>APVD<br>WRIGHT SCOTT<br>05JUL2019<br>PRODUCT SPEC<br>-<br>APPLICATION SPEC<br>- | TE Connectivity                               |                      |                    |
| DIMENSIONS:<br>mm                                                      |             | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± 0.3<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± 1°                                  | NAME<br>SOCKET CONTACT (MINI UNIVERSAL M-N-L) |                      |                    |
| MATERIAL<br>SEE TABLE                                                  |             | FINISH<br>-                                                                                                                                               | WEIGHT<br>-                                   | SIZE<br>A2           | CAGE CODE<br>00779 |
|                                                                        |             |                                                                                                                                                           |                                               | DRAWING NO<br>171637 | RESTRICTED TO<br>- |
| CUSTOMER DRAWING                                                       |             |                                                                                                                                                           | SCALE<br>1:1                                  | SHEET<br>1 of 1      | REV<br>D           |