



Representative Image

Catalog No. 3119-50

Description: 1-1/2 INCH ARMORED CABLE CONN

UPC No 786210947716

Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 1-1/2 Inch, Knockout Size 1-1/2 Inch, Cable Range 1.812 to 2.031 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

Descriptors

Category	Flex connectors
Special Features	The Tough Lining of Insulation and The Tite-Bite Principles Make These Connectors a Must When Conductors are Subject to Conditions of Vibration or Strain.
Application	For Use with Armored Cable and Flexible Metal Conduit.

Specifications

Conductor Range	1.812 to 2.031 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

Classifications

Brand Name	T&B Cord & Cable Fittings
Standard	UL E23018

Dimensions

Size	1-1/2 Inch
------	------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E23018	N/A	DWTT	N/A	N/A