

AMY-50-S

~18° spot beam

SPECIFICATION:

Dimensions	Ø 49.9
Height	10.8 mm
Fastening	socket
ROHS compliant	yes ⓘ


MATERIALS:



Component	Type	Material	Colour	Finish	Length (mm)
AMY-50-S	Single lens	PMMA			
AMY-50-HLD2-C	Holder C	PC	black		
AMY-50-HLD2-B	Holder B	PC	black		
AMY-50-HLD2-C-WHT	Holder C	PC	white		
AMY-50-HLD2-B-WHT	Holder B	PC	white		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C17686_AMY-50-S	690	120	30	9.5
Assembly				
CP19150_AMY-50-S-B2-WHT	510	120	30	8.8
CP19141_AMY-50-S-C2-WHT	510	120	30	8.4
CP19132_AMY-50-S-B2	510	120	30	8.8
CP19123_AMY-50-S-C2	510	120	30	8.3




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED BXRV-D10-RGBW2000-A3
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 19.0° / 40.0°
Efficiency 79 %
Peak intensity 4.4 cd/lm
LEDs/each optic 28
Light colour/type RGBW
Required components:
 C19950_HEKLA-SOCKET-RZ



Light distribution files





LED V10 Gen 8-9
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 18.0° / 38.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files



LED V11 HD Gen 8
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 20.0° / 41.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
 Bender Wirth: 633d Hekla





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V13 Gen 8-9
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 28.0° / 53.0°
Efficiency 87 %
LEDs/each optic 1
Light colour/type White
Required components:
F15859_HEKLA-SOCKET-I



Light distribution files




LED V4 HD Gen 7
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 10.0° / 24.0°
Efficiency 93 %
LEDs/each optic 1
Light colour/type White
Required components:
F15253_HEKLA-SOCKET-A



Light distribution files



LED V6 HD Gen 7
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 12.0° / 28.0°
Efficiency 92 %
LEDs/each optic 1
Light colour/type White
Required components:
F15255_HEKLA-SOCKET-C




Light distribution files

OPTICAL RESULTS (MEASURED):





LED V8 Gen 8-9
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 35.0°
 Efficiency 92 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files




LED V9 HD Gen7
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 33.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files



LED VERO10
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 17.0° / 36.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15616_HEKLA-SOCKET-F





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Vesta DTW 13mm (21W)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 27.0° / 49.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 491 Typ L8



Light distribution files





LED Vesta DTW 15mm (33W)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 24.0° / 49.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 491 Typ L8



Light distribution files



LED Vesta TW 13mm (18W) DP
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 25.0° / 49.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 492 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Vesta TW 15mm DP
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 30.0° / 55.0°
 Efficiency 85 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 482 Typ L8



Light distribution files




LED Vesta TW 6mm DP
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 13.0° / 28.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 504 Typ L8



Light distribution files



LED Vesta TW 6mm DP
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 16.0° / 33.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 504 Typ B35L




Light distribution files

OPTICAL RESULTS (MEASURED):




LED Vesta TW 9mm (9W) DP
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 36.0°
 Efficiency 88 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 489 Typ L8



Light distribution files

CITIZEN



LED CLU02x (LES10)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 36.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP19141_AMY-50-S-C2-WHT
 FWHM / FWTM 19.0° / 37.0°
 Efficiency 95 %
 Peak intensity 5.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU02x (LES10)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 17.0° / 38.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Green Gems: GH27d



Light distribution files

CITIZEN



LED CLU03x
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 26.0° / 50.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 13.0° / 28.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU7A2/7A3
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 10.0° / 23.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files

CITIZEN



LED CLU7B2
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 9.0° / 22.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU7L3
Ordering code CP19132_AMY-50-S-B2
FWHM / FWTM 9.0° / 23.0°
Efficiency 93 %
LEDs/each optic 1
Light colour/type White
Required components:
Bender Wirth: 667a Bayonet35




Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU7S3
Ordering code CP19132_AMY-50-S-B2
FWHM / FWTM 10.0° / 25.0°
Efficiency 92 %
LEDs/each optic 1
Light colour/type White
Required components:
Bender Wirth: 667a Bayonet35



Light distribution files





LED CMA1516
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 17.0° / 35.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17436_HEKLA-G2-D



Light distribution files



LED CMA1825
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 23.0° / 45.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type White
Required components:
F15254_HEKLA-SOCKET-B




Light distribution files

OPTICAL RESULTS (MEASURED):





LED CMT14xx
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 18.0° / 37.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files





LED CMT19xx
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 26.0° / 51.0°
Efficiency 87 %
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I



Light distribution files



LED CMU10xx
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 18.0° / 37.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CXA/B 13xx
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 12.0° / 27.0°
Efficiency 92 %
LEDs/each optic 1
Light colour/type White
Required components:
F17439_HEKLA-G2-J



Light distribution files




LED CXA/B 15xx
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 15.0° / 34.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17436_HEKLA-G2-D



Light distribution files



LED LEDIM/C6
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 19.0° / 37.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON 7070
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 13.0° / 29.0°
 Efficiency 93 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 634a Bayonet35L



Light distribution files




LED LUXEON CoB 1202/1203
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 17.0° / 35.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files



LED LUXEON CoB 1204HD
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 17.0° / 35.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB M02/M03
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D



Light distribution files





LED LUXEON CoB S01
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 12.0° / 27.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J



Light distribution files



LED LUXEON Fusion 12-up (20x24)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 19.0° / 38.0°
 Efficiency 83 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON Fusion 21-up (20x24)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 19.0° / 38.0°
 Efficiency 81 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8



Light distribution files





LED LUXEON Fusion 27-up (20x24)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 26.0° / 48.0°
 Efficiency 80 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8



Light distribution files



LED CTM-14 (Tunable White) Gen2
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 27.0° / 50.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 442 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CTM-9 (Tunable White)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 19.0° / 41.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 495 Typ B35L



Light distribution files





LED CXM-3
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 10.0° / 22.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED CXM-4
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 10.0° / 24.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):




LED COB L-Type (LES 11)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 22.0° / 43.0°
 Efficiency 88 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files




LED COB L-Type (LES 9)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files



LED COB S-Type (LES 7)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 13.0° / 29.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H




Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo SLM C TW L06A 1313 G7N
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 13.0° / 27.0°
 Efficiency 90 %
 Peak intensity 10.9 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 508 Typ L8



Light distribution files

PHILIPS


LED Fortimo SLM C TW L09A 1919 G7N
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 36.0°
 Efficiency 89 %
 Peak intensity 6.1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 501 Typ L8



Light distribution files

PHILIPS

LED Fortimo SLM L09 CoB
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 17.0° / 35.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H




Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 17.0° / 36.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

SAMSUNG


LED LC016D / LC019D / LC026D / LC033D
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 28.0° / 55.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

SAMSUNG

LED LC030C/040C G2
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 21.0° / 42.0°
 Efficiency 88 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I





Light distribution files

OPTICAL RESULTS (MEASURED):





LED MJT COB LES 14.5
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 28.0° / 53.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files




LED MJT COB LES 6
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 12.0° / 27.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED MJT COB LES 9.8
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 37.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC



LED SLE G7 LES09
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 16.0° / 34.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type White
Required components:
F15848_HEKLA-SOCKET-G



Light distribution files

TRIDONIC



LED SLE G7 LES13
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 25.0° / 48.0°
Efficiency 87 %
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I



Light distribution files

TRIDONIC

LED SLE G7 LES15
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 27.0° / 53.0°
Efficiency 86 %
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED V10 Gen 8-9
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 17.0° / 36.0°
 Efficiency 89 %
 Peak intensity 7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


BJB: 47.360.1020

Light distribution files




LED V3 HD Gen 8
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 12.0° / 26.0°
 Efficiency 94 %
 Peak intensity 13.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A

Light distribution files



LED V3 HD Gen 8 FC
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 12.0° / 27.0°
 Efficiency 94 %
 Peak intensity 13.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C


Light distribution files



OPTICAL RESULTS (SIMULATED):




LED V4 HD Gen 7
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 10.0° / 22.0°
 Efficiency 93 %
 Peak intensity 17.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files




LED V4 HD Gen 8
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 13.0° / 28.0°
 Efficiency 94 %
 Peak intensity 12.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V6 Gen 8-9
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 93 %
 Peak intensity 10.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V6 HD Gen 8
Ordering code CP19141_AMY-50-S-C2-WHT
FWHM / FWTM 12.0° / 28.0°
Efficiency 93 %
Peak intensity 11.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F19858_HEKLA-G2B-C3



Light distribution files




LED V6 HD Gen 8
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 14.0° / 30.0°
Efficiency 93 %
Peak intensity 10.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files



LED V8 Gen7
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 16.0° / 34.0°
Efficiency 89 %
Peak intensity 8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15253_HEKLA-SOCKET-A




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V9 HD Gen 8
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 92 %
 Peak intensity 8.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files




LED Vero SE 13
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 26.0° / 44.0°
 Efficiency 81 %
 Peak intensity 3.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files



LED VERO13
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 23.0° / 47.0°
 Efficiency 91 %
 Peak intensity 4.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED Vesta DTW 6mm
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 93 %
 Peak intensity 10.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652b Hekla

Light distribution files



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 31.0°
 Efficiency 90 %
 Peak intensity 8.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652b Hekla

Light distribution files



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 35.0°
 Efficiency 85 %
 Peak intensity 6.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F18158_HEKLA-RZ-LENS




Bender Wirth: 652b Hekla

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED Vesta SE 13mm TW
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 25.0° / 45.0°
 Efficiency 82 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files




LED Vesta TW 9mm (12W) CSP
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 32.0°
 Efficiency 81 %
 Peak intensity 7.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files

CITIZEN

LED CLU02Q Type-F
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 20.0° / 43.0°
 Efficiency 91 %
 Peak intensity 5.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU02x (LES10)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 34.0°
 Efficiency 87 %
 Peak intensity 6.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

CITIZEN


LED CLU02x (LES10)
 Ordering code C17686_AMY-50-S
 FWHM / FWTM 18.1° / 32.2°
 Efficiency 90 %
 Peak intensity 7.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 18.0° / 33.0°
 Efficiency 90 %
 Peak intensity 7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1020

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU02x (LES10)
 Ordering code CP19141_AMY-50-S-C2-WHT
 FWHM / FWTM 18.0° / 36.0°
 Efficiency 96 %
 Peak intensity 6.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 12.1° / 22.1°
 Efficiency 92 %
 Peak intensity 15.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 11.0° / 22.0°
 Efficiency 91 %
 Peak intensity 15 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU700/701/702/703
 Ordering code C17686_AMY-50-S
 FWHM / FWTM 11.1° / 22.1°
 Efficiency 92 %
 Peak intensity 15.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN


LED CLU710/711
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 30.0°
 Efficiency 89 %
 Peak intensity 8.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files

CITIZEN

LED CLU710/711
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 15.1° / 30.2°
 Efficiency 91 %
 Peak intensity 8.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1010

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU712/713
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 90 %
 Peak intensity 8.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN


LED CLU713 Type-F
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 20.0° / 40.0°
 Efficiency 92 %
 Peak intensity 6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN

LED CLU723 Type-F
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 22.0° / 46.0 + 47.0°
 Efficiency 90 %
 Peak intensity 4.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN

LED CLUD22
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 90 %
 Peak intensity 10.4 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 444 Typ L8

CITIZEN


LED CLUD32
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 20.0° / 40.0°
 Efficiency 90 %
 Peak intensity 5.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files



LED CHA0304
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 10.0° / 22.0°
 Efficiency 91 %
 Peak intensity 17.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED: CHA0612
 Ordering code: CP19123_AMY-50-S-C2
 FWHM / FWTM: 12.0° / 28.0°
 Efficiency: 91 %
 Peak intensity: 11.8 cd/lm
 LEDs/each optic: 1
 Light colour/type: White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files




LED: CHA0825
 Ordering code: CP19123_AMY-50-S-C2
 FWHM / FWTM: 16.0° / 34.0°
 Efficiency: 90 %
 Peak intensity: 7.6 cd/lm
 LEDs/each optic: 1
 Light colour/type: White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED: CMA1306
 Ordering code: CP19123_AMY-50-S-C2
 FWHM / FWTM: 12.0° / 26.0°
 Efficiency: 94 %
 Peak intensity: 13.5 cd/lm
 LEDs/each optic: 1
 Light colour/type: White
 Required components:
 F15956_HEKLA-SOCKET-J



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED CMB2550
FWHM / FWTM 34.0° / 66.0°
Efficiency 77 %
Peak intensity 1.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Bender Wirth: 639a Hekla XL


Light distribution files



LED CMU10xx
Ordering code CP19132_AMY-50-S-B2
FWHM / FWTM 16.0° / 36.0°
Efficiency 89 %
Peak intensity 7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

BJB: 47.360.1020


Light distribution files



LED CMU15xx
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 26.0° / 52.0°
Efficiency 86 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

F17438_HEKLA-G2-I

Light distribution files




OPTICAL RESULTS (SIMULATED):



LED CTW0607
FWHM / FWTM 12.0° / 26.0°
Efficiency 92 %
Peak intensity 13.9 cd/lm
LEDs/each optic 1
Light colour/type Tunable White

Required components:
C16142_HEKLA-SOCKET-K

Bender Wirth: 511 Typ L8




Light distribution files



LED CTW0910
Ordering code CP19123_AMY-50-S-C2
FWHM / FWTM 16.0° / 34.0°
Efficiency 90 %
Peak intensity 7.5 cd/lm
LEDs/each optic 1
Light colour/type Tunable White

Required components:
C16142_HEKLA-SOCKET-K

Bender Wirth: 512 Typ L8




Light distribution files



LED CTW1325
FWHM / FWTM 24.0° / 46.0°
Efficiency 88 %
Peak intensity 3.8 cd/lm
LEDs/each optic 1
Light colour/type Tunable White

Required components:
C16142_HEKLA-SOCKET-K

Bender Wirth: 513 Typ L8




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB L08 (Gen2)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 28.0° / 52.0°
 Efficiency 89 %
 Peak intensity 3.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 637a Hekla

Light distribution files




LED LUXEON CoB 1202/1203
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 30.0°
 Efficiency 88 %
 Peak intensity 8.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files



LED LUXEON CoB 1202/1203
 Ordering code C17686_AMY-50-S
 FWHM / FWTM 16.1° / 30.2°
 Efficiency 90 %
 Peak intensity 8.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON CoB 1204HD
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 36.0°
 Efficiency 92 %
 Peak intensity 7.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files




LED LUXEON CoB 1205HD
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 22.0° / 42.0°
 Efficiency 91 %
 Peak intensity 5.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files



LED LUXEON CX Plus CoB - HD S01H4
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 12.0° / 27.0°
 Efficiency 93 %
 Peak intensity 13 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB - HD S02H6
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 93 %
 Peak intensity 10.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB - HD S04H9
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 18.0° / 37.0°
 Efficiency 92 %
 Peak intensity 6.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 22.0° / 44.0°
 Efficiency 89 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15254_HEKLA-SOCKET-B




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON CX Plus CoB M02 / M03 (Gen2)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 36.0°
 Efficiency 91 %
 Peak intensity 7.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15256_HEKLA-SOCKET-D



Light distribution files




LED LUXEON CX Plus CoB S01 (Gen2)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 92 %
 Peak intensity 10.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15956_HEKLA-SOCKET-J



Light distribution files



LED CHM-9 XH (19x19)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 91 %
 Peak intensity 8.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CTM-6 (Tunable White) Gen2
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 92 %
 Peak intensity 11.1 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8



LED CTM-9 (Tunable White) Gen2
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 90 %
 Peak intensity 7.5 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K





Light distribution files

Bender Wirth: 495 Typ L8



LED CxM-11 (19x19)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 22.0° / 42.0°
 Efficiency 89 %
 Peak intensity 4.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CxM-11 (19x19)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 22.0° / 42.0°
 Efficiency 89 %
 Peak intensity 4.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files




LED CxM-14 (19x19)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 27.0 + 28.0° / 51.0 + 52.0°
 Efficiency 87 %
 Peak intensity 3.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED CxM-6 (13.5x13.5)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 13.0° / 28.0°
 Efficiency 92 %
 Peak intensity 12 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1020

OPTICAL RESULTS (SIMULATED):




LED CxM-9 (13.5x13.5)
 Ordering code CP19150_AMY-50-S-B2-WHT
 FWHM / FWTM 18.0° / 38.0°
 Efficiency 90 %
 Peak intensity 6.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C18968_SOCKET-B-35-C



Light distribution files



LED COB J-Type
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 28.0° / 50.0°
 Efficiency 82 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 663a Hekla XL

Light distribution files



LED COB L-Type (LES 9)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 34.0°
 Efficiency 91 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Bender Wirth: 638a Hekla

Light distribution files


OPTICAL RESULTS (SIMULATED):



LED COB L-Type (LES 9)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 89 %
 Peak intensity 8.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.360.1110


Light distribution files



LED COB S-Type (LES 6)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 93 %
 Peak intensity 11 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Bayonet35L


Light distribution files



LED COB S-Type (LES 7)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 89 %
 Peak intensity 10.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Hekla


Light distribution files



OPTICAL RESULTS (SIMULATED):



LED COB S-Type (LES 7)
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 93 %
 Peak intensity 9.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files



LED COB T-Type
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 93 %
 Peak intensity 10.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files



LED NF1202EFC-V5
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 28.0 + 29.0°
 Efficiency 91 %
 Peak intensity 11.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NF1203EJC-V5
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 90 %
 Peak intensity 7.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files




LED NF1206JLC-V5
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 24.0° / 49.0 + 48.0°
 Efficiency 88 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED NJCWL024Z-V1MT: COB L-Type Tunable White
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 14.0° / 30.0°
 Efficiency 91 %
 Peak intensity 10.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 497 Typ L8 HV

OPTICAL RESULTS (SIMULATED):



LED NJNWS012Z-V1MT: COB S-Type Tunable White
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 12.0° / 26.0°
 Efficiency 92 %
 Peak intensity 13.9 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8 HV



LED NVCWJ024Z-V1MT: COB J-Type Tunable White
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 18.0° / 38.0°
 Efficiency 90 %
 Peak intensity 5.8 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 498 Typ L8 HV



LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 16.0° / 32.0°
 Efficiency 87 %
 Peak intensity 7.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 18.0° / 36.0°
 Efficiency 91 %
 Peak intensity 6.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files

SAMSUNG

LED LC010C G2
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 12.0° / 28.0°
 Efficiency 92 %
 Peak intensity 12 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



BJB: 47.360.1020

Light distribution files

SAMSUNG

LED LC010T (Tunable White)
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 15.0° / 32.0°
 Efficiency 91 %
 Peak intensity 8.9 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K


Light distribution files

Bender Wirth: 501 Typ L8

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC020C G2
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 16.0° / 35.0°
 Efficiency 90 %
 Peak intensity 7.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1010

Light distribution files

SAMSUNG

LED LC030C/040C G2
 Ordering code CP19132_AMY-50-S-B2
 FWHM / FWTM 22.0° / 44.0°
 Efficiency 88 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1010

Light distribution files

SAMSUNG

LED LC040D / LC060D / LC080D
 FWHM / FWTM 36.0° / 74.0°
 Efficiency 70 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 631b Hekla XL

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED MJT COB LES 14.5
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 28.0° / 52.0°
 Efficiency 88 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files




LED MJT COB LES 6
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 13.0° / 29.0°
 Efficiency 93 %
 Peak intensity 11.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

TRIDONIC

LED SLE SNC8 LES06
 Ordering code CP19123_AMY-50-S-C2
 FWHM / FWTM 12.0° / 28.0°
 Efficiency 93 %
 Peak intensity 12.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)