



CATALOGUE

Power Connector

PWE, PWF, PWG



PWC, PWCU



PWL



Power II Series: PWJ, PWH




PWCU




Range Overview


Receptacle to Overmolded with Cable




Receptacle to Field Installable



In-Line



Accessories



[Note] Design and specification are subject to change without notice.

Specification

Identifications	Power Connector
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	8A, 12A, 16A, 20A, 25A, 30A, 20A+2A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : Nylon+GF, UL Recognized, PPE
Waterproof Rating	IP66~68
Temperature Range	Receptacle : -40°C ~ 105°C Overmolded with Cable : -20°C ~ 80°C Field Installable : -40°C ~ 105°C
Contact Resistance	≤ 5mΩ
Insulation Resistance	≥ 100 MΩ at DC 500V
Durability	500 cycles
Dielectric Withstand Voltage	≥ AC1000V / 1 minute
More to know	Standard Cable Length: 01~99M

Ordering Information

1	2	3	4	5	6	7	8	9	10
Specification / Current Rating (PWE) 8A (PWCU) 20A+2A (PWF) 12A (PWG) 16A (PWC) 20A (PWJ) 30A* (PWH) 25A* (PWL) 30A**									
Number of Contacts 02, 03, 04, 05, 06, 07.... e.g. (02)= 2 Contacts									
Connector Body (Style) <u>> For Receptacle</u> (P) Front Fastened (R) Rear Fastened <u>> For Overmolded with Cable</u> (A) With Strain Relief (B) Without Strain Relief <u>> For Field installable</u> (B) Without Strain Relief									
Connector (Housing) Gender (M) Male Connector (F) Female Connector									
Contact Gender (M) Male (C) Combo (F) Female									
Assemble Style <u>> For Receptacle</u> (S) Solder Type (B) Screw in Type (C) Crimp Type <u>> For Overmolded with Cable</u> (M) Overmolded with Cable <u>> For Field Installable</u> (A) Field installable (Solder) (B) Screw in Type (C) Crimp Type									
Mating Style (S) Screw Thread (L) 2 Points Lock Bayonet (T) 3 Points Lock Bayonet									
Backshell <u>> For Receptacle</u> (C) Circular (S) Square <u>> For Overmolded with Cable</u> (L) Straight (R) Right Angle <u>> For Field Installable</u> (L) Straight (R) Right Angle									
Waterproof Rating (6) IP 66 (7) IP 67 (8) IP 68									
More Information <u>> For Receptacle</u> (001), (002), (003) Without Cable : Different Versions <u>> For Overmolded with Cable</u> (□)+(■) : Cable Type + Cable Length e.g. (A01)= UL2464 Cable + 1M <u>(□) : Cable Type</u> (A) UL2464 Cable (B) Power Cable(TC-ER) (C) SJTOW Cable <u>(■) : Cable Length</u> (D) SJTW Cable From 1M to 99M (E) H05 Cable e.g.(01) = 1M (F) H07 Cable <u>> For Field Installable</u> (001), (002), (003) Without Cable : Different Versions									

* Recommended For Inverter Application


** Recommended For LED Application

[Note] Design and specification are subject to change without notice.

Physical Dimension

Receptacle Cut-Out


Panel Cut-Out



Connector(Housing) Gender Current Rating*	Type	L / W		OD	L / W		OD
Connector Gender		Male			Female		
8A (PWE)	C	31.1	21.55		31.1	21.55	
12A (PWF)	C	31.1	21.55		31.1	21.55	
16A (PWG)	C	31.1	21.60		31.1	21.60	
20A (PWC)	B	19.4	20.80		-	-	
25A (PWH)	B	30.2	32.00		-	-	
	A	23.2	25.20		-	-	
20A+2A (PWCU)	B	19.4	20.80		-	-	
30A (PWL)	D	23.0	23.00		-	-	
30A (PWJ)	A	23.2	25.20		-	-	

Unit: mm

Connector Dimension




Connector(Housing) Gender Current Rating*	Type	L		OD / W		Recommend Panel Thickness
Connector Gender		Female	Male	Female	Male	Female & Male
8A (PWE)	II	27.50	26.50	38.00	38.00	-
12A (PWF)	II	27.50	26.50	38.00	38.00	-
16A (PWG)	II	32.40	31.00	38.00	38.00	-
20A (PWC)	I	-	18.00	-	25.00	4.5 mm Max.
25A (PWH)	I	-	55.00	-	40.00	5.0 mm Max.
		-	47.00	-	35.00	0.5~8 mm
20A+2A (PWCU)	I	-	18.00	-	25.00	4.5 mm Max.
30A (PWL)	III	-	34.60	-	31.80	-
30A (PWJ)	I	-	47.00	-	35.00	0.5~8 mm

Unit: mm

*Current rating represents a maximum value for a largest wire size recommended for use.


Overmolded with Cable



Connector(Housing) Gender Current Rating*	L		OD	
	Female	Male	Female	Male
8A (PWE)	70.3	72.0	30.2	30.2
12A (PWF)	70.3	72.0	30.2	30.2
20A (PWC)	60.0	65.5	22.2 (L)** 23.0 (T)**	18.0
25A (PWH)	91.55	100.4	40.0	31.75
20A+2A (PWCU)	60.0	65.5	22.2	18.0


** (L) 2 Points Lock Bayonet | (T) 3 Points Lock Bayonet

Field Installable



(See 3rd top-right hand chart)

Connector(Housing) Gender Current Rating*	L		OD	
	Female	Male	Female	Male
8A (PWE)	60.7	60.4	30.2	30.2
12A (PWF)	60.7	60.4	30.2	30.2
16A (PWG)	67.0	67.0	30.2	30.2
20A (PWC)	48.15	-	22.2	-
20A+2A (PWCU)	88.4	91.0	33.0	26.9
	48.15	-	22.2	-
25A (PWH)	87.4	84.1	38.0	38.0
30A (PWL)	92.14	-	35.2	-
30A (PWJ)	87.4	84.1	38.0	38.0



(See bottom right hand chart)

Connector(Housing) Gender Current Rating*	L [A]	L [B]	OD
	Female / Male	Female / Male	Female / Male
16A (PWG)	62.0	54.0	30.2

Unit: mm

*Current rating represents a maximum value for a largest wire size recommended for use.

[Note] Design and specification are subject to change without notice.

Contact Configuration

	8A (PWE)		12A (PWF)		16A (PWG)		20A (PWC)	
4 5	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM
2Contacts (02)			 R C F					
3Contacts (03)			 R C F				 R C	 R C
4Contacts (04)			 R C F		 F			
5Contacts (05)	 R C F							
6Contacts (06)	 R C F							
7Contacts (07)	 R C F							
12Contacts (12)								

25A (PWH)			20A+2A (PWCU)			30A (PWL)/(PWJ)		
MM or FF	MF or FM		MM or FF	MF or FM		MM or FF	MF or FM	
								
R	C					R		F
								
			R	C	F	R	C	F
								
R		F	R		F			
								
					F			

R: receptacle

C: overmolded with cable

F: field installable

△ 8A (PWE)

□ 12A (PWF)

◆ 16A (PWG)

◇ 20A (PWC)

● 25A (PWH)

◇ ● 20A+2A (PWCU)

● 30A (PWL)

Number of Contacts:

Ex.2 contacts (02)

Connector (Housing) Gender:

Male(M) or Female(F)

Contact Gender:

Male(M) or Female(F)

More to Choose:

- Solder (S)
- Solder Cup



- Screw In (B)



- Crimp (C)




+



Product Features

┘ Receptacle



Backshell 8



Circular (C)



Square (S)


Mating Style



2 Points Lock Bayonet (L)




3 Points Lock Bayonet (T)
(With or without Unlocking
Tool)




Screw Thread (S)

Connector Body (Style)




Rear Fastened (R)




Front Fastened (P)

┘ Overmolded with Cable



Backshell 8



Straight
(L)

Mating Style



2 Points Lock Bayonet (L)



3 Points Lock Bayonet (T)
(With or without Unlocking
Tool)




Screw Thread (S)

Connector Body (Style)




With Strain Relief (A)



Without Strain Relief (B)


┘ Field Installable



Backshell 8



Straight
(L)



Right Angle
(R)

Mating Style



2 Points Lock Bayonet (L)




3 Points Lock Bayonet (T)
(With or without Unlocking
Tool)



Screw Thread (S)



Connector Body (Style)



Without Strain Relief (B)



Find Our Standard Products

└ In-Line

• Male Connector (Housing) • Male Contacts • Screw Thread		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
8A (PWE)	05,06,07	PWE- ② AMMM-SL7A _{XX} *	PWE- ② AFFM-SL7A _{XX} *	PWE- ② BFFA-SL7001
12A (PWF)	02,03,04	PWF- ② AMMM-SL7A _{XX} *	PWF- ② AFFM-SL7A _{XX} *	PWF- ② BFFA-SL7001
25A (PWH)	03	PWH-03AMMM-SL7A _{XX} *	PWH-03AFFM-SL7A _{XX} *	—



* XX: Choose the cable length from 01~99m

└ In-Line

• Female Connector (Housing) • Female Contacts • Screw Thread		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts ②	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
8A (PWE)	05,06,07	PWE- ② AFFM-SL7A _{XX} *	PWE- ② AMMM-SL7A _{XX} *	PWE- ② BMMA-SL7001
12A (PWF)	02,03,04	PWF- ② AFFM-SL7A _{XX} *	PWF- ② AMMM-SL7A _{XX} *	PWF- ② BMMA-SL7001
25A (PWH)	03	PWH-03AFFM-SL7A _{XX} *	PWH-03AMMM-SL7A _{XX} *	—

* XX: Choose the cable length from 01~99m


└ In-Line

• Female Connector (Housing) • Female Contacts • Screw Thread		Field Installable	Overmolded with Cable	Field Installable
				
		⑧ Choose straight (L) or right angle (R)		⑧ Choose straight (L) or right angle (R)
Current Rating (Code)	Contacts ②	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
8A (PWE)	05~07	PWE- ② BFFA-SL7001	—	PWE- ② BMMA-SL7001
12A (PWF)	02~04	PWF- ② BFFA-SL7001	—	PWF- ② BMMA-SL7001
16A (PWG)	04	PWG-04BFFB-S ⑧ 7XXX*	—	PWG-04BMMB-S ⑧ 7XXX*

* XXX: Choose Pin Plating: Gold Plated (001), Silver Plated (002) or Tin Plated (003)

[Note] Design and specification are subject to change without notice.

In-Line

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet & 3 Points Lock Bayonet		Overmolded with Cable 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
20A (PWC)	03	PWC-03AMMM-LL7A XX * PWC-03AMMM-LL7B XX * PWC-03AMMM-LL7D XX * PWC-03AMMM-LL7E XX * PWC-03BMMM-LL7D XX * PWC-03BMMM-LL7E XX * PWC-03AMMM-TL7A XX * PWC-03AMMM-TL7B XX *	PWC-03AFFM-LL7A XX * PWC-03AFFM-LL7B XX * PWC-03AFFM-LL7D XX * PWC-03AFFM-LL7E XX * PWC-03BFFM-LL7D XX * PWC-03BFFM-LL7E XX * PWC-03AFFM-TL7A XX * PWC-03AFFM-TL7B XX *	PWC-03BFFA-LL7 XXX ** PWC-03BFFA-TL7001
20A+2A (PWCU)	(3+1)	PWCU-04AMMM-LL7A XX * PWCU-04AMMM-LL7B XX * PWCU-04AMMM-TL7A XX * PWCU-04AMMM-TL7B XX *	PWCU-04AFFM-LL7A XX * PWCU-04AFFM-LL7B XX * PWCU-04AFFM-TL7A XX * PWCU-04AFFM-TL7B XX *	PWCU-04BFFA-LL7 XXX ** PWCU-04BFFA-TL7001



* ~~XX~~: Choose the cable length from 01~99m** ~~XXX~~: Select UL (002) or Non-UL (001)

In-Line

• Female Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Overmolded with Cable 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	-
20A (PWC)	03	PWC-03AFFM-LL7A XX * PWC-03AFFM-LL7B XX * PWC-03AFFM-LL7D XX * PWC-03AFFM-LL7E XX *	PWC-03AMMM-LL7A XX * PWC-03AMMM-LL7B XX * PWC-03AMMM-LL7D XX * PWC-03AMMM-LL7E XX *	-
20A+2A (PWCU)	(3+1)	PWCU-04AFFM-LL7A XX * PWCU-04AFFM-LL7B XX *	PWCU-04AMMM-LL7A XX * PWCU-04AMMM-LL7B XX *	-

* ~~XX~~: Choose the cable length from 01~99m

In-Line

• Female Connector (Housing) • Female Contacts • 3 Points Lock Bayonet		Field Installable 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
20A+2A (PWCU)	(6+6)	PWCU-12BFFA-TL7001	-	PWCU-12BMMA-TL7001

In-Line

• Male Connector (Housing) • Male Contacts • 3 Points Lock Bayonet • Unlock Tool Needed (Part Number: ANB00010649) 		Field Installable 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F)** Female Contacts (F)
25A (PWH)	05	PWH-05BMMC-LL8XXX*	-	PWH-05BFFC-LL8XXX*
30A (PWJ)	03	PWJ-03BMMB-LL8XXX*	-	PWJ-03BFFB-LL8XXX*

* XXX: Choose the cable OD range 13~16mm (001) or OD 09~12mm (002)

** The unlock tool is packed with the female connector to sell.




In-Line

• Male Connector (Housing) • Female Contacts • 3 Points Lock Bayonet • Unlock Tool Needed (Part Number: ANB00010649) 		Field Installable 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F)** Male Contacts (M)
25A (PWH)	05	PWH-05BMFC-LL8XXX*	-	PWH-05BFMC-LL8XXX*
30A (PWJ)	03	PWJ-03BMFB-LL8XXX*	-	PWJ-03BFMB-LL8XXX*

* XXX: Choose the cable OD range 13~16mm (001) or OD 09~12mm (002)

** The unlock tool is packed with the female connector to sell.



In-Line

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet & 3 Points Lock Bayonet		Overmolded with Cable 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
20A (PWC)	03	PWC-03AMFM-LL7AXX* PWC-03AMFM-LL7BXX* PWC-03AMFM-LL7DXX* PWC-03AMFM-LL7EXX* PWC-03BMFM-LL7DXX* PWC-03BMFM-LL7EXX* PWC-03AMFM-TL7AXX* PWC-03AMFM-TL7BXX*	PWC-03AFMM-LL7AXX* PWC-03AFMM-LL7BXX* PWC-03AFMM-LL7DXX* PWC-03AFMM-LL7EXX* PWC-03BFMM-LL7DXX* PWC-03BFMM-LL7EXX* PWC-03AFMM-TL7AXX* PWC-03AFMM-TL7BXX*	PWC-03BFMA-LL7XXX**
20A+2A (PWCU)	(3+1)	PWCU-04AMFM-LL7AXX* PWCU-04AMFM-LL7BXX*	PWCU-04AFMM-LL7AXX* PWCU-04AFMM-LL7BXX*	-

* XX: Choose the cable length from 01~99m

** XXX: Select UL (002) or Non-UL (001)




⌋ Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Screw Thread		Receptacle  Overmolded with Cable  Field Installable 		
		8 Choose straight (L) or right angle (R)		
Current Rating (Code)	Contacts 2	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
8A (PWE)	05, 06, 07	PWE- 2 PFFS-SC7001	PWE- 2 AMMM-SL7Axx**	PWE- 2 BMMA-SL7001
12A (PWF)	02, 03, 04	PWF- 2 PFFS-SC7001	PWF- 2 AMMM-SL7Axx**	PWF- 2 BMMA-SL7001
16A (PWG)	04	PWG-04PFFB-SC7xxx*	-	PWG-04BMMB-S 8 7xxx*

* XXX: Choose Pin Plating: Gold Plated **(001)**, Silver Plated **(002)** or Tin Plated **(003)**

* XX: Choose the cable length from 01~99m

⌋ Receptacle and Mating Pair




• Male Connector (Housing) • Male Contacts • Screw Thread		Receptacle 	Overmolded with Cable 	Field Installable 
		8 Choose straight (L) or right angle (R)		
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
8A (PWE)	05, 06, 07	PWE- 2 PMMS-SC7001	PWE- 2 AFFM-SL7A <u>XX</u> **	PWE- 2 BFFA-SL7001
12A (PWF)	02, 03, 04	PWF- 2 PMMS-SC7001	PWF- 2 AFFM-SL7A <u>XX</u> **	PWF- 2 BFFA-SL7001
16A (PWG)	04	PWG- 2 PMMB-SC7 <u>XXX</u> *	–	PWG-04BFFB-S 8 7 <u>XXX</u> *
25A (PWH)	03	PWH-03PMBB-SC7001	PWH-03AFFM-SL7A <u>XX</u> **	–

* XXX: Choose Pin Plating: Gold Plated (001), Silver Plated (002) or Tin Plated (003)

* XX: Choose the cable length from 01~99m




[Note] Design and specification are subject to change without notice.

Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet		Receptacle	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
20A (PWC)	03	(UL) PWC-03PMMS-LC7001 (Non UL) PWC-03RMMS-LC7001 (UL) PWC-03RMMS-LC7002	PWC-03AFFM-LL7A ^{XX} * PWC-03AFFM-LL7B ^{XX} * PWC-03AFFM-LL7D ^{XX} * PWC-03AFFM-LL7E ^{XX} * PWC-03BFFM-LL7D ^{XX} * PWC-03BFFM-LL7E ^{XX} *	PWC-03BFFA-LL7 ^{XXX} **
20A+2A (PWCU)	(3+1)	(Non UL) PWCU-04RMMS-LC7001 (UL) PWCU-04RMMS-LC7002	PWCU-04AFFM-LL7A ^{XX} * PWCU-04AFFM-LL7B ^{XX} *	-


* ^{XX}: Choose the cable length from 01~99m** ^{XXX}: Select UL (002) or Non-UL (001)

Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • 3 Points Lock Bayonet		Receptacle	Overmolded with Cable	Field Installable
				
			** Cable length from 1~99m for your connector	***Selecting UL(002) or Non-UL (001)
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
20A (PWC)	03	PWC-03RMMS-TC7001	PWC-03AFFM-TL7A ^{XX} * PWC-03AFFM-TL7B ^{XX} *	-
30A (PWL)	03	PWL-03PMMB-TS7001	-	PWL-03BFFA-TL7 ^{XXX} **

* ^{XX}: Choose the cable length from 01~99m** ^{XXX}: Select UL (002) or Non-UL (001)




Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • 3 Points Lock Bayonet • PWH For Inverter Application • Unlock Tool Needed  (Part Number: ANB00010649)		Receptacle 	Overmolded with Cable 	Field Installable  UL 6703A Certification (E-Number 346280)
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F)* Female Contacts (F)
25A (PWH)	05	PWH-05PMMC-LC8001	-	PWH-05BFFC-LL8XXX**
30A (PWJ)	03	PWJ-03PMMB-LC8001	-	PWJ-03BFFB-LL8XXX**

* The unlock tool is packed with the female connector to sell.

** XXX: Select the cable OD range 13~16mm (001) or OD 09~12mm (002)



Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • 2 Points Lock Bayonet & 3 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (M) Male Contacts (F)	Female Connector (M) Male Contacts (F)
20A (PWC)	03	PWC-03PMFS-LC7001 PWC-03RMFS-LC7XXX* PWC-03RMFS-TC7001	PWC-03AFMM-LL7AXX** PWC-03AFMM-LL7BXX** PWC-03AFMM-LL7DXX** PWC-03AFMM-LL7EXX** PWC-03AFMM-TL7AXX** PWC-03AFMM-TL7BXX**	PWC-03BFMA-LL7XXX* PWC-03BFMA-TL7001
20A+2A (PWCU)	(3+1)	PWCU-04RMFS-LC7XXX*	PWCU-04AFMM-LL7AXX** PWCU-04AFMM-LL7BXX**	PWCU-04BFMA-LL7002

* XXX: Select UL (002) or Non-UL (001)



* XX: Choose the cable length from 01~99m

Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • 3 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
30A (PWL)	03	PWL-03PMFB-TS7001	-	PWL-03BFMA-TL7XXX*

* XXX: Select UL (002) or Non-UL (001)

Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • 3 Points Lock Bayonet • PWJ & PWH For Inverter Application • Unlock Tool Needed  (Part Number: ANB00010649)		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F)* Male Contacts (M)
25A (PWH)	05	PWH-05PMFC-LC8001	-	PWH-05BFMC-LL8XXX**
30A (PWJ)	03	PWJ-03PMFB-LC8001	-	PWJ-03BFMB-LL8XXX**






* The unlock tool is packed with the female connector to sell.

** XXX: Select the cable OD range 13~16mm (001) or OD 09~12mm (002)

Accessories

Waterproof Cap


Customization - Upon Request



6 More to choose: None (A) / With Chain (B) /
With Rubber Lead (C) / With Fish Line (D)

Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
8A (PWE)	Receptacle	Screw Thread	Male	CAP-WTAMSP 6 1
			Female	CAP-WTAFSP 6 1
	Receptacle and Overmolded with Cable		Male	CAP-WTAMSMA1
			Female	CAP-WTAFSMA1
12A (PWF)	Receptacle	Screw Thread	Male	CAP-WTAMSP 6 1
			Female	CAP-WTAFSP 6 1
	Receptacle and Overmolded with Cable		Male	CAP-WTAMSMA1
			Female	CAP-WTAFSMA1
16A (PWG)	Receptacle	Screw Thread	Male	CAP-WTAMSP 6 1
			Female	CAP-WTAFSP 6 1
	Receptacle and Overmolded with Cable		Male	CAP-WTAMSMA1
			Female	CAP-WTAFSMA1
20A (PWC)	Receptacle	2 Points Lock Bayonet	Male	CAP-WACMLP 6 1
	Receptacle and Overmolded with Cable			CAP-WACMLMA1
	Receptacle and Overmolded with Cable		Female	CAP-WACFLMA2
20A+2A (PWCU)	Receptacle	2 Points Lock Bayonet	Male	CAP-WACMLP 6 1
	Receptacle and Overmolded with Cable			CAP-WACMLMA1
	Receptacle and Overmolded with Cable		Female	CAP-WACFLMA2
25A (PWH)	Receptacle and Overmolded with Cable	3 Points Lock Bayonet	Female	CAP-WPWFTMD1
30A (PWJ)	Receptacle and Overmolded with Cable	3 Points Lock Bayonet	Male	CAP-WPWMTMD1

∟ **Unlock Tool**



Amphenol LTW Technology Co., Ltd.

5F-3, No.51, Sec.4, Zhongyang Rd., Tucheng Dist., New Taipei City 236, Taiwan
Telephone: +886-2-77416888 Fax: +886-2-77416999
www.amphenolltw.com

Kunshan Factory

No. 62, DaTong Road, Development Zone, Kunshan City, JiangSu Province, 215333 China
Telephone: +86-512-5761-0501
Fax: : +86-512-5761-0515

For further information, please contact :

Sales & Marketing Department | Email : sales@ltw-tech.com