

Industrial.

Industrial environments are often exposed to many harsh elements such as water, vibration, chemicals & extreme temperatures, but with demand growing for automated processes, there is more pressure than ever before on production & motion control systems. To overcome these challenging conditions, our connectivity solutions with metal or plastic housings are used around the world to facilitate secure power, signal & data connections in the harshest of environments.

Our robust range of vandal proof push button switches are also a perfect solution for operating heavy duty tools, metal & wood processing equipment, food & beverage processing systems & packaging machinery.



Automation.

With an increasing demand for automated machines & systems, secure & reliable connections are vital for industrial automation applications where efficiency & uptime is of the utmost importance. Our waterproof circular connectors are the perfect solution for automation systems such as factory automation, industrial networks & robotics.

From movement signals to manufacturing & material handling processes, our robust sealed connector range for power, signal & data perform excellently in harsh environments where moisture, extreme temperatures & vibration are present. With IP66, IP67, IP68 & IP69K ratings, they are particularly ideal for production lines that are prone to dust & liquid build up.

With IP66, IP67, IP68 & IP69K ratings, they are particularly ideal for production lines that are prone to dust & liquid build up.

// Industry Applications:

- Industrial Robotics
- Pharmaceutical Manufacturing
- Automotive Manufacturing
- Food & Beverage Processing
- Material Handling Equipment
- Packaging Equipment
- Process Control Systems
- Machining & Metal Processing
- Semiconductor Manufacturing
- Factory Automation Machines



Products Related To Industry:

M5 / M8 / M12 / M16 / M23

Circular Automation Connectors



- A, B & D Coding Options
- IP67 protection
- Plastic & Metal Variants
- Overmolded cables PVC & PUR
- Ratings from 1A, 30V ac/dc up to 8A, 250V ac/dc

Standard Series USB

Circular Data Connectors



- USB V2.0 performance
- IP66, IP67, IP68 & IP69K protection
- USB type 'A' or 'B' configurations
- Single & double ended cable / panel mount options

4000 Series

Circular Power Connectors



- Ratings up to 13A, 600V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 Contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, bayonet locking
- UL, CSA & VDE approvals

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

7000 Series

Circular Power Connectors



- Ratings up to 25A, 600V
- 2, 3, 6, 10 & 32 contacts
- IP66, IP67 IP68 & IP69K rated
- Plastic Shells
- cULus, UL & VDE approvals

Push-Pull Series

Circular Automation Connectors



- Multiple contacts from 2 to 30
- High packing density for space savings
- Temp: -50°C to +200°C
- Cycle: >4500
- Resistance of Vibration: 10-2000Hz, 15g

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

Tools & Machinery.

Industrial environments are exposed to many impeding elements such as water, vibration, chemicals & extreme temperatures. With demand growing for automated processes, there is more pressure than ever before on production & motion control systems.

To overcome these potentially detrimental conditions, our connectivity solutions with metal or plastic housings are used around the world to facilitate secure power, signal & data connections in the harshest of environments. Our robust range of vandal proof push button switches are also a perfect solution for operating heavy duty tools, metal & wood processing equipment, food & beverage processing systems & packaging machinery.

// Industry Applications:

- Industrial Food Slicer
- Vacuum Packaging Machine
- Printed Electronics Machinery
- Heavy Industrial Food Processor
- Industrial Grade Printer
- Industrial Automated Saws
- Industrial Coating Machinery
- Industrial Sand Blaster



Products Related To Industry:

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

900 Series

Circular Power Connectors



- 32A, 600V ac/dc max rating
- 2, 3, 4, 5, 7 & 10 contacts
- IP66, IP67, IP68 & IP69K protection
- Single or 3 phase applications
- CCC, UL, CSA & VDE approvals

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

7000 Series

Circular Power Connectors



- Ratings up to 25A, 600V
- 2, 3, 6, 10 & 32 contacts
- IP66, IP67 IP68 & IP69K rated
- Plastic Shells
- cULus, UL & VDE approvals

M16 Series

Circular Automation Connectors



- A-Coding
- Max Rating 7A, 250V ac/dc
- IP67 protection
- 3, 4, 5, 6, 8 & 12 contacts
- Metal shells with good shielding

M23 Series

Circular Automation Connectors



- A-Coding
- Max Rating 8A, 200V ac/dc
- IP67 protection
- 12 & 19 contacts
- Straight & angled options

Vandal Resistant

Switches



- Rugged & Attractive
- High Corrosion Resistance
- Dome, Low & Prominent Profiles
- IP66, IP67 & IP68 Sealing Versions
- Illuminated & Non-Illuminated

Instrumentation & Measurement.

Instrumentation & measurement systems are vital for ensuring productivity, reliability, safety & continuity in the industrial sector. Accurate & consistent measurements allow for process control & automated manufacturing systems to be optimised for maximum efficiency. Reliable electronic components are essential for achieving this.

That's where we come in. From control interfaces to power & data connections, Bulgin has a diverse choice of electronic solutions ideal for systems that measure a variety of parameters including pressure, moisture, flow, temperature & vibration.

// Industry Applications:

- | | |
|-----------------------------------|--------------------------------|
| ○ Handheld Moisture Detectors | ○ Handheld Radiation Detection |
| ○ Wireless Data Logger | ○ Pipe Inspection System |
| ○ Flow Meters & Industrial Scales | ○ Pressure Transmitter |
| ○ Solar Water Pump Controller | ○ Wireless Load Sensors |
| ○ Terrain Monitoring | ○ Moisture Meters |



Products Related To Industry:

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

Photoelectric Sensor

Sensors



- Sealed to IP67
- Stainless Steel 316 shell
- Detection distance 1 - 40mm
- Light point diameter 5.0mm at 30mm
- Ambient humidity 35 - 85%

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

Push-Pull Series

Circular Automation Connectors



- Multiple contacts from 2 to 30
- High packing density for space savings
- Temp: -50°C to +200°C
- Cycle: >4500
- Resistance of Vibration: 10-2000Hz, 15g

Vandal Resistant

Switches



- Rugged & Attractive
- High Corrosion Resistance
- Dome, Low & Prominent Profiles
- IP66, IP67 & IP68 Sealing Versions
- Illuminated & Non-Illuminated

USB C-Type

Circular Data Connectors



- USB3.2 supported
- Data rates up to 20 Gbps
- IP66, IP68 & IP69K rated
- Plug & play capability
- Secure, proven locking system

M12 Series

Circular Automation Connectors



- A, B & D Coding
- Max rating 4A, 250V ac/dc
- IP67 protection
- 3, 4, 5, 8 & 12 contacts
- PUR & PVC cable options

400 Series SMB

Circular Data Connectors



- 50Ω impedance SMB antenna
- Frequency range 0 - 4GHz
- IP66, IP67, IP68 & IP69K protection
- Rewireable & pre-wired options
- RG-174 cables