

PwrCAN Cable

SKU:A146/A146-B



Description

The **PwrCAN Cable** is a specially designed CAN communication cable for the Module13.2 PwrCAN. The cable features an XT30(2+2)-F female connector and comes in lengths of 50cm or 10cm. The cable is designed to ensure stable power and CAN signal transmission, making it suitable for various industrial and automation application environments.

Features

- XT30(2+2)-F female connector
- Available in 50cm and 10cm lengths
- Compatible with Module13.2 PwrCAN(M139)

Include

- A146: PwrCAN Cable (10pcs 10cm)
- A146-B: PwrCAN Cable (2pcs 50cm)

Applications

- Robot control
- Protocol conversion
- Industrial automation
- Vehicle communication systems
- Building automation

Specifications

Specification	Parameter
Wire Gauge	Power: 18AWG, Signal: 26AWG
10cm (10pcs)	47.5g
50cm (2pcs)	35.0g
Package Size	160 x 120 x 15mm

PinMap

CAN Communication Protocol Pinout

PwrCAN Cable	Red	Black	White	Green
CAN Bus	VCC	GND	L	H

Datasheets

- [XT30\(2+2\)-F](#)