

IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX

THIS IS A CLASS 1 DOCUMENT WHICH IS NONCONFIDENTIAL.

The information contained within this document is the property of TE Connectivity. It is supplied in confidence and the commercial security of the contents must be maintained. It must not be used for any purpose other than that for which it is supplied nor may any information contained in it be disclosed to unauthorised persons. It must not be reproduced in whole or in part without obtaining written permission from TE Connectivity (TE).

te.com

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

Table of Contents

Introduction	3
SECTION 1, CURRENT THERMAL TRANSFER PRINTERS	4
T2212-PRINTER/T200-Ident-Printer	4
Cable Identification markers	4
T2212-PRINTER/T200-Ident-Printer	5
Continuous Tube	5
T2212-PRINTER/T200-Ident-Printer	6
Labels	6
T3212-PRINTER/TE3112-PRINTER & T3224-PRINTER/TE3124-PRINTER	7
Cable Identification markers	7
T3212-PRINTER/TE3112-PRINTER & T3224-PRINTER/TE3124-PRINTER	8
Continuous Tube	8
T3212-PRINTER/TE3112-PRINTER & T3224-PRINTER/TE3124-PRINTER	9
Labels	9
T7112DS-PRINTER	10
Continuous Tube	10
T7112DS-PRINTER	11
Labels	11
SQUIX 6.3/300 Printer	12
SECTION 2, CURRENT INK JET & LASER PRINTERS	12
Ink Jet Printers	12
Epson GP-C831	12
Epson WF-7310DTW	12
Laser Printers	12
HP M452nw Laser Jet Pro	12
SL-M2026W A4 Mono Wireless Laser Printer	12
SECTION 3, TERMINAL BLOCK TT PRINTER	13
HTP600 Printer	13
SECTION 4, RIBBON ORDERING DETAILS	13
Cable Identification markers (25.4mm ID core) ordering details	13
Cable Identification markers (12.7mm ID core) ordering details	14
Labels (25.4mm ID core) ordering details	14
Labels (12.7mm ID core) ordering details	14
Trademarks	15
Related Documents:	15
SECTION 5, DISCONTINUED TT PRINTERS	16
For discontinued printers not list see previous revisions	16
T200-Label-Printer (Discontinued)	16
Labels (Only)	16
T312M-Printer and T312Mi-Printer (Discontinued)	17
Cable Identification markers	17
T312M-Printer and T312Mi-Printer (Discontinued)	18
Labels	18
Cable Identification Markers	19

T6112DS-Printer (Discontinued)	19
Continuous Tube	19
TTD03E / TTD04E / TTD05E / TTD06E-Printer (Discontinued)	20
TTD03E / TTD04E / TTD05E / TTD06E-Printer (Discontinued)	20
TTP5200 / TTP5300 Printer (Discontinued)	21
TTP5200 / TTP5300 Printer (Discontinued)	21
SECTION 6, DISCONTINUED INKJET & CARD PRINTERS	22
Epson WF-C5710 (Discontinued)	22
Epson WF-R5190DW (Discontinued)	22
Epson WF-4820DWF	22
BTT-02 Card printer (Discontinued)	22

Introduction

It is essential that the combination of Printers, Products and Ribbons or Inks are correct, to ensure the best print quality and mark permanence.

Each combination of Printer, Product, Ribbon and Ink have been evaluated for Print quality and tested for mark permanence. Any deviation from the information contained in this document will invalidate any assurances of print quality and mark permanence.

This document supersedes all previous documents detailing Identification printer, ribbon and product combinations. Please always check for the latest revision of this document by using the following link or by asking your local TE representative.

[Find Documents & Drawings](#)

A downloadable declaration and further information covering RoHS and REACH compliance can be found at the 'TE Product Compliance Support Centre': [product-compliance](#)

When selecting a TT ribbon width, it is essential that the ribbon width covers the entire area of the label, to avoid missed print and damage to the print head.

SECTION 1, CURRENT THERMAL TRANSFER PRINTERS

T2212-PRINTER/T200-Ident-Printer

Cable Identification markers

COMPATIBLE PRODUCTS	STANDARD RIBBON
*CM-SCE-TP	1966-RIBBON
D-SCE	1966-RIBBON (For Superior performance) TMS-RJS-RIBBON-4DSCE (For Standard performance)
D-SCE (Black)	TMS-RJS-RIBBON-4AG (Silver) RIB-1981-300-110-9 (White)
HLX-NEL	1966-RIBBON
HS	For Print width 60mm and above TMS-RJS-RIBBON-4RPSCE (For Standard performance) 1966-RIBBON (For Superior performance) For print width of 60mm or less LBF-2000P-RIBBON-1966-MED
HT-SCE	TMS-RJS-RIBBON-4HT
HT-SCE (Black)	T300-RIBBON-WH-4HT (White)
HX-SCE	1966-RIBBON
RPS	TMS-RJS-RIBBON-4RPSCE
NBC-SCE	TMS-RJS-RIBBON-4HT
TMS-SCE and TMS-SCE 2X	1966-RIBBON (For Superior performance) TMS-RJS-RIBBON-4RPSCE (For Standard performance)
TMS-SCE (Black)	TMS-RJS-RIBBON-4AG (Silver) RIB-1981-300-110-9 (White)
TMS-90-SCE	1966-RIBBON
UV-SCE	RIB-1976-300-110-L-0
ZHD-SCE	1966-RIBBON

*When printing CM-SCE-TP, the smooth side of the marker must be used to print onto when using a Thermal Transfer printer. The T200-Ident-Printer is approved for the standard CM-SCE-TP thickness of 0.51mm only.

SPECIFICATION

**T2212-PRINTER/T200-Ident-Printer**

Continuous Tube

COMPATIBLE PRODUCTS	STANDARD RIBBON
D-SCE-FLAT-SP, D-CT Sizes 38.1	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4DSCE (For Standard performance)
D-SCE-FLAT-SP, D-CT Sizes 25.0 to 19.0	LBF-2000P-RIBBON-1966-MED
D-SCE-FLAT-SP, D-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR
D-SCE-FLAT-SP, D-CT Sizes 38.1 (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
D-SCE-FLAT-SP, D-CT Sizes 25.0 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
D-SCE-FLAT-SP, D-CT Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
HT-CT Sizes 38.1 and above	TMS-RJS-RIBBON-4HT
HT-CT Sizes 25.4 to 19.0	TMS-RJS-RIBBON-4HT-MED
HT-CT Sizes 12.7 to 2.4	TMS-RJS-RIBBON-4HT-NAR
HT-CT (Black)	T300-RIBBON-WH-4HT (White)
HXCT, HX-CT Sizes 38.1	1966-RIBBON
HXCT, HX-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
HXCT, HX-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR
RPS-CT Sizes 38.1 and above	TMS-RJS-RIBBON-4RPSCE
RPS-CT Sizes 25.4 to 19.0	2000P-RIBBON-4TT-MED
RPS-CT Sizes 12.7 to 2.4	2000P-RIBBON-4TT-NAR
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above	1966-RIBBON (For Superior performance) TMS-RJS-RIBBON-4RPSCE (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED (For Superior performance) 2000P-RIBBON-4TT-MED (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4	1966-RIBBON-NAR (For Superior performance) 2000P-RIBBON-4TT-NAR (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
ZHD-CT Sizes 38.1 and above	1966-RIBBON
ZHD-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
ZHD-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR

SPECIFICATION

**T2212-PRINTER/T200-Ident-Printer**

Labels

COMPATIBLE PRODUCTS	STANDARD RIBBON
Decals (TTP)	1330-0607-10
Destructible Polyethylene (TN)	1330-0607-10
EET...P-8A EET...P-9 EET...P-4 SET...PSL	For labels with liner width of 64mm or smaller: 1330-3300-06 For labels with liner width of 64mm to 80mm: 1330-3300-08 For labels with liner width of 80mm to 110mm: 1330-3300-10
HPK	1330-0607-10
HPR100-A / 101-A / 110	1966-RIBBON
HPR105	For printing onto Blue / Red / Green / Black: RIB-1976-360-076-L-9 (White) for labels 76mm or smaller RIB-1976-300-110-L-9 (White) for labels 110mm to 76mm For printing onto White: 1966-RIBBON (Black) for labels 100mm to 60mm LBF-2000P-RIBBON-1966-MED (Black) for 60mm labels or smaller.
EET...V-8A	RIB-1976-300-110-L-0
EET...PY-9 EET...G-4	For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0-IN (RIB-1984-450-60-L-0), see note 2 For labels with liner width of 88mm to 60mm: RIB-1984-360-88-L-0-IN For labels with liner width of 110mm to 88mm: RIB-1984-300-110-L-0 (RIB-1984-360-114-L-0-IN), see note 2
Polyimide T1K / T2K	1330-0619-10
Polyimide T2KP	For labels with liner width of 25mm or smaller: RIB-1976-450-25-L-0 For labels with liner width of 50mm or smaller: RIB-1976-450-50-L-0 For labels with liner width of 50mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm or smaller: RIB-1976-300-110-L-0
MC / RC / CP - Strips	RIB-1976-450-25-L-0
Nylon cloth (NC)	1330-0607-10
Polyesters (WP/MP/CP/HW/HM/MV/HMM)	1330-0607-10
PANEL LABEL (PL)	Standard performance For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0 For labels with liner width of 88mm to 60mm: RIB-1984-360-88-L-0-IN For labels with liner width of 110mm to 88mm: RIB-1984-300-110-L-0 Superior Performance For labels with liner width of 60mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm to 60mm: RIB-1976-300-110-L-0
SBP	For labels with liner width of 60mm to 100mm: TMS-RJS-RIBBON-4RPSCE For labels with liner width of 60mm to 40mm: 2000P-RIBBON-4TT-MED For labels with liner width of 40mm or smaller: 2000P-RIBBON-4TT-NAR
SP	1330-0607-10
TP Tape	1330-0607-10
Tedlar PVF / TTVF	1330-3300-10 RIB-1981-300-110-9 (White), see note 1
WV / EET...V-9	1330-0607-10 (Ink wound out) 1330-0507-10 (Ink wound in)
YV	For labels with liner width of 50mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm or smaller: RIB-1976-300-110-L-0
Velum and coated paper (customized)	RIB-1997-210-110-0-IN, see note 2 RIB-1997-450-110-0 RIB-1997-450-86-0

Note 1, when printing TTVF labels with the recommended ribbons, mark permanence is classified as Class 3 in accordance with BMS-13-47L section 5.1.12.

Note 2, suffix "IN" signifies Inside wound ink.

SPECIFICATION

**T3212-PRINTER/TE3112-PRINTER & T3224-PRINTER/TE3124-PRINTER**

Cable Identification markers

COMPATIBLE PRODUCTS	STANDARD RIBBON
*CM-SCE-TP	1966-RIBBON
D-SCE	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4DSCE (For Standard performance)
D-SCE (Black)	TMS-RJS-RIBBON-4AG (Silver)
	RIB-1981-300-110-9 (White)
HL	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4RPSCE (For Standard performance)
HLX and HLX-NEL	1966-RIBBON
HLX	LBF-2000P-RIBBON-1966-MED (For print width of 60mm or less)
HTCM-SCE-TP	TMS-RJS-RIBBON-4HT
HT-SCE HT-SCE (Black)	TMS-RJS-RIBBON-4HT
	T300-RIBBON-WH-4HT (White)
HS/HC	TMS-RJS-RIBBON-4RPSCE (For Standard performance)
	1966-RIBBON (For Superior performance)
	LBF-2000P-RIBBON-1966-MED (For print width of 60mm or less)
HX	1966-RIBBON
HX-SCE	1966-RIBBON
NBC-SCE	TMS-RJS-RIBBON-4HT
NCM-SCE-TP	1966-RIBBON
NHT-SCE	TMS-RJS-RIBBON-4HT
RPS	TMS-RJS-RIBBON-4RPSCE
TMS-SCE and TMS-SCE 2X	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4RPSCE (For Standard performance)
TMS-SCE (Black)	TMS-RJS-RIBBON-4AG (Silver) RIB-1981-300-110-9 (White)
TMS-90-SCE	1966-RIBBON
UV-SCE	RIB-1976-300-110-L-0
ZHD-SCE	1966-RIBBON

When printing CM-SCE-TP, NCM-SCE-TP or HTCM-SCE-TP, the smooth side of the marker must be used to print onto, when using a Thermal Transfer printer.

*The T3212/TE3112 and the TE3124 Printers, are recommended for all CM-SCE-TP thickness variants.

SPECIFICATION

**T3212-PRINTER/TE3112-PRINTER & T3224-PRINTER/TE3124-PRINTER**

Continuous Tube

COMPATIBLE PRODUCTS	STANDARD RIBBON
D-SCE-FLAT-SP, D-CT Sizes 38.1	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4DSCE (For Standard performance)
D-SCE-FLAT-SP, D-CT Sizes 25.0 to 18.0	LBF-2000P-RIBBON-1966-MED
D-SCE-FLAT-SP, D-CT Sizes 12 to 2.4	1966-RIBBON-NAR
D-SCE-FLAT-SP, D-CT Sizes 38.1 (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
D-SCE-FLAT-SP, D-CT Sizes 25.0 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
D-SCE-FLAT-SP, D-CT Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
HT-CT Sizes 38.1	TMS-RJS-RIBBON-4HT
HT-CT Sizes 25.4 to 19.0	TMS-RJS-RIBBON-4HT-MED
HT-CT Sizes 12.7 to 2.4	TMS-RJS-RIBBON-4HT-NAR
HT-CT (Black)	T300-RIBBON-WH-4HT (White)
HXCT, HX-CT Sizes 38.1	1966-RIBBON
HXCT, HX-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
HXCT, HX-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR
RPS-CT Sizes 38.1	TMS-RJS-RIBBON-4RPSCE
RPS-CT Sizes 25.4 to 19.0	2000P-RIBBON-4TT-MED
RPS-CT Sizes 12.7 to 3.2	2000P-RIBBON-4TT-NAR
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above	1966-RIBBON (For Superior performance) TMS-RJS-RIBBON-4RPSCE (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED (For Superior performance) 2000P-RIBBON-4TT-MED (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4	1966-RIBBON-NAR (For Superior performance) 2000P-RIBBON-4TT-NAR (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
ZHD-CT Sizes 38.1	1966-RIBBON
ZHD-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
ZHD-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR

SPECIFICATION



T3212-PRINTER/TE3112-PRINTER & T3224-PRINTER/TE3124-PRINTER

Labels

COMPATIBLE PRODUCTS	STANDARD RIBBON
Decals (TTP)	1330-0607-10
Destructible Polyethylene (TN)	1330-0607-10
EET...P-8A EET...P-9 EET...P-4 SET...PSL	For labels with liner width of 64mm or smaller: 1330-3300-06 For labels with liner width of 64mm to 80mm: 1330-3300-08 For labels with liner width of 80mm to 110mm: 1330-3300-10
HPK	1330-0607-10
HPR100-A / 101-A / 110	1966-RIBBON
HPR105	For printing onto Blue / Red / Green / Black: RIB-1976-360-076-L-9 (White) for labels 76mm or smaller RIB-1976-300-110-L-9 (White) for labels 110mm to 76mm For printing onto White: 1966-RIBBON (Black) for labels 100mm to 60mm LBF-2000P-RIBBON-1966-MED (Black) for 60mm labels or smaller.
EET...V-8A	RIB-1976-300-110-L-0
EET...PY-9 EET...G-4	For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0-IN (RIB-1984-450-60-L-0) For labels with liner width of 88mm to 60mm: RIB-1984-360-88-L-0-IN For labels with liner width of 110mm to 88mm: RIB-1984-300-110-L-0 (RIB-1984-360-114-L-0-IN)
Polyimide T1K / T2K	1330-0619-10
Polyimide T2KP	For labels with liner width of 25mm or smaller: RIB-1976-450-25-L-0 For labels with liner width of 50mm or smaller: RIB-1976-450-50-L-0 For labels with liner width of 50mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm or smaller: RIB-1976-300-110-L-0
MC / RC / CP - Strips	RIB-1976-450-25-L-0
Nylon cloth (NC)	1330-0607-10
Polyesters (WP/MP/CP/HW/HM/MV/HMM)	1330-0607-10
PANEL LABEL (PL)	Standard performance For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0 (liner width <60mm) For labels with liner width of 88mm to 60mm: RIB-1984-360-88-L-0-IN, see note 2 For labels with liner width of 110mm to 88mm: RIB-1984-300-110-L-0 Superior Performance For labels with liner width of 60mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm to 60mm: RIB-1976-300-110-L-0
SBP	For labels with liner width of 60mm to 100mm: TMS-RJS-RIBBON-4RPSCE For labels with liner width of 60mm to 40mm: 2000P-RIBBON-4TT-MED For labels with liner width of 40mm or smaller: 2000P-RIBBON-4TT-NAR
SP	1330-0607-10
TP Tape	1330-0607-10
Tedlar PVF / TTVF	1330-3300-10 RIB-1981-300-110-9 (White), see note 1
WV / EET...V-9	1330-0607-10 (Ink wound out) 1330-0507-10 (Ink wound in)
YV	For labels with liner width of 50mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm or smaller: RIB-1976-300-110-L-0
Velum and coated paper (customized)	RIB-1997-210-110-0-IN, see note 2 RIB-1997-450-110-0 RIB-1997-450-86-0

Note 1, when printing TTVF labels with the recommended ribbons, mark permanence is classified as Class 3 in accordance with BMS-13-47L section 5.1.12.

Note 2, suffix "IN" signifies Inside wound ink.

SPECIFICATION

**T7112DS-PRINTER**

Continuous Tube

COMPATIBLE PRODUCTS	STANDARD RIBBON
D-SCE-FLAT-SP, D-CT Sizes 38.1	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4DSCE (For Standard performance)
D-SCE-FLAT-SP, D-CT Sizes 25.0 to 18.0	LBF-2000P-RIBBON-1966-MED
D-SCE-FLAT-SP, D-CT Sizes 12 to 2.4	1966-RIBBON-NAR
D-SCE-FLAT-SP, D-CT Sizes 38.1 (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
D-SCE-FLAT-SP, D-CT Sizes 25.0 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
D-SCE-FLAT-SP, D-CT Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
HT-CT Sizes 38.1	TMS-RJS-RIBBON-4HT
HT-CT Sizes 25.4 to 19.0	TMS-RJS-RIBBON-4HT-MED
HT-CT Sizes 12.7 to 2.4	TMS-RJS-RIBBON-4HT-NAR
HT-CT (Black)	T300-RIBBON-WH-4HT (White)
HXCT, HX-CT Sizes 38.1	1966-RIBBON
HXCT, HX-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
HXCT, HX-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR
RPS-CT Sizes 38.1	TMS-RJS-RIBBON-4RPSCE
RPS-CT Sizes 25.4 to 19.0	2000P-RIBBON-4TT-MED
RPS-CT Sizes 12.7 to 3.2	2000P-RIBBON-4TT-NAR
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above	1966-RIBBON (For Superior performance) TMS-RJS-RIBBON-4RPSCE (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED (For Superior performance) 2000P-RIBBON-4TT-MED (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4	1966-RIBBON-NAR (For Superior performance) 2000P-RIBBON-4TT-NAR (For Standard performance)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
ZHD-CT Sizes 38.1	1966-RIBBON
ZHD-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
ZHD-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR

SPECIFICATION



T7112DS-PRINTER

Labels

COMPATIBLE PRODUCTS	STANDARD RIBBON
Decals (TTP)	1330-0607-10
Destructible Polyethylene (TN)	1330-0607-10
EET...P-8A EET...P-9 EET...P-4 SET...PSL	For labels with liner width of 64mm or smaller: 1330-3300-06 For labels with liner width of 64mm to 80mm: 1330-3300-08 For labels with liner width of 80mm to 110mm: 1330-3300-10
HPK	1330-0607-10
HPR100-A / 101-A / 110	1966-RIBBON
HPR105	For printing onto Blue / Red / Green / Black: RIB-1976-360-076-L-9 (White) for labels 76mm or smaller RIB-1976-300-110-L-9 (White) for labels 110mm to 76mm For printing onto White: 1966-RIBBON (Black) for labels 100mm to 60mm LBF-2000P-RIBBON-1966-MED (Black) for 60mm labels or smaller.
EET...V-8A	RIB-1976-300-110-L-0
EET...PY-9 EET...G-4	For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0-IN (RIB-1984-450-60-L-0) For labels with liner width of 88mm to 60mm: RIB-1984-360-88-L-0-IN For labels with liner width of 110mm to 88mm: RIB-1984-300-110-L-0 (RIB-1984-360-114-L-0-IN)
Polyimide T1K / T2K	1330-0619-10
Polyimide T2KP	For labels with liner width of 25mm or smaller: RIB-1976-450-25-L-0 For labels with liner width of 50mm or smaller: RIB-1976-450-50-L-0 For labels with liner width of 50mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm or smaller: RIB-1976-300-110-L-0
MC / RC / CP - Strips	RIB-1976-450-25-L-0
Nylon cloth (NC)	1330-0607-10
Polyesters (WP/MP/CP/HW/HM/MV/HMM)	1330-0607-10
PANEL LABEL (PL)	Standard performance For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0 (liner width <60mm) For labels with liner width of 88mm to 60mm: RIB-1984-360-88-L-0-IN, see note 2 For labels with liner width of 110mm to 88mm: RIB-1984-300-110-L-0 Superior Performance For labels with liner width of 60mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm to 60mm: RIB-1976-300-110-L-0
SBP	For labels with liner width of 60mm to 100mm: TMS-RJS-RIBBON-4RPSCE For labels with liner width of 60mm to 40mm: 2000P-RIBBON-4TT-MED For labels with liner width of 40mm or smaller: 2000P-RIBBON-4TT-NAR
SP	1330-0607-10
TP Tape	1330-0607-10
Tedlar PVF / TTVF	1330-3300-10 RIB-1981-300-110-9 (White), see note 1
WV / EET...V-9	1330-0607-10 (Ink wound out) 1330-0507-10 (Ink wound in)
YV	For labels with liner width of 50mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm or smaller: RIB-1976-300-110-L-0
Velum and coated paper (customized)	RIB-1997-210-110-0-IN, see note 2 RIB-1997-450-110-0 RIB-1997-450-86-0

Note 1, when printing TTVF labels with the recommended ribbons, mark permanence is classified as Class 3 in accordance with BMS-13-47L section 5.1.12.

Note 2, suffix "IN" signifies Inside wound ink.

SQUIX 6.3/300 Printer

COMPATIBLE PRODUCTS	STANDARD RIBBON
TTVF	1330-3300-15 (For label width up to 152mm (6 inch))

The SQUIX 6.3/300 printer is only for use with TTVF labels, please contact your local TE representative for details.

SECTION 2, CURRENT INK JET & LASER PRINTERS**Ink Jet Printers****Epson GP-C831**

COMPATIBLE PRODUCTS	STANDARD INK
Raymark 1 & 6	DURA BRITE ULTRA (Epson ink)

Epson WF-7310DTW

COMPATIBLE PRODUCTS	STANDARD INK
Raymark A4 sheets	DURA BRITE ULTRA (Epson ink)

Laser Printers**HP M452nw Laser Jet Pro**

COMPATIBLE PRODUCTS	STANDARD INK
LSR self-laminating polyester labels	HP 410A
CSL self-laminating polyester labels	HP 410A

SL-M2026W A4 Mono Wireless Laser Printer

COMPATIBLE PRODUCTS	STANDARD INK
LSR self-laminating polyester labels	MLT-D1115
CSL self-laminating polyester labels	MLT-D1115

Ink jet and Laser printers are recommended for use with the compatible products and standard inks detailed in section 2. Printers and genuine OEM inks are to be sourced locally by customers.

SECTION 3, TERMINAL BLOCK TT PRINTER

HTP600 Printer

COMPATIBLE PRODUCTS	STANDARD RIBBON CASSETTE
TERMINAL BLOCK MARKERS	RIB1-B (Black) RIB1-BL (Blue) RIB1-GN (Green) RIB1-RD (Red)
MC, RC/CPMF, RCL/RCP/RCS/RCW, CPMF	
TERMINAL BLOCK ACCESSORIES MARKERS	
MCLH/MC/RCPEAD, MC, PAM	
WIRE AND CABLE MARKERS	
TDM, WMTT, TPMF	
WIRE AND CABLE FLAT MARKERS	
ETF	
PUSH BUTTON MARKERS	
PTS / PPB	
MODULAR DEVICE MARKERS	
TAP/MG, TAP	
COMPONENT AND EQUIPMENT MARKERS	
BA4 / WMTT, VYT/TAA	
PANEL MARKERS	
PAT/PPT	

SECTION 4, RIBBON ORDERING DETAILS

Cable Identification markers (25.4mm ID core) ordering details

DESCRIPTION	TE PART NUMBER
1330-3300-10	980892-000
1966-RIBBON	F55931-000
LBF-2000P-RIBBON-1966-MED	6-1768383-4
1966-RIBBON-NAR	1-2186559-1
TMS-RJS-RIBBON-4RPSCE	557721-000
2000P-RIBBON-4TT-MED	893803-000
2000P-RIBBON-4TT-NAR	277493-000
TMS-RJS-RIBBON-4DSCE	311292-000
RIB-1976-300-110-L-0	1-2186547-1
TMS-RJS-RIBBON-4HT	754073-000
TMS-RJS-RIBBON-4HT-MED	1-2186491-1
TMS-RJS-RIBBON-4HT-NAR	1-2186496-1
T300-RIBBON-WH-4HT (White)	154739-000
RIB-1981-300-110-9 (White)	2547830-1
RIB-1981-300-60-9 (White)	2547831-1
RIB-1981-300-40-9 (White)	2547833-1
TMS-RJS-RIBBON-4AG (Silver)	124503-000
2000P-RIBBON-4AG-MED	351013-000
2000P-RIBBON-4AG-NAR	346933-000
1330-0607-10	742412-000
1330-0507-10	900742-000

SPECIFICATION

**Cable Identification markers (12.7mm ID core) ordering details**

DESCRIPTION	TE PART NUMBER
TMS-101-RIBBON-4DSCE	505478-000
T200-RIBBON-1966	D60849-000
1330-0607-T200	E45478-000
TMS-101-RIBBON-4HT	746617-000
T200-RIBBON-WH-4HT (White)	086961-000
TMS-101-RIBBON-4RPSCE	310109-000
TMS-101-RIBBON-4AG (Silver)	252557-000

Labels (25.4mm ID core) ordering details

DESCRIPTION	TE PART NUMBER
1330-0607-10	742412-000
1330-0507-10	900742-000
RIB-1984-450-60-L-0-IN	1-2186560-1
RIB-1984-450-60-L-0	1-2186563-1
RIB-1984-360-88-L-0-IN	1-2186561-1
RIB-1984-300-110-L-0	1-2186564-1
RIB-1984-360-114-L-0-IN	1-2186562-1
1330-0619-10	952888-000
1330-0600-10	143060-000
1966-RIBBON	F55931-000
TMS-RJS-RIBBON-4RPSCE	557721-000
2000P-RIBBON-4TT-MED	893803-000
RIB-1976-300-60-L-0	1-2186548-1
RIB-1976-300-110-L-0	1-2186547-1
RIB-1976-360-076-L-9 (White)	1-2186321-1
RIB-1976-300-110-L-9 (White)	1-2186043-1
1330-3300-10 (For labels with liner width of 110mm or smaller)	980892-000
1330-3300-15 (For labels with liner width of 110mm to 165mm)	562492-000

Labels (12.7mm ID core) ordering details

DESCRIPTION	TE PART NUMBER
1330-0607-T200	E45478-000
1330-0619-T200	C49013-000
TMS-101-RIBBON-4RPSCE	310109-000
1330-3300-101TT	C95590-000
1330-TTB-T200	1-1768384-8
1330-0600-T200	C36369-000

For full ribbon ordering details, shelf-life conditions and dimensions please consult TE document **TTDS-257**.

HTP600 (Terminal Block TT printer) ordering details

DESCRIPTION	TE PART NUMBER
RIB1-RD	1SNA235735R0000
RIB1-B	1SNA235734R0000
RIB1-BL	1SNA235732R0000
RIB1-GN	1SNA235729R0000

All Dot Matrix inks are now obsolete please see IPB-209 for further details

Trademarks

TMS, TE Connectivity, TE connectivity (logo), Every Connection Counts and WinTotal are trademarks of the Tyco Electronics group of companies and its licensors. Other products, logos, and Company names mentioned herein may be trademarks of their respective owners.

Tedlar is a trademark of E I du Pont de Nemours & Company for polyimide films.

Related Documents:

TTDS-257 Printing Ribbons and Inks

SECTION 5, DISCONTINUED TT PRINTERS

For discontinued printers not list see previous revisions

T200-Label-Printer (Discontinued)

Labels (Only)

COMPATIBLE PRODUCTS	STANDARD RIBBON
Decals (TTP)	1330-0607-T200
Destructible Polyethylene (TN)	1330-0607-T200
EET (P-8A, P-9, P-4)	1330-TTB-T200
EET (PY-9)	1330-TTB-T200
EET (G-4)	1330-TTB-T200
EET (V-8A, V-4-W, SL...V-4-W)	1330-TTB-T200
EET (V-9)	1330-TTB-T200
EET (K-9)	1330-TTB-T200
HPK	1330-0607-T200
Polyimide (T1K/T2K)	1330-0619-T200
KTT	1330-TTB-T200
Nylon Cloth (NC)	1330-0607-T200
Paper (EP)	1330-0600-T200
Polyesters (WP/MP/HW/HM/MV/HMM)	1330-0607-T200
PPT	1330-TTB-T200
Self-Lams (SBP)	TMS-101-RIBBON-4RPSCE
Self-Lams (PVF)	1330-3300-101TT
Self-Lams (SP)	1330-0607-T200
SOLAR LABELS	1330-0607-T200
PVF	1330-3300-101TT
TTVF	1330-3300-101TT T200-RIBBON-WH (White), see note 1
White Vinyl (WV)	1330-0607-T200

Note 1, when printing TTVF labels with the recommended ribbons, mark permanence is classified as class 3 in accordance with BMS-13-47L section 5.1.12

SPECIFICATION

**T312M-Printer and T312Mi-Printer (Discontinued)**

Cable Identification markers

COMPATIBLE PRODUCTS	STANDARD RIBBON
*CM-SCE-TP	1966-RIBBON
D-SCE	TMS-RJS-RIBBON-4DSCE (For Standard performance)
	1966-RIBBON (For Superior performance)
¹ HL	TMS-RJS-RIBBON-4RPSCE (For Standard performance)
¹ HL	1966-RIBBON (For Superior performance)
HLX	1966-RIBBON
HS/HC	TMS-RJS-RIBBON-4RPSCE (For Standard performance)
HS/HC	1966-RIBBON (For Superior performance)
HTCM-SCE-TP	TMS-RJS-RIBBON-4HT
HT-SCE	TMS-RJS-RIBBON-4HT
HT-SCE (Black)	T300-RIBBON-WH-4HT (white)
HX	1966-RIBBON
HX-SCE	1966-RIBBON
NBC-SCE	TMS-RJS-RIBBON-4HT
NCM-SCE-TP	1966-RIBBON
NHT-SCE	TMS-RJS-RIBBON-4HT
RPS	TMS-RJS-RIBBON-4RPSCE
TMS-SCE and TMS-SCE-2X	TMS-RJS-RIBBON-4RPSCE (For Standard performance)
* TMS-SCE and TMS-SCE 2X	*1966-RIBBON (For Superior performance)
TMS-SCE (Black)	TMS-RJS-RIBBON-4AG (silver)
	RIB-1981-300-110-9 (White)
TMS-90-SCE	1966-RIBBON
UV-SCE	RIB-1976-300-110-L-0
ZHD-SCE	1966-RIBBON

¹Note: HL sizes HL253 and HL203 can be printed on TE3112 only

Note: T312M is superseded by the T312Mi

*Note: When printing with 1966-RIBBON. Select High energy and half speed check boxes. This feature is only available in WinTotal 5.4.03 or higher

When printing CM-SCE-TP, HTCM-SCE-TP or NCM-SCE-TP, the smooth side of the marker must be used to print onto, when using a Thermal Transfer printer. *The TE312M-Printer and T312Mi-Printer are recommended for all CM-SCE-TP thickness variants.

SPECIFICATION



T312M-Printer and T312Mi-Printer (Discontinued)

Labels

COMPATIBLE PRODUCTS	STANDARD RIBBON
Decals (TTP)	1330-0607-10
Destructible Polyethylene (TN)	1330-0607-10
HPK	1330-0607-10
HPR100-A / 101-A / 110	1966-RIBBON
HPR105	For printing onto Blue / Red / Green: RIB-1976-360-076-L-9 (White) for labels 76mm or smaller RIB-1976-300-110-L-9 (White) for labels 110mm to 76mm
	For printing onto White: 1966-RIBBON (Black) for labels 100mm to 60mm LBF-2000P-RIBBON-1966-MED (Black) for 60mm labels or smaller.
Nylon Cloth (NC)	1330-0607-10
Paper (EP)	1330-0600-10
PANEL LABEL (PL)	Standard performance For labels with liner width of 60mm or smaller: RIB-1984-450-60-L-0-IN For labels with liner width of 90mm to 60mm: RIB-1984-360-88-L-0-IN For labels with liner width of 110mm to 90mm: TTB-110SC/300AQ529
	Superior Performance For labels with liner width of 60mm or smaller: RIB-1976-300-060-L-0 For labels with liner width of 110mm to 60mm: RIB-1976-300-110-L-0
Polyesters (WP/MP/CP/HW/HM/MV/HMM)	1330-0607-10
Self-Lams (SBP)	TMS-RJS-RIBBON-4RPSCE. For labels with liner width of 60mm to 40mm: 2000P-RIBBON-4TT-MED For labels with liner width of 40mm or smaller: 2000P-RIBBON-4TT-NAR
Self-Lams (PVF)	1330-3300-10
Self-Lams (SP)	1330-0607-10
PVF	1330-3300-10
TTVF	1330-3300-10 RIB-1981-300-110-9 (White), see note 1
TP Tape	1330-0607-10
White Vinyl (WV)	1330-0607-10

Note 1, when printing TTVF labels with the recommended ribbons, mark permanence is classified as class 3 in accordance with BMS-13-47L section 5.1.12

SPECIFICATION

**T6112DS-Printer (Discontinued)**

Cable Identification Markers

COMPATIBLE PRODUCTS	STANDARD RIBBON
D-SCE	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4DSCE (For Standard performance)
HT-SCE,	TMS-RJS-RIBBON-4HT
HX-SCE	1966-RIBBON
NBC-SCE	TMS-RJS-RIBBON-4HT
NHT-SCE	TMS-RJS-RIBBON-4HT
RPS	TMS-RJS-RIBBON-4RPSCE
TMS-SCE (2X)	TMS-RJS-RIBBON-4RPSCE
TMS-SCE (Black)	TMS-RJS-RIBBON-4AG (Silver) RIB-1981-300-110-9 (White)
TMS-90-SCE	1966-RIBBON
UV-SCE	RIB-1976-300-110-L-0
ZHD-SCE	1966-RIBBON

T6112DS-Printer (Discontinued)

Continuous Tube

COMPATIBLE PRODUCTS	STANDARD RIBBON
D-SCE-FLAT-SP, D-CT Size 38.1	1966-RIBBON (For Superior performance)
	TMS-RJS-RIBBON-4DSCE (For Standard performance)
D-SCE-FLAT-SP, D-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
D-SCE-FLAT-SP, D-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR
D-SCE-FLAT-SP, D-CT (Black) Size 38.1	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
HT-CT Sizes 38.1 and above	TMS-RJS-RIBBON-4HT
HT-CT Sizes 19.0 and 25.4	TMS-RJS-RIBBON-4HT-MED
HT-CT Sizes 2.4 to 12.7	TMS-RJS-RIBBON-4HT-NAR
HT-CT (Black)	T300-RIBBON-WH-4HT (White)
HXCT, HX-CT Sizes 38.1	1966-RIBBON
HXCT, HX-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
HXCT, HX-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR
RPS-CT Sizes 38.1 and above	TMS-RJS-RIBBON-4RPSCE
RPS-CT Sizes 25.4 to 19.0	2000P-RIBBON-4TT-MED
RPS-CT Sizes 17.7 to 2.4	2000P-RIBBON-4TT-NAR
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above	TMS-RJS-RIBBON-4RPSCE
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0	2000P-RIBBON-4TT-MED
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4	2000P-RIBBON-4TT-NAR
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 38.1 and above (Black)	TMS-RJS-RIBBON-4AG (Silver), RIB-1981-300-110-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 25.4 to 19.0 (Black)	2000P-RIBBON-4AG-MED (Silver), RIB-1981-300-60-9 (White)
TTMS, TMS-CT, TTMS-2X & TTMS-MP Sizes 12.7 to 2.4 (Black)	2000P-RIBBON-4AG-NAR (Silver), RIB-1981-300-40-9 (White)
ZHD-CT Sizes 38.1 and above	1966-RIBBON
ZHD-CT Sizes 25.4 to 19.0	LBF-2000P-RIBBON-1966-MED
ZHD-CT Sizes 12.7 to 2.4	1966-RIBBON-NAR

SPECIFICATION

**TTD03E / TTD04E / TTD05E / TTD06E-Printer (Discontinued)**

Labels (only)

COMPATIBLE PRODUCTS	STANDARD RIBBON
IKT...PV-4 IKT...PY-9 IMT...PV-4 IMT...PY-9 EET...PY-9 EET...G-4 EET...V-8A EET...V-4-W EET-SL...V-4-W EET...K-9 PPT...DF-4 PPT...DF-9	 For labels with liner width of 60mm to 40mm: RIB-1984-450-60-L-0-INS For labels with liner width of 90mm to 76mm: TTB-090SC/36-AQ529 For labels with liner width of 110mm to 90mm: RIB-1984-300-110-L-0 For labels with liner width of 114mm to 110mm: RIB-1984-360-114-L-0-IN For labels with liner width of 166mm to 165mm: TTB-166SC/360AQ529 When "Ink in" is required delete "S" (TTB-040SC/450AQ529)
EET...P-8A EET...P-9 EET...P-4 EET...V-9 SET...PSL	For labels with liner width of 60mm or smaller: TTB-060SC/300 For labels with liner width of 76mm to 60mm: TTB-076SC/300 For labels with liner width of 84mm to 76mm: TTB-084SC/300 For labels with liner width of 110mm to 84mm: TTB-110SC/300 For labels with liner width of 128mm to 110mm: TTB-128SC/300 For labels with liner width of 145mm to 128mm: TTB-145SC/300 For labels with liner width of 170mm to 145mm: TTB-170SC/300

TTD03E / TTD04E / TTD05E / TTD06E-Printer (Discontinued)

COMPATIBLE PRODUCTS	STANDARD RIBBON
PPT...DF-4 PPT...DF-9 KMT EP	For labels with liner width of 76mm or smaller: TTB-076SC/300WH For labels with liner width of 84mm to 76mm: TTB-084SC/300WH For labels with liner width of 110mm to 84mm: TTB-110SC/300WH For labels with liner width of 145mm to 110mm: TTB-145SC/300WH For labels with liner width of 170 to 145mm: TTB-170SC/300WH

SPECIFICATION

**TTP5200 / TTP5300 Printer (Discontinued)**

COMPATIBLE PRODUCTS	STANDARD RIBBON
IKT...PV-4 IKT...PY-9 IMT...PV-4 IMT...PY-9 EET...PY-9 EET...V-8A EET...G-4 EET...V-4-W EET-SL...V-4-W EET...K-9 PPT...DF-4 PPT...DF-9	For labels with liner width of 60mm to 40mm: RIB-1984-450-60-L-0-INS For labels with liner width of 90mm to 76mm: RIB-1984-360-88-L-0-IN For labels with liner width of 110mm to 90mm: RIB-1984-300-110-L-0 For labels with liner width of 114mm to 110mm: RIB-1984-360-114-L-0-IN
EET...P-8A EET...P-9 EET...P-4 EET...V-9 SET...PSL	For labels with liner width of 60mm or smaller: TTB-060SC/300 For labels with liner width of 76mm to 60mm: TTB-076SC/300 For labels with liner width of 84mm to 76mm: TTB-084SC/300 For labels with liner width of 110mm to 84mm: TTB-110SC/300 For labels with liner width of 128mm to 110mm: TTB-128SC/300 For labels with liner width of 145mm to 128mm: TTB-145SC/300 For labels with liner width of 170mm to 145mm: TTB-170SC/300

TTP5200 / TTP5300 Printer (Discontinued)

COMPATIBLE PRODUCTS	STANDARD RIBBON
PPT...DF-4 PPT...DF-9 KMT EP	For labels with liner width of 76mm or smaller: TTB-076SC/300WH For labels with liner width of 84mm to 76mm: TTB-084SC/300WH For labels with liner width of 110mm to 84mm: TTB-110SC/300WH For labels with liner width of 145mm to 110mm: TTB-145SC/300WH For labels with liner width of 170mm to 145mm: TTB-170SC/300WH

SECTION 6, DISCONTINUED INKJET & CARD PRINTERS

Epson WF-C5710 (Discontinued)

COMPATIBLE PRODUCTS	STANDARD INK
Raymark A4 sheets	DURA BRITE ULTRA (Epson ink)

Epson WF-R5190DW (Discontinued)

COMPATIBLE PRODUCTS	STANDARD INK
Raymark A4 sheets	DURA BRITE ULTRA (Epson ink)

Epson WF-4820DWF

COMPATIBLE PRODUCTS	STANDARD INK
Raymark A4 sheets	DURA BRITE ULTRA (Epson ink)

BTT-02 Card printer (Discontinued)

COMPATIBLE PRODUCTS	STANDARD RIBBON
BGS	BBB-060SC/200 (black).
BGF	
BET	
BTS	
BBK	
BBL	
BBS	

BTT-02 (card printer) ordering details

DESCRIPTION	TE PART NUMBER
BBB-060SC/200 (black).	1-1768016-4