

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
SFML-105-02-S-D-A-K-TR	200-SFML10502SDAKTR	SFML-105-02-L-D-A-K-TR	200-SFML10502LDAKTR
SFML-105-03-S-D-LC	200-SFML10503SDLCL	SFML-105-03-L-D-LC	200-SFML-10503LDLCL
SFML-105-T2-S-D-A-K-TR	200-SFML105T2SDAKTR	SFML-105-T2-L-D-A-K-TR	200-SFML105T2LDAKTR
SFML-105-T2-S-D-SN-K-TR	200-SFML105T2SDSNKTR	SFML-105-T2-L-D-SN-K-TR	200-SFML105T2LDSNKTR
SFML-107-01-S-D	200-SFML10701SD	SFML-107-01-L-D	200-SFML10701LD
SFML-110-01-S-D	200-SFML11001SD	SFML-110-01-L-D	200-SFML11001LD
SFML-110-02-S-D-A	200-SFML11002SDA	SFML-110-02-L-D-A	200-SFML11002LDA
SFML-110-02-S-D-A-K-TR	200-SFML11002SDAKTR	SFML-110-02-L-D-A-K-TR	200-SFML11002LDAKTR
SFML-110-02-S-D-LC-K-TR	200-SFML11002SDLCKTR	SFML-110-02-L-D-LC-K-TR	200-SFML11002LDLCKTR
SFML-110-T1-S-D	200-SFML110T1SD	SFML-110-T1-L-D	200-SFML110T1LD
SFML-110-T2-H-D-LC-P-TR	200-SFML110T2HDLCPTR	SFML-110-T2-L-D-LC-P-TR	200-SFML110T2LDLCPTR
SFML-110-T2-S-D-A-K-TR	200-SFML110T2SDAKTR	SFML-110-T2-L-D-A-K-TR	200-SFML110T2LDAKTR
SFML-110-T2-S-D-A-P-TR	200-SFML110T2SDAPTR	SFML-110-T2-L-D-A-P-TR	200-SFML110T2LDAPTR
SFML-110-T2-S-D-K-TR	200-SFML110T2SDKTR	SFML-110-T2-L-D-K-TR	200-SFML110T2LDKTR
SFML-110-T2-S-D-LC-K-TR	200-SFML110T2SDLCKTR	SFML-110-T2-L-D-LC-K-TR	200-SFML110T2LDLCKTR
SFML-110-T2-S-D-P-TR	200-SFML110T2SDPTR	SFML-110-T2-L-D-P-TR	200-SFML110T2LDPTR
SFML-115-02-S-D-A-K-TR	200-SFML11502SDAKTR	SFML-115-02-L-D-A-K-TR	200-SFML11502LDAKTR
SFML-115-02-S-D-K	200-SFML11502SDK	SFML-115-02-L-D-K	200-SFML11502LDK
SFML-115-02-S-D-K-TR	200-SFML11502SDKTR	SFML-115-02-L-D-K-TR	200-SFML11502LDKTR
SFML-115-03-S-D-LC	200-SFML11503SDLCL	SFML-115-03-L-D-LC	200-SFML-11503LDLCL
SFML-115-T2-S-D-A-P-TR	200-SFML115T2SDAPTR	SFML-115-T2-L-D-A-P-TR	200-SFML115T2LDAPTR
SFML-115-T2-S-D-LC-K-TR	200-SFML115T2SDLCKTR	SFML-115-T2-L-D-LC-K-TR	200-SFML115T2LDLCKTR
SFML-120-02-S-D-A-K-TR	200-SFML12002SDAKTR	SFML-120-02-L-D-A-K-TR	200-SFML1200-2LDAKTR
SFML-120-02-S-D-A-P-TR	200-SFML1200-2SDAPTR	SFML-120-02-L-D-A-P-TR	200-SFML12002LDAPTR
SFML-120-T2-H-D-LC	200-SFML120T2HDLCL	SFML-120-T2-L-D-LC	200-SFML120T2LDLCL
SFML-120-T2-S-D-A	200-SFML120T2SDA	SFML-120-T2-L-D-A	200-SFML120T2LDA
SFML-120-T2-S-D-A-K-TR	200-SFML120T2SDAKTR	SFML-120-T2-L-D-A-K-TR	200-SFML120T2LDAKTR

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
SFML-120-T2-S-D-K	200-SFML120T2SDK	SFML-120-T2-L-D-K	200-SFML120T2LDK
SFML-120-T2-S-D-LC-K-TR	200-SFML120T2SDLCKTR	SFML-120-T2-L-D-LC-K-TR	200-SFML120T2LDLCKTR
SFML-120-T2-S-D-LC-P-TR	200-SFML120T2SDLCPTR	SFML-120-T2-L-D-LC-P-TR	200-SFML120T2LDLCPTR
SFML-125-T2-S-D-A-K-TR	200-SFML125T2SDAKTR	SFML-125-T2-L-D-A-K-TR	200-SFML125T2LDAKTR
SFML-125-T2-S-D-LC	200-SFML125T2SDLC	SFML-125-T2-L-D-LC	200-SFML125T2LDLC
SFML-130-02-S-D-LC	200-SFML13002SDLC	SFML-130-02-L-D-LC	200-SFML13002LDLC
SFML-140-L2-S-D-LC	200-SFML140L2SDLC	SFML-140-L2-L-D-LC	200-SFML140L2LDLC
SFML-150-02-S-D-A-K-TR	200-SFML15002SDAKTR	SFML-150-02-L-D-A-K-TR	200-SFML-15002LDAKTR