

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
SSM-102-S-DV-K-TR	200-SSM102SDVKTR	SSM-102-L-DV-K-TR	200-SSM102LDVKTR
SSM-103-S-DV-BE-LC-P-TR	200-SSM103SDVBELCPTR	SSM-103-L-DV-BE-LC-P-TR	200-SSM103LDVBELCPTR
SSM-103-S-DV-K-TR	200-SSM103SDVKTR	SSM-103-L-DV-K-TR	200-SSM103LDVKTR
SSM-103-S-DV-P-TR	200-SSM103SDVPTR	SSM-103-L-DV-P-TR	200-SSM103LDVPTR
SSM-103-S-SV-BE-P-TR	200-SSM103SSVBEPTR	SSM-103-L-SV-BE-P-TR	200-SSM103LSVBEPTR
SSM-103-S-SV-P-TR	200-SSM103SSVPTR	SSM-103-L-SV-P-TR	200-SSM103LSVPTR
SSM-104-S-DV	200-SSM104SDV	SSM-104-L-DV	200-SSM104LDV
SSM-104-S-DV-BE-A-K-TR	200-SSM104SDVBEAKTR	SSM-104-L-DV-BE-A-K-TR	200-SSM104LDVBEAKTR
SSM-104-S-DV-K-TR	200-SSM104SDVKTR	SSM-104-L-DV-K-TR	200-SSM104LDVKTR
SSM-104-S-DV-P-FR	200-SSM104SDVPFR	SSM-104-L-DV-P-FR	200-SSM104LDVPFR
SSM-104-S-DV-P-TR	200-SSM104SDVPTR	SSM-104-L-DV-P-TR	200-SSM104LDVPTR
SSM-105-S-DH-TR	200-SSM105SDHTR	SSM-105-L-DH-TR	200-SSM105LDHTR
SSM-105-S-DV-A-P-TR	200-SSM105SDVAPTR	SSM-105-L-DV-A-P-TR	200-SSM105LDVAPTR
SSM-105-S-DV-BE-LC-K-TR	200-SSM105SDVBELCKTR	SSM-105-L-DV-BE-LC-K-TR	200-SSM105LDVBELCKTR
SSM-105-S-DV-BE-LC-P-FR	200-SSM105SDVBELCPFR	SSM-105-L-DV-BE-LC-P-FR	200-SSM105LDVBELCPFR
SSM-105-S-DV-BE-P-TR	200-SSM105SDVBEPTR	SSM-105-L-DV-BE-P-TR	200-SSM105LDVBEPTR
SSM-105-S-DV-K-TR	200-SSM105SDVKTR	SSM-105-L-DV-K-TR	200-SSM105LDVKTR
SSM-105-S-DV-P-TR	200-SSM105SDVPTR	SSM-105-L-DV-P-TR	200-SSM105LDVPTR
SSM-105-S-SH-TR	200-SSM105SSHTR	SSM-105-L-SH-TR	200-SSM105LSHTR
SSM-105-S-SV-P-TR	200-SSM105SSVPTR	SSM-105-L-SV-P-TR	200-SSM105LSVPTR
SSM-106-S-DV-K-TR	200-SSM106SDVKTR	SSM-106-L-DV-K-TR	200-SSM106LDVKTR
SSM-106-S-DV-LC	200-SSM106SDVLC	SSM-106-L-DV-LC	200-SSM106LDVLC
SSM-106-S-DV-LC-K-TR	200-SSM106SDVLCCKTR	SSM-106-L-DV-LC-K-TR	200-SSM106LDVLCCKTR
SSM-106-S-DV-P-TR	200-SSM106SDVPTR	SSM-106-L-DV-P-TR	200-SSM106LDVPTR
SSM-107-H-DV-A-P-TR	200-SSM107HDVAPTR	SSM-107-L-DV-A-P-TR	200-SSM107LDVAPTR
SSM-107-S-DV-A-K-TR	200-SSM107SDVAKTR	SSM-107-L-DV-A-K-TR	200-SSM107LDVAKTR
SSM-107-S-DV-BE-P-TR	200-SSM107SDVBEPTR	SSM-107-L-DV-BE-P-TR	200-SSM107LDVBEPTR

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
SSM-107-S-DV-K-TR	200-SSM107SDVKTR	SSM-107-L-DV-K-TR	200-SSM107LDVKTR
SSM-108-S-DV-A-K-TR	200-SSM108SDVAKTR	SSM-108-L-DV-A-K-TR	200-SSM108LDVAKTR
SSM-108-S-DV-A-M-TR	200-SSM108SDVAMTR	SSM-108-L-DV-A-M-TR	200-SSM108LDVAMTR
SSM-108-S-DV-A-P-TR	200-SSM108SDVAPTR	SSM-108-L-DV-A-P-TR	200-SSM108LDVAPTR
SSM-108-S-DV-BE-A-M-TR	200-SSM108SDVBEAMTR	SSM-108-L-DV-BE-A-M-TR	200-SSM108LDVBEAMTR
SSM-108-S-DV-BE-P-TR	200-SSM108SDVBEPTR	SSM-108-L-DV-BE-P-TR	200-SSM108LDVBEPTR
SSM-108-S-DV-K-TR	200-SSM108SDVKTR	SSM-108-L-DV-K-TR	200-SSM108LDVKTR
SSM-108-S-DV-P-TR	200-SSM108SDVPTR	SSM-108-L-DV-P-TR	200-SSM108LDVPTR
SSM-108-S-SH-TR	200-SSM108SSHTR	SSM-108-L-SH-TR	200-SSM108LSHTR
SSM-108-S-SV-LC	200-SSM108SSVLC	SSM-108-L-SV-LC	200-SSM108LSVLC
SSM-109-S-DV-P-TR	200-SSM109SDVPTR	SSM-109-L-DV-P-TR	200-SSM109LDVPTR
SSM-110-S-DH	200-SSM110SDH	SSM-110-L-DH	200-SSM110LDH
SSM-110-S-DH-TR	200-SSM110SDHTR	SSM-110-L-DH-TR	200-SSM110LDHTR
SSM-110-S-DV	200-SSM110SDV	SSM-110-L-DV	200-SSM110LDV
SSM-110-S-DV-A-M-TR	200-SSM110SDVAMTR	SSM-110-L-DV-A-M-TR	200-SSM110LDVAMTR
SSM-110-S-DV-A-P-TR	200-SSM110SDVAPTR	SSM-110-L-DV-A-P-TR	200-SSM110LDVAPTR
SSM-110-S-DV-BE	200-SSM110SDVBE	SSM-110-L-DV-BE	200-SSM110LDVBE
SSM-110-S-DV-BE-K-TR	200-SSM110SDVBKTR	SSM-110-L-DV-BE-K-TR	200-SSM110LDVBKTR
SSM-110-S-DV-K	200-SSM110SDVK	SSM-110-L-DV-K	200-SSM110LDVK
SSM-110-S-DV-K-TR	200-SSM110SDVKTR	SSM-110-L-DV-K-TR	200-SSM110LDVKTR
SSM-110-S-DV-LC-P-TR	200-SSM110SDVLCPTR	SSM-110-L-DV-LC-P-TR	200-SSM110LDVLCPTR
SSM-110-S-SV-BE-K-TR	200-SSM110SSVBKTR	SSM-110-L-SV-BE-K-TR	200-SSM110LSVBKTR
SSM-110-S-SV-P-TR	200-SSM110SSVPTR	SSM-110-L-SV-P-TR	200-SSM110LSVPTR
SSM-112-S-DV-BE	200-SSM112SDVBE	SSM-112-L-DV-BE	200-SSM112LDVBE
SSM-112-S-DV-K-TR	200-SSM112SDVKTR	SSM-112-L-DV-K-TR	200-SSM112LDVKTR
SSM-112-S-DV-LC	200-SSM112SDVLC	SSM-112-L-DV-LC	200-SSM112LDVLC
SSM-112-S-DV-LC-K-TR	200-SSM112SDVLCCKTR	SSM-112-L-DV-LC-K-TR	200-SSM112LDVLCCKTR
SSM-113-S-DV-P-TR	200-SSM113SDVPTR	SSM-113-L-DV-P-TR	200-SSM113LDVPTR
SSM-114-S-DV-BE-K-TR	200-SSM114SDVBKTR	SSM-114-L-DV-BE-K-TR	200-SSM114LDVBKTR
SSM-114-S-DV-K-TR	200-SSM114SDVKTR	SSM-114-L-DV-K-TR	200-SSM114LDVKTR
SSM-115-S-DV	200-SSM115SDV	SSM-115-L-DV	200-SSM115LDV

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
SSM-115-S-DV-A-K-TR	200-SSM115SDVAKTR	SSM-115-L-DV-A-K-TR	200-SSM-115LDVAKTR
SSM-115-S-DV-K-TR	200-SSM115SDVKTR	SSM-115-L-DV-K-TR	200-SSM115LDVKTR
SSM-115-S-DV-P	200-SSM115SDVP	SSM-115-L-DV-P	200-SSM115LDVP
SSM-116-H-DV-P-TR	200-SSM116HDVPTR	SSM-116-L-DV-P-TR	200-SSM116LDVPTR
SSM-116-S-SH-TR	200-SSM116SSHTR	SSM-116-L-SH-TR	200-SSM116LSHTR
SSM-118-S-DV-A-K-TR	200-SSM118SDVAKTR	SSM-118-L-DV-A-K-TR	200-SSM118LDVAKTR
SSM-120-S-DV-BE	200-SSM120SDVBE	SSM-120-L-DV-BE	200-SSM120LDVBE
SSM-120-S-DV-BE-P-TR	200-SSM120SDVBEPTR	SSM-120-L-DV-BE-P-TR	200-SSM120LDVBEPTR
SSM-120-S-DV-LC-M-TR	200-SSM120SDVLCMTR	SSM-120-L-DV-LC-M-TR	200-SSM120LDVLCMTR
SSM-120-S-SH	200-SSM120SSH	SSM-120-L-SH	200-SSM120LSH
SSM-122-S-SH-TR	200-SSM122SSHTR	SSM-122-L-SH-TR	200-SSM122LSHTR
SSM-125-S-DV-BE-LC	200-SSM125SDVBELC	SSM-125-L-DV-BE-LC	200-SSM125LDVBELC
SSM-126-S-SH	200-SSM126SSH	SSM-126-L-SH	200-SSM126LSH
SSM-132-S-DV-LC-P	200-SSM132SDVLCPC	SSM-132-L-DV-LC-P	200-SSM132LDVLCPC
SSM-136-S-DV-LC-K	200-SSM136SDVLCCK	SSM-136-L-DV-LC-K	200-SSM136LDVLCCK