

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
TFML-107-01-S-D-RA	200-TFML10701SDRA	TFML-107-01-L-D-RA	200-TFML10701LDRA
TFML-110-01-S-D	200-TFML11001SD	TFML-110-01-L-D	200-TFML11001LD
TFML-110-01-S-D-RA	200-TFML11001SDRA	TFML-110-01-L-D-RA	200-TFML11001LDRA
TFML-110-02-H-D-LC-P-TR	200-TFML11002HDLCPTR	TFML-110-02-L-D-LC-P-TR	200-TFML11002LDLCPTR
TFML-110-02-S-D	200-TFML11002SD	TFML-110-02-L-D	200-TFML11002LD
TFML-110-02-S-D-A	200-TFML11002SDA	TFML-110-02-L-D-A	200-TFML11002LDA
TFML-110-02-S-D-A-K	200-TFML11002SDAK	TFML-110-02-L-D-A-K	200-TFML11002LDAK
TFML-110-02-S-D-A-K-TR	200-TFML11002SDAKTR	TFML-110-02-L-D-A-K-TR	200-TFML11002LDAKTR
TFML-110-02-S-D-A-P-TR	200-TFML11002SDAPTR	TFML-110-02-L-D-A-P-TR	200-TFML11002LDAPTR
TFML-110-02-S-D-K-TR	200-TFML11002SDKTR	TFML-110-02-L-D-K-TR	200-TFML11002LDKTR
TFML-110-02-S-D-LC	200-TFML11002SDLC	TFML-110-02-L-D-LC	200-TFML11002LDLC
TFML-110-02-S-D-LC-K-TR	200-TFML11002SDLCCKTR	TFML-110-02-L-D-LC-K-TR	200-TFML11002LDLCCKTR
TFML-110-02-S-D-LC-P-TR	200-TFML11002SDLCPTR	TFML-110-02-L-D-LC-P-TR	200-TFML11002LDLCPTR
TFML-110-02-S-D-P-TR	200-TFML11002SDPTR	TFML-110-02-L-D-P-TR	200-TFML11002LDPTR
TFML-115-01-S-D	200-TFML11501SD	TFML-115-01-L-D	200-TFML11501LD
TFML-115-01-S-D-LC	200-TFML11501SDLC	TFML-115-01-L-D-LC	200-TFML11501LDLC
TFML-115-01-S-D-RA	200-TFML11501SDRA	TFML-115-01-L-D-RA	200-TFML11501LDRA
TFML-115-02-S-D-A-K-TR	200-TFML11502SDAKTR	TFML-115-02-L-D-A-K-TR	200-TFML11502LDAKTR
TFML-115-02-S-D-A-P-TR	200-TFML11502SDAPTR	TFML-115-02-L-D-A-P-TR	200-TFML11502LDAPTR
TFML-115-02-S-D-LC	200-TFML11502SDLC	TFML-115-02-L-D-LC	200-TFML11502LDLC
TFML-115-02-S-D-LC-K-TR	200-TFML11502SDLCCKTR	TFML-115-02-L-D-LC-K-TR	200-TFML11502LDLCCKTR
TFML-115-02-S-D-P-TR	200-TFML11502SDPTR	TFML-115-02-L-D-P-TR	200-TFML11502LDPTR
TFML-120-01-S-D-LC	200-TFML12001SDLC	TFML-120-01-L-D-LC	200-TFML12001LDLC
TFML-120-01-S-D-RA	200-TFML12001SDRA	TFML-120-01-L-D-RA	200-TFML12001LDRA
TFML-120-02-S-D-A	200-TFML12002SDA	TFML-120-02-L-D-A	200-TFML12002LDA
TFML-120-02-S-D-A-K-TR	200-TFML12002SDAKTR	TFML-120-02-L-D-A-K-TR	200-TFML12002LDAKTR
TFML-120-02-S-D-A-P-TR	200-TFML12002SDAPTR	TFML-120-02-L-D-A-P-TR	200-TFML12002LDAPTR

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
TFML-120-02-S-D-K	200-TFML12002SDK	TFML-120-02-L-D-K	200-TFML12002LDK
TFML-120-02-S-D-P-TR	200-TFML12002SDPTR	TFML-120-02-L-D-P-TR	200-TFML12002LDPTR
TFML-125-01-S-D-RA	200-TFML12501SDRA	TFML-125-01-L-D-RA	200-TFML12501LDRA
TFML-125-02-S-D-A	200-TFML12502SDA	TFML-125-02-L-D-A	200-TFML12502LDA
TFML-125-02-S-D-LC	200-TFML12502SDLC	TFML-125-02-L-D-LC	200-TFML12502LDLC
TFML-125-02-S-D-LC-K-TR	200-TFML12502SDLCKTR	TFML-125-02-L-D-LC-K-TR	200-TFML12502LDLCKTR
TFML-125-02-S-D-P-TR	200-TFML12502SDPTR	TFML-125-02-L-D-P-TR	200-TFML12502LDPTR
TFML-130-02-S-D-A-P-TR	200-TFML13002SDAPTR	TFML-130-02-L-D-A-P-TR	200-TFML13002LDAPTR
TFML-130-02-S-D-LC	200-TFML13002SDLC	TFML-130-02-L-D-LC	200-TFML13002LDLC
TFML-150-01-S-D-RA	200-TFML15001SDRA	TFML-150-01-L-D-RA	200-TFML15001LDRA
TFML-150-02-S-D-A	200-TFML15002SDA	TFML-150-02-L-D-A	200-TFML15002LDA
TFML-150-02-S-D-A-K-TR	200-TFML15002SDAKTR	TFML-150-02-L-D-A-K-TR	200-TFML15002LDAKTR