




REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/20/2022	GUTTADAURO



"HOSPITAL GRADE" DESIGNATION




NEMA HG 5-15P  
PLUG




LENGTH

SJT 18AWG, BLACK  
3-COND CORDAGE



C13 LOCKING  
CONNECTOR



NOTES:

1. PLUG: NEMA HG 5-15P, BLACK
2. CONNECTOR: EN60320 C13 LOCK PLUS, BLACK
3. CORDAGE: SJT3X18AWG, BLACK  
COLOR CODING OF CONDUCTORS: BLACK, WHITE, GREEN  
APPROVALS: UL/CSA  
RATING: 10A/125V
4. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
5. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:

$\leq 12$  [305] =  $+1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $+2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $+4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $+6$  [152] / -0  
 $> 300$  [7620] =  $+5\%$  / -0

ALL OTHER DIMENSIONAL TOLERANCES:

$.X = \pm .2$  [5]      FRACTIONS  
 $.XX = \pm .02$  [5]       $\pm 1/32$   
 $.XXX = \pm .005$  [1.3]      ANGLES  $\pm 1^\circ$

THIRD-ANGLE PROJECTION



CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

COLOR VARIATIONS  
MAY OCCUR

APPROVALS

DATE

DRAWN BY

07/20/2022

CHECKED BY

07/20/2022

APPROVED BY

07/20/2022

GUTTADAURO

07/20/2022

CATEGORY



50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

POWER PRODUCTS

PRODUCT DESCRIPTION  
IEC LOCK C13+ TO HG NEMA 5-15P,  
10A, 125V

SIZE      CAGE CODE      ITEM NO.

A

43321

C13LPHGN515-10

REV.

A

SCALE: NONE

CAD FILE: C13LPHGN515-10.SLDDRW

SHEET 1 OF 1