

AMY-70-M

~24° medium beam

SPECIFICATION:

Dimensions	Ø 69.9
Height	12.8 mm
Fastening	socket
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
AMY-70-M	Single lens	PMMA	clear		
AMY-70-HLD2-C	Holder C	PC	black		
AMY-70-HLD2-B	Holder B	PC	black		
AMY-70-HLD2-C-WHT	Holder C	PC	white		
AMY-70-HLD2-B-WHT	Holder B	PC	white		
AMY-70-HLD2-B50	Holder B	PC	black		
AMY-70-HLD2-B50-WHT	Holder B	PC	white		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C17777_AMY-70-M	285	285	15	9.2
Assembly				
CP19652_AMY-70-M-B50-WHT	210	210	15	8.7
CP19644_AMY-70-M-B50	210	210	15	8.4
CP19116_AMY-70-M-B2-WHT	210	210	15	8.7
CP19108_AMY-70-M-C2-WHT	210	210	15	8.4
CP19091_AMY-70-M-B2	210	210	15	8.7
CP19038_AMY-70-M-C2	210	210	15	8.4




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED BXRV-D10-RGBW2000-A3
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 23.0° / 44.0°
Efficiency 79 %
Peak intensity 3.6 cd/lm
LEDs/each optic 28
Light colour/type RGBW
Required components:
 C19950_HEKLA-SOCKET-RZ



Light distribution files




LED V10 Gen 8-9
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 23.0° / 42.0°
Efficiency 92 %
LEDs/each optic 1
Light colour/type White
Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files



LED V11 HD Gen 8
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 23.0° / 44.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
 Bender Wirth: 633d Hekla





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V13 Gen 8-9
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 51.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files





LED V8 Gen 8-9
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 93 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 41.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CMU15xx
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 51.0°
 Efficiency 88 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files





LED LUXEON Fusion 12-up (20x24)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 41.0°
 Efficiency 84 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8



Light distribution files



LED LUXEON Fusion 21-up (20x24)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 23.0° / 42.0°
 Efficiency 82 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON Fusion 27-up (20x24)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 48.0°
 Efficiency 82 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8



Light distribution files




LED CTM-14 (Tunable White) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.5° / 48.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 442 Typ L8



Light distribution files



LED Fortimo SLM C TW L06A 1313 G7N
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 92 %
 Peak intensity 5.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 508 Typ L8




Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS



LED Fortimo SLM C TW L09A 1919 G7N
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 41.0°
 Efficiency 91 %
 Peak intensity 4.9 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 501 Typ L8



Light distribution files

SAMSUNG



LED LC016D / LC019D / LC026D / LC033D
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 27.0° / 53.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files

SAMSUNG

LED LC016D / LC019D / LC026D / LC033D
 Ordering code C17777_AMY-70-M
 FWHM / FWTM 27.0° / 53.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V13 Gen7
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 51.0°
 Efficiency 92 %
 Peak intensity 3.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED V18 Gen 8-9
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 32.0° / 61.0°
 Efficiency 86 %
 Peak intensity 2.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 639b Hekla XL



LED V3 HD Gen 8
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 32.0°
 Efficiency 94 %
 Peak intensity 7.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V3 HD Gen 8 FC
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 32.0°
 Efficiency 93 %
 Peak intensity 7.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files




LED V4 HD Gen 8
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 34.0°
 Efficiency 94 %
 Peak intensity 7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V6 Gen 8-9
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 35.0°
 Efficiency 94 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V6 Gen 8-9
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 35.0°
 Efficiency 96 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V6 HD Gen 8
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 20.0° / 34.0°
 Efficiency 94 %
 Peak intensity 7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Hekla

Light distribution files



LED V6 HD Gen 8
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 93 %
 Peak intensity 6.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V8 Gen 8-9
 Ordering code C17777_AMY-70-M
 FWHM / FWTM 21.0° / 37.0°
 Efficiency 96 %
 Peak intensity 6.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED V8 Gen7
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 91 %
 Peak intensity 5.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V9 HD Gen 8
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 93 %
 Peak intensity 5.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED VERO10
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 22.0° / 39.0°
Efficiency 91 %
Peak intensity 5.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 F15616_HEKLA-SOCKET-F



Light distribution files




LED VERO13
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 24.0° / 44.0°
Efficiency 89 %
Peak intensity 4.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files



LED VERO18
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 33.0° / 62.0°
Efficiency 90 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED Vesta DTW 13mm (21W)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 93 %
 Peak intensity 6.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 632b Hekla XL

Light distribution files



LED Vesta DTW 15mm (33W)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 27.0° / 50.0°
 Efficiency 91 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 632b Hekla XL

Light distribution files



LED Vesta DTW 6mm
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 93 %
 Peak intensity 6.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652b Hekla

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 37.0°
 Efficiency 91 %
 Peak intensity 6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652b Hekla

Light distribution files



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 23.0° / 39.0°
 Efficiency 87 %
 Peak intensity 5.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F18158_HEKLA-RZ-LENS




Bender Wirth: 652b Hekla

Light distribution files



LED Vesta SE 13mm TW
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 45.0°
 Efficiency 87 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED Vesta TW 13mm (18W) DP
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 45.0°
 Efficiency 90 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 492 Typ L8



LED Vesta TW 15mm DP
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 27.0° / 50.0°
 Efficiency 89 %
 Peak intensity 3.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 482 Typ L8



LED Vesta TW 9mm (9W) DP
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 25.0° / 44.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 489 Typ L8

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU03Q Type-F
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 28.0° / 54.0°
 Efficiency 92 %
 Peak intensity 3.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN


LED CLU03x
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 23.0° / 49.0°
 Efficiency 89 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files

CITIZEN

LED CLU04x
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 33.0° / 66.0°
 Efficiency 80 %
 Peak intensity 1.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 631a Hekla XL

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU700/701/702/703
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 20.0° / 36.0°
 Efficiency 92 %
 Peak intensity 6.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

CITIZEN


LED CLU700/701/702/703
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 21.0° / 37.0°
 Efficiency 93 %
 Peak intensity 6.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

CITIZEN

LED CLU733 Type-F
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 50.0°
 Efficiency 93 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files


Bender Wirth: 631b Hekla XL

OPTICAL RESULTS (SIMULATED):

CITIZEN

LED	CLUD22
Ordering code	CP19038_AMY-70-M-C2
FWHM / FWTM	21.0° + 22.0° / 35.0°
Efficiency	93 %
Peak intensity	6.4 cd/lm
LEDs/each optic	1
Light colour/type	Tunable White
Required components:	
	C16142_HEKLA-SOCKET-K


Bender Wirth: 444 Typ L8



Light distribution files



LED	CMA1825
Ordering code	CP19038_AMY-70-M-C2
FWHM / FWTM	24.0° / 45.0°
Efficiency	90 %
Peak intensity	4.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	
	F15254_HEKLA-SOCKET-B




Light distribution files



LED	CMA1840
Ordering code	CP19038_AMY-70-M-C2
FWHM / FWTM	25.0° / 49.0°
Efficiency	90 %
Peak intensity	3.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	

Bender Wirth: 637a Hekla




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CMA2550
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 30.0° / 60.0°
Efficiency 86 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Bender Wirth: 639a Hekla XL

Light distribution files



LED CMB1818-25
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 22.0° / 44.0°
Efficiency 91 %
Peak intensity 4.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Bender Wirth: 637a Hekla

Light distribution files



LED CMT14xx
Ordering code C17777_AMY-70-M
FWHM / FWTM 22.0° / 38.0°
Efficiency 96 %
Peak intensity 5.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CMT14xx
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 39.0°
 Efficiency 91 %
 Peak intensity 5.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files




LED CMU10xx
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 91 %
 Peak intensity 5.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED CMU22xx
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 33.0° / 67.0°
 Efficiency 80 %
 Peak intensity 1.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 631b Hekla XL





Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CTW0910
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 93 %
 Peak intensity 6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 512 Typ L8




LED CXA/B 15xx
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 20.0° / 40.0°
 Efficiency 91 %
 Peak intensity 5.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15256_HEKLA-SOCKET-D



Light distribution files



LED LUXEON CX Plus CoB L08 (Gen2)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 49.0°
 Efficiency 93 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 637a Hekla

OPTICAL RESULTS (SIMULATED):




LED LUXEON CoB 1202/1203
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 93 %
 Peak intensity 6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files




LED LUXEON CoB 1202HD
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 94 %
 Peak intensity 6.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15848_HEKLA-SOCKET-G



Light distribution files



LED LUXEON CoB 1204/1205
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 25.0° / 46.0°
 Efficiency 92 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 632a Hekla XL

OPTICAL RESULTS (SIMULATED):




LED LUXEON CoB 1204HD
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 93 %
 Peak intensity 5.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files




LED LUXEON CoB 1205HD
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 92 %
 Peak intensity 4.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files



LED LUXEON CoB 1208
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 25.0° / 48.0°
 Efficiency 92 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 632a Hekla XL

OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB - HD S02H6
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 22.0° / 35.0°
 Efficiency 94 %
 Peak intensity 6.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files




LED LUXEON CX Plus CoB - HD S04H9
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 91 %
 Peak intensity 5.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files



LED LUXEON CX Plus CoB - HD S04H9
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 94 %
 Peak intensity 5.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON CX Plus CoB - HD S04H9
 Ordering code C17777_AMY-70-M
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 96 %
 Peak intensity 5.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 44.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15254_HEKLA-SOCKET-B



Light distribution files



LED LUXEON CX Plus CoB M02 / M03 (Gen2)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 94 %
 Peak intensity 5.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15256_HEKLA-SOCKET-D




Light distribution files

OPTICAL RESULTS (SIMULATED):





LED LUXEON CX Plus CoB S01 (Gen2)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 35.0°
 Efficiency 94 %
 Peak intensity 6.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15956_HEKLA-SOCKET-J



Light distribution files



LED CDM-14 (Dim-to-Warm) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 25.0° / 48.0°
 Efficiency 91 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

Bender Wirth: 632b Hekla XL



LED CDM-6 (Dim-To-Warm)
 Ordering code MBO19268_AMY-70-M
 FWHM / FWTM 22.0° / 37.0°
 Efficiency 93 %
 Peak intensity 5.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files


Bender Wirth: 652b Hekla

OPTICAL RESULTS (SIMULATED):



LED CDM-9 (Dim-to-Warm) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 92 %
 Peak intensity 5.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Bender Wirth: 652b Hekla



Light distribution files




LED CHM-9 XH (19x19)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 94 %
 Peak intensity 6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files



LED CTM-14 (Tunable White) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 27.0° / 48.0°
 Efficiency 83 %
 Peak intensity 3.3 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CTM-6 (Tunable White) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 94 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K





Light distribution files

Bender Wirth: 495 Typ L8



LED CTM-6 (Tunable White) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 85 %
 Peak intensity 5.3 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS




Light distribution files

Bender Wirth: 495 Typ L8



LED CTM-9 (Tunable White) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 38.0°
 Efficiency 93 %
 Peak intensity 5.9 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8

OPTICAL RESULTS (SIMULATED):



LED CTM-9 (Tunable White) Gen2
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 85 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS




Light distribution files

Bender Wirth: 495 Typ L8




LED CxM-11 (19x19)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 42.0°
 Efficiency 92 %
 Peak intensity 5.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED CXM-3
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 20.0° / 32.0°
 Efficiency 94 %
 Peak intensity 7.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 634a Bayonet35L

OPTICAL RESULTS (SIMULATED):



LED CXM-4
Ordering code CP19091_AMY-70-M-B2
FWHM / FWTM 21.0° / 32.0°
Efficiency 94 %
Peak intensity 7.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files



LED CxM-6 (13.5x13.5)
Ordering code CP19091_AMY-70-M-B2
FWHM / FWTM 22.0° / 34.0°
Efficiency 94 %
Peak intensity 6.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




BJB: 47.360.1020

Light distribution files



LED COB J-Type
Ordering code CP19038_AMY-70-M-C2
FWHM / FWTM 26.0° / 49.0°
Efficiency 93 %
Peak intensity 3.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Bender Wirth: 663a Hekla XL

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED COB L-Type (LES 11)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 23.0° / 43.0°
 Efficiency 90 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files



LED COB S-Type (LES 6)
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 22.0° / 34.0°
 Efficiency 94 %
 Peak intensity 6.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files



LED COB S-Type (LES 7)
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 94 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED COB T-Type
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 22.0° / 35.0°
 Efficiency 94 %
 Peak intensity 6.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files





LED NF1203EJC-V5
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 20.0 + 22.0° / 38.0°
 Efficiency 93 %
 Peak intensity 6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED NF1206JLC-V5
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 25.0 + 24.0° / 48.0°
 Efficiency 92 %
 Peak intensity 4.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED NJCWL024Z-V1MT: COB L-Type Tunable White
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 36.0°
 Efficiency 94 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 497 Typ L8 HV



LED NJNWS012Z-V1MT: COB S-Type Tunable White
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 34.0°
 Efficiency 94 %
 Peak intensity 6.8 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8 HV



LED NVCWJ024Z-V1MT: COB J-Type Tunable White
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 41.0°
 Efficiency 94 %
 Peak intensity 5.2 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 498 Typ L8 HV

OPTICAL RESULTS (SIMULATED):

PHILIPS

LED Fortimo SLM L15 CoB
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 48.0°
 Efficiency 90 %
 Peak intensity 3.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 632a Hekla XL

Light distribution files

SAMSUNG


LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 20.0° / 40.0°
 Efficiency 92 %
 Peak intensity 5.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

SAMSUNG

LED LC010C G2
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 22.0° / 34.0°
 Efficiency 94 %
 Peak intensity 6.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



BJB: 47.360.1020


Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED	LC010T (Tunable White)
Ordering code	CP19038_AMY-70-M-C2
FWHM / FWTM	22.0° / 37.0°
Efficiency	94 %
Peak intensity	6.1 cd/lm
LEDs/each optic	1
Light colour/type	Tunable White
Required components:	


Bender Wirth: 501 Typ L8



Light distribution files

SAMSUNG

LED	LC016D / LC019D / LC026D / LC033D
Ordering code	CP19038_AMY-70-M-C2
FWHM / FWTM	24.0° / 52.0°
Efficiency	89 %
Peak intensity	3.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	
	F15859_HEKLA-SOCKET-I




Light distribution files

SAMSUNG

LED	LC020C G2
Ordering code	CP19091_AMY-70-M-B2
FWHM / FWTM	22.0° / 38.0°
Efficiency	93 %
Peak intensity	5.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	

BJB: 47.360.1010




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LC020T (Tunable white)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 20.0° / 43.0°
 Efficiency 91 %
 Peak intensity 5.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files

SAMSUNG

LED LC020T (Tunable white)
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 94 %
 Peak intensity 5 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 501 Typ L8

SAMSUNG

LED LC030C/040C G2
 Ordering code CP19091_AMY-70-M-B2
 FWHM / FWTM 24.0° / 44.0°
 Efficiency 93 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1010

OPTICAL RESULTS (SIMULATED):




LED MJT COB LES 14.5
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 48.0°
 Efficiency 93 %
 Peak intensity 4.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files




LED MJT COB LES 14.5
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 26.0° / 51.0°
 Efficiency 89 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED MJT COB LES 6
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 22.0° / 34.0°
 Efficiency 95 %
 Peak intensity 6.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED MJT COB LES 9.8
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 23.0° / 40.0°
 Efficiency 94 %
 Peak intensity 5.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

TRIDONIC


LED SLE G7 LES13
 Ordering code CP19038_AMY-70-M-C2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 92 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

TRIDONIC

LED SLE G7 LES17 H
 Ordering code CP19644_AMY-70-M-B50
 FWHM / FWTM 29.0° / 51.0°
 Efficiency 84 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

XICATO

LED	XOB 14.5 mm
Ordering code	CP19038_AMY-70-M-C2
FWHM / FWTM	26.0° / 45.0°
Efficiency	82 %
Peak intensity	3.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	
	F17438_HEKLA-G2-I



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)